

# Wireless Car Charger - 15W Fast Charging, USB-C, Apple and Samsung Compatible, Windshield/Dash/Vent Phone Holder

MODEL NUMBER: U280-CQ01



Wireless charger delivers convenient, cable-free charging to your Qi-compliant smartphone while you're driving to your destination.

## Features

**Wireless Car Charger Delivers up to 15W to Get Your Device to Capacity While You Travel**Who wants to plug and unplug power cords when you just want to charge your cell phone? The U280-CQ01 makes charging in your vehicle more convenient by doing it wirelessly. Plug the included USB cable from the mobile charger to any compatible USB-A car charger, like the U280-C02-45W-1B (sold separately). Place your Qi-compliant device between the secure clamps on each side of the charger and your device will begin to power up. This wireless phone charger even works through most protective phone cases up to 5 millimeters. Note: please remove any magnetic or metal objects from your phone or case before charging.

**Compatible with Qi-Compliant Cell Phones to Ensure a Safe, Flawless Charge**This Qi wireless charger works with all Qi smartphones from Apple, Samsung, Sony, LG, Nokia and other popular brands, including iPhone and Galaxy S10 models. It protects your expensive device from overheating and overcharging that could lead to internal damage. Dual LEDs glow blue to indicate the charging process is underway. The Qi charger supports power output up to 15W and inputs of 5V 2A, 9V 1.67A and 12V 1.5A.

**Keeps Your Phone Secure for Hands-Free Use While Driving**Use the included cable to connect the wireless charging pad to a user-supplied USB-A power adapter installed in your vehicle (Quick Charge 2.0 or 3.0 adapter is recommended for high-speed charging). A mounting stand and mounting clip are included for securing your phone to the windshield, dashboard or air vents of your vehicle. Adjustable clamps with anti-slip silicon pads effortlessly hold your phone in place while you're driving, even over bumpy roads.

## Specifications

OVERVIEW	
UPC Code	037332250582
Product Type	Wireless Charger

## Highlights

- Charges your Apple, Samsung, Sony, LG or Nokia smartphone wirelessly without a cable
- Universally compatible with all Qi-compatible smartphones and other devices
- Prevents overheating and overcharging to shield your essential device from damage
- Charges your smartphone through its protective case to avoid the hassle of removing it
- Comes with mounting stand and clip for installation on windshield, dashboard or vents

## Applications

- Transfer power from your vehicle's power outlet to your smartphone's battery without the burden of carrying and connecting extra cabling

## System Requirements

- Compatible with all Qi-compliant smartphones, including Apple iPhone 11/11 Pro/11 Pro Max/XS Max/XR/XS/X/8/8 Plus and Samsung Galaxy S10/S10 Plus/S10E/S9/S9 Plus/S8/S8 Plus/Note 9/Note 8/S7/S7 Edge/S6 Edge Plus/Note 5

## Package Includes

- Wireless car charger
- Windshield/dashboard mounting stand
- Vent-mounting clip
- USB-A to USB-C cable, 3.3 ft.
- Owner's manual



Powering Business Worldwide

**TRIPP-LITE**  
by **EAT•N**

Charging Form Factor	Pad/Stand
Device Compatibility	Phone
Technology	Wireless
<b>INPUT</b>	
Nominal Input Voltage(s) Supported	12V DC
Input Connection Type	USB Type-C
Voltage Compatibility (VDC)	5-12V
Input Plug Type	USB-C (FEMALE)
Input Plug Type Details	USB-A to USB-C cable provided
Input Current	1.5-2A
Product Length (in.)	4.764
Product Length (cm.)	12.1
Product Length (ft.)	0.397
Product Length (m)	0.121
<b>OUTPUT</b>	
Overload Protection	Yes
<b>POWER</b>	
Power Consumption (Watts)	15
Power Consumption Detail	15W, 10W, 7.5W, 5W
<b>CONNECTIONS</b>	
Number of Ports	1
Side A - Connector 1	USB C (FEMALE)
Side B - Connector 1	WIRELESS CHARGING COIL
<b>USER INTERFACE, ALERTS &amp; CONTROLS</b>	
LED Indicators	Power Connection (Blue)
<b>CHARGING</b>	
Number of Charging Ports	1
Total Charging Amps	2A
Total Charging Watts	15
Charging Method	Wireless
Charging Method Detail	Qi Compatible
Charging Port Type	WIRELESS CHARGING COIL



Powering Business Worldwide



Charging Ports Details	5W/7.5W/10W/15W
Charging Ports / Amps	2A
<b>PHYSICAL</b>	
Color	Black
Material of Construction	ABS, PVC
Unit Dimensions (hwd / in.)	2.894 x 4.764 x 2.047
Unit Dimensions (hwd / cm)	7.35 x 12.1 x 5.2
Unit Packaging Type	Box
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	32° to 104°F (0° to 40°C)
Storage Temperature Range	14° to 122°F (-10° to 50°C)
Relative Humidity	10% - 80%, NON-CONDENSING
<b>FEATURES &amp; SPECIFICATIONS</b>	
GaN Technology	No
Overcurrent Protection	Yes
Overvoltage Protection	Yes
Over Current Protection	Y
Quick Charge Compliant	No
Driver Required	No
<b>STANDARDS &amp; COMPLIANCE</b>	
Product Compliance	RoHS; REACH
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	2-year limited warranty

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.