

## 10W Magnetic Wireless Charging Pad - Adjustable Stand, 5 ft. Cable, Black

MODEL NUMBER: U280M-005-10-BK



Magnetically secures a compatible smartphone into place for safe, reliable charging with up to 10W of power.

### Features

#### Wireless Cell Phone Charger Delivers Power to Your Smartphone

Who wants to plug and unplug power cords when you want to charge your phone? The U280M-005-10-BK makes charging easier by doing it wirelessly. Just place your Qi-certified cell phone (including iPhone 12 and above) on the 10W charging pad. That's all there is to it. Connect no cable to your phone.

#### Supports Magnetic Charging for a Secure Charge Every Time

The magnetic pad delivers up to 10W of charging power. It snaps a magnetic charging-compatible smartphone securely into place to prevent it from falling off the pad and being disconnected while charging. It even charges your phone through its protective case to spare you the hassle of removing it.

#### Adjustable Stand Gives You More Flexibility Over Charging

You can charge your phone while it lays flat on the charging pad, or you can use the adjustable kickstand for flexible placement during charging. You can place the phone vertically to read notifications and messages while it charges or horizontally to stream video. Note: A device that supports non-magnetic wireless charging can only be charged while laying flat on the charging pad.

#### Compact Charging Pad Fits Comfortably on Any Counter, Table or Workspace

The portable U280M-005-10-BK takes up hardly any space, making it ideal for your bedside table or for carrying in a backpack or laptop bag. A built-in five-foot (1.5-meter) USB-C charging cable connects the charging pad to a wall charger, such as the 9V 2.2A U280-W01-20C1-G (sold separately).

### Highlights

- Magnetic charging pad snaps your smartphone into place for secure charging every time
- Charges your smartphone through its protective case to avoid the hassle of removing it
- Features over-current, over-voltage and short circuit protections to ensure safe charging
- Adjustable stand allows scrolling, texting or watching video vertically or horizontally
- Compatible with Apple iPhone 12 and up, Android and Windows phones

### System Requirements

- Compatible with all Qi-enabled smartphones
- Magnetic charging function requires a compatible smartphone or other device
- Requires a USB-C wall charger up to 20W or a laptop or PC with a USB-C port

### Package Includes

- U280M-005-10-BK 10W Magnetic Wireless Charging Pad
- Quick Start Guide

## Specifications

OVERVIEW	
UPC Code	037332279293
Product Type	Magnetic Charger
Charging Form Factor	Pad/Stand



Powering Business Worldwide

TRIPP LITE  
SERIES

Device Compatibility	Phone
Technology	USB
Country/Region	Global
Host Connector	USB C (MALE)
<b>INPUT</b>	
Nominal Input Voltage(s) Supported	5V DC; 9V DC
Input Cord Gauge (AWG)	24
Input Plug Type	USB-C (MALE)
Bus Powered	No
<b>POWER</b>	
Power Source Type	USB
Power Source	Unit (Included)
<b>CONNECTIONS</b>	
Side A - Connector 1	USB C (MALE)
Side B - Connector 1	Magnetic Charger
Connector Style	Straight
<b>USER INTERFACE, ALERTS &amp; CONTROLS</b>	
LED Indicators	(x1) Charging Status = Green (Charging normally) or Red (flashing when encountering charging error)
<b>CHARGING</b>	
Number of Charging Ports	1
Total Charging Amps	2
Total Charging Watts	10
Charging Method	Magnetic Charger
Charging Method Detail	Provides up to 10W maximum charging output wirelessly to a connected iPhone 12, iPhone 12 Mini, iPhone 12 Pro, iPhone 12 Pro Max, iPhone 13, iPhone 13 Pro and iPhone 13 Pro Max
Charging Port Type	Magnetic Charger
Charging Ports Details	Wireless magnetic pad supports up to 10 watts of charging power
Magnetic Charging	Yes
Wireless Charging	Yes
Overcharge Protection	Yes
Compatible Devices	Smartphone
<b>PHYSICAL</b>	
Color	Black



Powering Business Worldwide

TRIPP LITE  
SERIES

Material of Construction	Plastic
Cable Jacket Color	Black
Connector Color	Black
Cable Jacket Material	PVC
Cable Outer Diameter (OD)	3.5mm
Wire Gauge (AWG)	24
Charging Station Form Factor	Pad/Stand
Cable Length (ft.)	5
Cable Length (m)	1.52
Cable Length (in.)	60
Cable Length (cm)	152.4
Total Number of Ports	1
Unit Dimensions (hwd / in.)	0.670 x 2.360 x 0.000
Unit Dimensions (hwd / cm)	1.69 x 5.98
Unit Dimensions (hwd / mm)	16.9 x 59.8
Unit Packaging Type	Box
Unit Weight (lbs.)	1
Unit Weight (kg)	0.45
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	32° to 104°F (0° to 40°C)
Storage Temperature Range	-4° to 104°F (-20° to 40°C)
Operating Humidity Range	10% to 80% RH
Storage Humidity Range	5% to 95% RH
<b>FEATURES &amp; SPECIFICATIONS</b>	
GaN Technology	No
Overcurrent Protection	Yes
Overvoltage Protection	Yes
Driver Required	No
Qi Compliant	Yes
<b>STANDARDS &amp; COMPLIANCE</b>	
Product Certifications	ICES (Canada); NOM (Mexico)
Product Compliance	CE (Europe); FCC (USA); REACH; RoHS3; UKCA; WEEE
<b>WARRANTY &amp; SUPPORT</b>	



Powering Business Worldwide

TRIPP LITE  
SERIES

Product Warranty Period (Worldwide)	1-year limited warranty
----------------------------------------	-------------------------

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.