

# 10W Magnetic Wireless Charging Pad - Adjustable Stand, 3 ft. Cable, Black

MODEL NUMBER: U280M-S01-10-BK



Magnetically secures a compatible smartphone into place for safe, reliable charging with up to 10W of power.

## Features

### Wireless Cell Phone Charger Delivers Power to Your Smartphone

Who wants to plug and unplug power cords when you want to charge your phone? The U280M-S01-10-BK makes charging easier by doing it wirelessly. Just place your Qi-certified cell phone (including iPhone 12 and above) on the 10W charging pad. That's all there is to it. Connect no cable to your phone.

### Supports Magnetic Charging for a Secure Charge Every Time

The magnetic pad delivers up to 10W of charging power. It snaps a magnetic charging-compatible smartphone securely into place to prevent it from falling off the pad and being disconnected while charging. It even charges your phone through its protective case to spare you the hassle of removing it.

### Adjustable Stand Gives You More Flexibility Over Charging

You can charge your phone while it lays flat on the charging pad, or you can use the adjustable hinge for flexible placement during charging. You can place the phone vertically to read notifications and messages while it charges or horizontally to stream video. **Note:** A device that supports non-magnetic wireless charging can only be charged while laying flat on the charging pad.

### Compact Charging Pad Fits Comfortably on Any Counter, Table or Workspace

The portable U280M-S01-10-BK takes up hardly any space, making it ideal for your bedside table or for carrying in a backpack or laptop bag. A removable three-foot (0.9-meter) charging cable connects the charging pad to a wall charger, such as the 9V 2A U280-W01-QC3-1 (sold separately).

## Highlights

- Magnetic charging pad snaps your smartphone into place for secure charging every time
- Charges your smartphone through its protective case to avoid the hassle of removing it
- Features over-current and over-voltage protections to ensure safe charging
- Adjustable stand allows scrolling, texting or watching video vertically or horizontally
- Compatible with Apple iPhone 12 and up, Android and Windows phones

## System Requirements

- Compatible with all Qi-enabled smartphones
- Magnetic charging function requires a compatible smartphone or other device
- Requires a USB-A wall charger up to 18W or a laptop or PC with a USB-A port

## Package Includes

- U280M-S01-10-BK 10W Magnetic Wireless Charging Pad
- USB-A to USB-C charging cable (M/M), 3 ft. (0.9 m)
- Quick Start Guide

## Specifications

OVERVIEW	
UPC Code	037332279286
Product Type	Wireless Charging Pad
Charging Form Factor	Pad/Stand



Powering Business Worldwide

TRIPP LITE  
SERIES

Device Compatibility	Phone
Technology	Wireless
Country/Region	Global
<b>INPUT</b>	
Nominal Input Voltage(s) Supported	5V DC; 9V DC
Input Connection Type	USB Type-C
Input Cord Gauge (AWG)	30+24
Input Plug Type	USB-C (FEMALE)
Input Plug Type Details	USB-A to USB-C Cable Included
<b>OUTPUT</b>	
Output Capacity (Watts)	10
Overload Protection	N
<b>POWER</b>	
Power Source Type	USB
Power Source	Unit (Included)
Power Consumption (Watts)	10.00
USB Power Delivery (PD) Charging Support	No
<b>CONNECTIONS</b>	
Number of Ports	1
Side A - Connector 1	USB C (FEMALE)
Side B - Connector 1	Magnetic Charger
<b>CHARGING</b>	
Number of Charging Ports	1
Total Charging Amps	1.1
Total Charging Watts	10
Charging Method	Magnetic Charger; Wireless
Charging Method Detail	Place a magnetic charging compatible smartphone directly onto the pad to secure it in place and charge the device
Charging Port Type	WIRELESS CHARGING COIL
Charging Ports Details	Wirelessly and securely charges magnetic charging compatible smartphones with up to 10 Watts (5V/1A, 7.5V/1A, 9V/1.1A)
Charging Ports / Amps	1A
Magnetic Charging	Yes
Wireless Charging	Yes



Powering Business Worldwide

TRIPP LITE  
SERIES

Overcharge Protection	Yes
Compatible Devices	Smartphone
<b>PHYSICAL</b>	
Color	Black
Material of Construction	PC (Plastic)
Cable Jacket Color	Black
Cable Jacket Material	PVC
Cable Outer Diameter (OD)	3.5mm
Wire Gauge (AWG)	30+24
Charging Station Form Factor	Pad/Stand
Cable Length (ft.)	3
Cable Length (m)	0.91
Cable Length (in.)	36.02
Cable Length (cm)	91.5
Total Number of Ports	1
Unit Dimensions (hwd / in.)	0.710 x 3.940 x 3.940
Unit Dimensions (hwd / cm)	1.8 x 10
Unit Dimensions (in.)	0.71 x 3.94
Unit Packaging Type	Box
Unit Weight (lbs.)	0.353
Unit Weight (kg)	0.16
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	32° to 104°F (0° to 40°C)
Storage Temperature Range	-4° to 158°F (-20° to 70°C)
Operating Humidity Range	10% to 80% RH
Storage Humidity Range	5% to 95% RH
<b>FEATURES &amp; SPECIFICATIONS</b>	
GaN Technology	No
Overcurrent Protection	Yes
Overvoltage Protection	Yes
Driver Required	No
Qi Compliant	Yes
<b>STANDARDS &amp; COMPLIANCE</b>	



Powering Business Worldwide

TRIPP LITE  
SERIES

Product Certifications	ICES (Canada); NOM (Mexico)
Product Compliance	CE (Europe); FCC (USA); REACH; RoHS3; UKCA; WEEE
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	1-year limited warranty

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.