

3-Port Compact USB Wall Charger - GaN Technology, 100W PD Charging, 2 USB-C & 1 USB-A, White

MODEL NUMBER: U280-W03-100-G



Travel-sized USB-C/USB-A wall charger provides up to 100W to quickly and efficiently charge your mobile devices at home or on the move.

Features

UL-Listed 3-Port Charger Gets Your Devices Ready in a Hurry, Wherever You Are

This USB charger features one USB-A and two USB-C ports for quickly and safely charging your high-wattage mobile devices. Plug the U280-W03-100-G into any NEMA 1-15R, NEMA 5-15R or NEMA 5-15/20R AC outlet to ensure your laptop, smartphone, tablet, smart watch, earbuds, handheld gaming device and other USB devices charge at the fastest possible speed. The compact unit supports up to 100W for charging when all three ports are being used simultaneously.

PD Charging Port Supports 100W for Fast Charging

The USB-C Power Delivery ports, when used alone, support power output up to 20V 5A (100W), which is more than sufficient for charging and powering nearly any mobile device, including a MacBook or Chromebook. The charger also can support single-device charging up to 22.5W (USB-A only), dual output up to 100W (70W + 30W, 70W + 18W or 12W + 12W), or triple charging output up to 94W (70W + 12W + 12W).

Gallium Nitride Technology Allows High-Wattage Capacity in a Compact Package

This UL-listed wall charger is designed using GaN technology, which has a higher power density than silicon and provides higher efficiency than standard USB-C fast chargers. It stays cool during operation, despite its small size, meaning it won't get hot while charging your device. The U280-W03-100-G also protects your devices against overheating, overcurrent, overcharging and short circuits.

Folding Plug Design Perfectly Sized for Travel

The compact USB Type-C charger is less than 12 cubic inches, easy to carry in your purse, suitcase, backpack or laptop bag and a comfortable fit into crowded power strips and surge protectors. The NEMA 1-15P plug folds into the unit when not in use to shield it from damage and prevent it from snagging or scratching your bag's contents.

Specifications

OVERVIEW

Highlights

- Ideal for charging phones, tablets, handheld gaming devices and laptops while traveling
- USB-C PD 3.0 port supports a maximum power capacity of 100W for fast charging
- Gallium nitride (GaN) technology generates less heat to support high-efficiency charging
- Connects to any NEMA 1-15R, 5-15R or 5-15R/20R AC outlet for immediate charging
- Measures less than 12 cu. in., making it perfectly sized for convenient travel use

Package Includes

- U280-W03-100-G 3-Port USB Wall Charger with PD Charging
- Owner's manual



Powering Business Worldwide

TRIPP LITE
SERIES

UPC Code	037332294609
Product Type	Wall Charger
Charging Form Factor	Direct Plug-In
Device Compatibility	Chromebook; Laptop; Phone; Tablet
Technology	USB
INPUT	
Nominal Input Voltage(s) Supported	120V AC; 240V AC
Input Connection Type	NEMA 1-15P
Voltage Compatibility (VAC)	100; 110; 120; 125; 127; 200; 208; 220; 230; 240
Input Frequency	50/60 Hz
Input Plug Type	NEMA 1-15P (NON-POLARIZED)
Input Current	5A (Max)
OUTPUT	
Frequency Compatibility	50 / 60 Hz
Overload Protection	Yes
POWER	
Power Consumption (Watts)	100.00
USB Power Delivery (PD) Charging Support	Yes
USB Power Delivery (PD) Charging Specification	100W; 20V/5A; 3.0
CONNECTIONS	
Number of Ports	3
Side A - Connector 1	USB C (FEMALE)
Side A - Connector 2	USB C (FEMALE)
Side A - Connector 3	USB A (FEMALE)
USER INTERFACE, ALERTS & CONTROLS	
LED Indicators	Blue - Power
CHARGING	
Number of Charging Ports	3
Total Charging Amps	USB-C1/C2: 20V/5A (100W); USB-A: 10V/2.25A (22.5W)
Total Charging Watts	100
Charging Method	USB



Powering Business Worldwide

TRIPP LITE
SERIES

Charging Port Type	(1) USB A (FEMALE); (2) USB C (FEMALE)
Charging Ports Details	Single Output (100W Max): USB-C1/C2: 5V3A or 9V3A or 15V3A or 20V5A; USB-A: 5V3A or 9V2A or 12V1.5A or 10V2.25A Dual Output (100W Max): USB-C1 + USB-C2: 70W Max + 30W Max; USB-C1 + USB-A: 70W Max + 18W Max; USB-C2 + USB-A: 12W + 12W Triple Output (94W Max): USB-C1 + USB-C2 + USB-A: 70W Max + 12W + 12W
Charging Ports / Amps	1.5A; 2A; 2.25A; 3A; 5A
Compatible Devices	Chromebook; Laptop; Smartphone; Tablet
PHYSICAL	
Color	White
Material of Construction	PC, UL94V-0
Total Number of Ports	3
Unit Dimensions (hwd / in.)	1.165 x 3.169 x 3.149
Unit Dimensions (hwd / cm)	4.7 x 4.1 x 5.6
Unit Packaging Type	Box
Unit Weight (lbs.)	0.40
Unit Weight (kg)	0.18
ENVIRONMENTAL	
Operating Temperature Range	32°F to 77°F (0°C to 25°C)
Storage Temperature Range	-22°F to 158°F (-30°C to 70°C)
Operating Humidity Range	10 to 90% RH, Non-Condensing
Storage Humidity Range	10 to 90% RH, Non-Condensing
Power Provided to Connected Device(s)	USB-C1/C2: 20V/5A (100W), USB-A: 10V/2.25A (22.5W)
FEATURES & SPECIFICATIONS	
GaN Technology	Yes
Overcurrent Protection	Yes
Overvoltage Protection	Yes
Over Current Protection	Yes
Quick Charge Compliant	No
Driver Required	No
STANDARDS & COMPLIANCE	
Product Certifications	NOM (Mexico); UL Listed
Product Compliance	RoHS; REACH; WEEE; FCC (USA)
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	2-year limited warranty



Powering Business Worldwide

TRIPP LITE
SERIES

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2026 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.