

## 4-Port Compact USB Wall Charger - GaN Technology, 100W PD Charging, 2 USB-C & 2 USB-A, White

MODEL NUMBER: **U280-W04-100C2G**



Travel-sized USB-C/USB-A wall charger provides up to 100W to quickly and efficiently charge your mobile devices at home or on the move.

### Features

#### 100W 4-Port Charger Gets Your Mobile Devices Ready in a Hurry, Wherever You Are

This USB charger features two USB-C and two USB-A ports for quickly and safely charging your mobile devices. Plug the U280-W04-100C2G into any NEMA 1-15R, NEMA 5-15R or NEMA 5-15/20R AC outlet to ensure your laptop, smartphone, tablet and other USB devices charge at their fastest possible speed. The compact unit supports up to 100W for charging when all four ports are being used simultaneously.

#### PD Charging Port Supports 100W for Fast Charging

The USB-C Power Delivery port, when used alone, supports power output up to 20V 5A (100W), which is more than sufficient for charging and powering nearly any mobile device, such as a MacBook or Chromebook.

#### Gallium Nitride Technology Allows High-Wattage Capacity in a Compact Package

This USB wall charger is designed using GaN technology, which has a higher power density than silicon and provides higher efficiency than standard USB-C fast chargers. It also stays cool during operation, despite its small size, meaning it won't get hot while charging your device.

#### Built-In Auto-Sensing Adjusts to Proper Power Level to Get Your Device to 100%

The U280-W04-100C2G features auto-sensing technology that automatically adjusts to your devices' appropriate power level, perfect for fast-charging tablets and e-readers. The unit protects against overheating, overcurrent, overcharging and short circuits. In fact, it stops charging as soon as your device's batteries are at full capacity.

#### Folding Plug Design Perfectly Sized for Travel

The compact USB Type-C charger is less than 12 cubic inches, easy to carry in your purse, suitcase, backpack or laptop bag. The NEMA 1-15P plug folds into the unit when not in use to shield it from damage and prevent it from snagging or scratching your bag's contents.

### Highlights

- Ideal for charging smartphones, tablets, e-readers and laptops while traveling
- USB-C PD 3.0 port supports a maximum power capacity of 100W for fast charging
- Gallium nitride (GaN) technology generates less heat to support high-efficiency charging
- Connects to any NEMA 1-15R, 5-15R or 5-15R/20R AC outlet for immediate charging
- Measures less than 12 cu. in., making it perfectly sized for convenient travel use

### Applications

Charge multiple smartphones, tablets, laptops or other mobile devices without taking up valuable USB ports on your computer

### Package Includes

- U280-W04-100C2G 4-Port USB Wall Charger with PD Charging
- Quick Start Guide

## Specifications

OVERVIEW	
UPC Code	037332259684
Device Compatibility	Phone; Tablet



Over Current Protection	Yes
Technology	USB 3.0 (SuperSpeed); USB 3.1 (Gen 1)
<b>INPUT</b>	
Voltage Compatibility (VAC)	100; 110; 120; 125; 127; 200; 208; 220; 230; 240
Input Frequency	50/60 Hz
Input Current	1.6A (Max)
Product Length (in.)	3.169
Product Length (cm.)	8.05
Product Length (ft.)	0.264
Product Length (m.)	0.081
<b>OUTPUT</b>	
Output Capacity	5V 3A, 9V 3A, 15V 3A, 20V 3.25A, 9V 2A, 5V 3.4A, 20V 5A, 5V 2.4A
<b>POWER</b>	
USB Power Delivery (PD) Charging Support	Yes
USB Power Delivery (PD) Charging Specification	3.0
<b>USER INTERFACE, ALERTS &amp; CONTROLS</b>	
LED Indicators	Blue - Power
<b>CHARGING</b>	
Number of Charging Ports	4
Charging Method	USB
Charging Ports / Amps	(2) 2.4A; 3A; 5A
<b>PHYSICAL</b>	
Color	White
Material of Construction	PC (Plastic)
Unit Dimensions (hwd / cm)	2.96 x 8.05 x 8.0
Unit Dimensions (hwd / in.)	1.165 x 3.169 x 3.149
Unit Packaging Type	Box
Unit Weight (kg)	0.26
Unit Weight (lbs.)	0.58
<b>ENVIRONMENTAL</b>	



Operating Temperature Range	0 to 77 °F (0 to 25 °C)
Storage Temperature Range	-4 to 176 °F (-20 to 80 °C)
Operating Humidity Range	20 to 90% RH, Non-Condensing
Storage Humidity Range	5 to 95% RH, Non-Condensing
Power Provided to Connected Device(s)	USB C1 (65W) + USB C2 (18W) + USB A1-2 (17W) = 100W
<b>CONNECTIONS</b>	
Ports	4
Side A - Connector 1	(2) USB C (FEMALE)
Side A - Connector 2	(2) USB A (FEMALE)
<b>SPECIAL FEATURES</b>	
GaN Technology	Yes
<b>STANDARDS &amp; COMPLIANCE</b>	
Certifications	RoHS, REACH, FCC, UL, NOM, ISO9001, WEEE
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	2-year limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>