

USB 3.0 SuperSpeed Adapter - USB-A to USB-A, M/F, Down Angle, Black

MODEL NUMBER: U324-000-DN



Converts a standard USB port into a more convenient down-angled USB port in tight spaces, such as behind furniture or against a wall.

Features

One-Piece Adapter Connects Computers, Printers, Modems and Other USB Equipment This palm-sized USB adapter connects your computer, laptop or other compatible USB-A device, such as a Chromebook or Surface Pro tablet, to a USB-A keyboard, printer, portable hard drive, patch panel or other peripheral. It supports USB 3.0 data transfer speeds up to 5 Gbps, which is 10 times faster than USB 2.0. The fully molded piece is small enough to carry in your pocket, purse or laptop bag.

Down-Angle USB-A Port Makes Connecting and Disconnecting Easier in Tight Spaces The female USB connector is designed at a 90-degree down angle, which makes it easier to connect cables where space is at a premium. This helps you, for instance, save space in your workspace by letting you push your PC flush against the wall or the back of a cabinet. Instead of leaving space in the rear for protruding USB cables, the U324-000-DN allows you to connect cables parallel to your computer.

Highlights

- Recommended for powering computers, printers and other home/office peripherals
- 90-degree-angled form factor is ideal for tight spaces, such as flush against a wall
- Supports USB 3.0 SuperSpeed data transfer rates up to 5 Gbps—10x faster than USB 2.0
- Durable one-piece molded adapter fits easily in pocket or bag for connecting anywhere
- Plug-and-play operation with no software required for easy, immediate installation

Applications

- Connect devices like computers, servers and external hard drives in your data center, workspace or home theater
- Create a USB connection in a hard-to-reach space, such as against a wall or behind a desk

Package Includes

- U324-000-DN USB 3.0 SuperSpeed Adapter

Specifications

OVERVIEW	
UPC Code	037332248688
Technology	USB
CONNECTIONS	
Side A - Connector 1	USB 3.0 A (MALE)
Side B - Connector 1	USB 3.0 A (FEMALE)
Connector Plating	Nickel
Contact Plating	Gold
PHYSICAL	



Powering Business Worldwide

TRIPP LITE
SERIES

Color	Black
Material of Construction	PVC
Unit Dimensions (hwd / in.)	0.690 x 0.910 x 0.340
Unit Packaging Type	Polybag
ENVIRONMENTAL	
Operating Temperature Range	32° to 122°F (0° to 50°C)
Storage Temperature Range	-4° to 140°F (-20° to 60°C)
Relative Humidity	10% to 90%, Non-Condensing
FEATURES & SPECIFICATIONS	
USB Specification	USB 3.0 (up to 5 Gbps); USB 3.1 Gen 1 (up to 5 Gbps)
STANDARDS & COMPLIANCE	
Product Compliance	RoHS; REACH
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.