

## USB 3.0 SuperSpeed Extension Cable (A M/F), Blue, 16 ft. (4.88 m)

MODEL NUMBER: U324-016



Extension cord connects two devices with USB-A connectors or extends your existing USB cable by 16 feet.

### Features

**16-Foot Extension Cable Connects Computers, Printers, Modems and Other USB Equipment** This USB 3.0 SuperSpeed Type-A Extension Cable (M/F) attaches to your current USB 3.0 cable to extend it by 16-ft. (4.88 m) It connects your computer, laptop or other compatible USB 3.0 device, such as a Chromebook or Surface Pro tablet, to a USB-A keyboard, printer, portable hard drive, patch panel or other peripheral. The 16-ft. (4.88 m) length allows you great flexibility in placing equipment with respect to the power outlet.

**Transfers Data at SuperSpeed Transfer Rates up to 5 Gbps** The U324-016 supports USB 3.0 speeds up to 5 Gbps—10 times the speed of USB 2.0—and better power efficiency with no device polling and lower active and idle power requirements. The cable's bi-directional data interface allows data to flow both directions simultaneously, increasing theoretical bandwidth by 10 times. Sync-N-Go technology allows the cable to quickly detect and sync the connected devices. The cable is backward compatible with previous USB generations, allowing you to use it with legacy devices.

### Highlights

- Recommended for connecting computers, hard drives and other USB-A devices
- Supports USB 3.0 SuperSpeed data transfer rates up to 5 Gbps—10x faster than USB 2.0
- Bi-directional data interface allows data to flow both directions simultaneously
- 16-ft. (4.88 m) length allows great flexibility in placing devices in relationship to AC outlet
- Ideal replacement for worn-out or missing 16-ft. (4.88 m) extension cord

### Applications

- Connect devices like computers, servers and external hard drives in your data center, workspace or home theater
- Extend an existing USB connection up to 16-ft. (4.88 m) to more easily place a device
- Provide a high-quality replacement for a worn-out or missing power cord

### System Requirements

- Devices and cable with USB-A connectors (USB 3.0 capability required to reach USB 3.0 speeds)

### Package Includes

- U324-016 USB 3.0 SuperSpeed Extension Cable, A to A, M/F, Blue, 16-ft. (4.88 m)

## Specifications

OVERVIEW	
UPC Code	037332241467
Technology	USB 3.x
Cable Type	Passive
INPUT	
Product Length (in.)	192
Product Length (cm.)	487.68



Powering Business Worldwide

TRIPP LITE  
SERIES

Product Length (ft.)	16
Product Length (m)	4.87
<b>CONNECTIONS</b>	
Side A - Connector 1	USB 3.0 A (MALE)
Side B - Connector 1	USB 3.0 A (FEMALE)
Connector Plating	Nickel
Contact Plating	Gold
Connector Style	Straight
<b>PHYSICAL</b>	
Material of Construction	PVC
Cable Jacket Color	Blue
Cable Jacket Rating	VW-1
Cable Outer Diameter (OD)	5.5MM
Cable Length (ft.)	16
Cable Length (m)	4.88
Cable Length (in.)	192
Cable Length (cm)	487.68
Shipping Dimensions (hwd / in.)	9.00 x 7.00 x 0.50
Shipping Weight (lbs.)	0.43
Shipping Weight (kg)	0.20
Unit Packaging Type	Polybag
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	32° to 113°F (0° to 45°C)
Storage Temperature Range	-43° to 158°F (-40° to 70°C)
Operating Humidity Range	10% to 85% RH, Non-Condensing
Storage Humidity Range	5% to 90% RH, Non-Condensing
<b>FEATURES &amp; SPECIFICATIONS</b>	
USB Specification	USB 3.0 (up to 5 Gbps)
<b>STANDARDS &amp; COMPLIANCE</b>	
Product Compliance	RoHS; CE (Europe); REACH; FCC (USA)
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty



*Powering Business Worldwide*

TRIPP LITE  
SERIES

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.