

- Male-to-male is not a standard USB cable configuration. It's used only in rare instances where a peripheral or patch bay employs a female connector instead of a USB-B port.
- This cable will not connect two PCs. File-sharing between computers requires special software-driven cables.

USB 3.0 SuperSpeed A to A Cable for Tripp Lite USB 3.0 All-in-One Keystone/Panel Mount Couplers (M/M), Black, 15 ft. (4.6 m)

MODEL NUMBER: U325-015



Connects peripherals, patch bays and Tripp Lite USB All-in-One Keystone/Panel Mount Couplers with female USB-A ports to your computer, laptop or other compatible USB device, such as a Chromebook™ or Microsoft® Surface®.

Features

USB Cable Connects USB Type-A Peripherals to Your Computer

This USB-A to USB-A cable is ideal for connecting high-speed USB 3.0 equipment, such as a patch bay or other USB peripherals, to your computer, laptop or other compatible device, such as a Chromebook or Microsoft Surface. Additionally, the U325-015 cable is recommended for use with Tripp Lite's U325-000-KP-BK, U325-000-KPA-BK and U325-001-KPA-BK USB couplers.

Supports USB 3.0 Speeds for a Faster, More Efficient Signal

The U325-015 supports USB 3.0 data transfer rates up to 5 Gbps—10 times faster than USB 2.0. Its bi-directional data interface allows data to flow both directions simultaneously, increasing theoretical bandwidth by 10 times for efficient power and little wait-time. The U325-015 is also backward compatible with previous USB generations, so you can continue to use legacy USB 2.0 and USB 1.1 peripherals.

Filtering EMI/RFI Line Noise and Eliminating Cable Strain Help Your Equipment Perform Better

Foil and braid shielding blocks disruptive EMI (electromagnetic interference) and RFI (radio frequency interference) line noise that can disturb your electronics and inflict hardware damage or data loss. Integral strain relief gives the U325-015 extra flexibility, reduces stress and helps the cable move freely without cracking or breaking loose from the connector.

Specifications

OVERVIEW

UPC Code

037332274588

Highlights

- Supports USB 3.0 speeds up to 5 Gbps to ensure fast data transfers
- Backward compatible with legacy USB 2.0 and USB 1.1 peripherals
- Foil/braid shielding protects against EMI/RFI line noise that can distort or destroy data
- Integral strain relief helps cable move freely without stress or cracking
- Plug-and-play operation with no drivers required for easy, immediate installation

System Requirements

- Computer with USB-A female port
- Peripheral or patch bay with USB-A female port

Package Includes

- U325-015 USB 3.0 SuperSpeed A/A Cable (M/M), Black, 15 ft.

Technology	USB; USB 3.x
Host Connector	USB A (MALE)
USB Cable Type	Passive
PHYSICAL	
Material of Construction	PVC
Cable Jacket Color	Black
Connector Color	Black
Cable Jacket Material	PVC
Cable Jacket Rating	VW-1
Cable Outer Diameter (OD)	5.5mm
Cable Length (ft.)	15
Cable Length (m)	4.57
Cable Length (in.)	180
Unit Packaging Type	Polybag
ENVIRONMENTAL	
Operating Temperature Range	32 TO 122 F (0 TO 50 C)
Storage Temperature Range	-4 to 140 F (-20 to 60 C)
Operating Humidity Range	10% TO 90% RH, Non-Condensing
Storage Humidity Range	10% TO 90% RH, Non-Condensing
CONNECTIONS	
Side A - Connector 1	USB A (MALE)
Side B - Connector 1	USB A (MALE)
Connector Plating	Nickel
Contact Plating	Gold
FEATURES & SPECIFICATIONS	
USB Specification	USB 3.0 (up to 5 Gbps)
STANDARDS & COMPLIANCE	
Product Compliance	RoHS; REACH
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty



1000 Eaton Boulevard
Cleveland, OH 44122
United States



© 2023 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.