

- Male-to-male is not a standard USB cable configuration. It's used only in rare instances where a peripheral or patch bay employs a female connector instead of a USB-B port.
- This cable will not connect two PCs. File-sharing between computers requires special software-driven cables.

## USB 3.2 Gen 1 SuperSpeed A/A Cable (M/M), Black, 6 ft. (1.83 m)

MODEL NUMBER: U325X-006



Connects a USB peripheral or patch bay to your computer, laptop or other USB-enabled device compatible with 5 Gbps speeds.

### Features

#### USB Cable Connects USB Type-A Peripherals to Your Computer

This USB-A to USB-A cable is ideal for connecting external hard drives and other high-speed USB 3.2 Gen 1 peripherals to your computer, laptop or other compatible device, such as a Chromebook or Microsoft Surface.

#### Supports USB 3.2 Gen 1 Speeds for a Faster, More Efficient Signal

The U325X-006 supports USB 3.2 Gen 1 data transfer rates up to 5 Gbps—10 times faster than USB 2.0. Its bi-directional data interface allows data to flow both directions simultaneously, increasing theoretical bandwidth by 10 times for efficient power and little wait-time. The U325X-006 is also backward compatible with previous USB generations, so you can continue to use legacy USB 2.0 and USB 1.1 peripherals.

#### Filtering EMI/RFI Line Noise and Eliminating Cable Strain Help Your Equipment Perform Better

Foil and braid shielding blocks disruptive EMI (electromagnetic interference) and RFI (radio frequency interference) line noise that can disturb your electronics and inflict hardware damage or data loss. Twisted pair construction reduces crosstalk, which helps your connected components perform better and last longer. Integral strain relief gives the U325X-006 extra flexibility, reduces stress and helps the cable move freely without cracking or breaking loose from the connector.

### Highlights

- Supports USB 3.2 Gen 1 speeds up to 5 Gbps to ensure fast data transfers
- Backward compatible with legacy USB 2.0 and USB 1.1 peripherals
- Foil/braid shielding protects against EMI/RFI line noise that can distort or destroy data
- Integral strain relief helps cable move freely without stress or cracking
- Plug-and-play operation with no drivers required for easy, immediate installation

### Package Includes

- U325X-006 USB-A Cable (M/M), USB 3.2 Gen 1, Black, 6 ft. (1.8 m)

## Specifications

OVERVIEW	
UPC Code	037332274595
Technology	USB; USB 3.x



Host Connector	USB A (MALE)
USB Cable Type	Passive
<b>PHYSICAL</b>	
Material of Construction	PVC
Color	Black
Cable Jacket Color	Black
Connector Color	Black
Cable Jacket Material	PVC
Cable Jacket Rating	VW-1
Cable Outer Diameter (OD)	5.5mm
Cable Length (ft.)	6
Cable Length (m)	1.83
Cable Length (in.)	72
Unit Packaging Type	Polybag
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	32 TO 122 F (0 TO 50 C)
Storage Temperature Range	-4 TO 140 F (-20 TO 60 C)
Operating Humidity Range	10% TO 90% RH, Non-Condensing
Storage Humidity Range	10% TO 90% RH, Non-Condensing
<b>CONNECTIONS</b>	
Side A - Connector 1	USB A (MALE)
Side B - Connector 1	USB A (MALE)
Connector Plating	Nickel
Contact Plating	Gold
<b>FEATURES &amp; SPECIFICATIONS</b>	
USB Specification	USB 3.2 Gen 1 (up to 5 Gbps)
<b>STANDARDS &amp; COMPLIANCE</b>	
Product Compliance	RoHS; REACH
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>