



# USB 3.2 Gen 2 Active Extension Cable - USB-C to USB-A (M/F), 10 Gbps, Data Only, 5 m (16.4 ft.)

MODEL NUMBER: U330-05M-C2A-G2











Active 16 ft. extension cord increases the distance between two USB devices, including MacBooks and Windows laptops, without signal loss.

#### **Features**

USB Extension Cable Connects Computers, Printers, Modems and Other USB Equipment
This USB-C to USB-A Active Extension Cable (M/F) attaches to your current USB 3.2 Gen 2 cable to
extend it by five meters (16.4 feet). It connects your MacBook Pro, Windows laptop, Chromebook or other
compatible USB-C device to a USB-A webcam, keyboard, printer, portable hard drive, patch panel or
other peripheral. The extra length allows you greater flexibility in placing equipment where most needed.

### **Built-In Signal Booster for Peak Performance**

Just connect the active cable's USB-C plug to your computer's USB-C port and the USB-A female connector to a USB device cable to extend your total connection beyond USB's natural five-meter limit. The bus-powered signal booster ensures USB 3.2 Gen 2 data transfer speeds up to 10 Gbps, twice as fast as USB 3.2 Gen 1, with no signal loss. The cable is backward compatible with previous USB generations, so you can use it with legacy equipment.

# 900mA of Proper Power to Keep Devices Functioning

The U330-05M-C2A-G2 works with standard USB 3.2 Gen 2 cables and provides up to 900mA of power to a connected device.

# **Specifications**

OVERVIEW		
UPC Code	037332268686	
Technology	USB 3.x	
Cable Type	Active	
INPUT		
Bus Powered	Yes	

# **Highlights**

- Adds 5 meters to your existing USB connection to provide flexibility in placing devices
- Connects existing USB-A peripherals to newer laptops or tablets with USB-C ports
- Supports USB 3.2 Gen 2 speeds up to 10 Gbps to ensure fast data transfers
- Provides up to 900mA of power to connected device without need for external power
- Plug-and-play operation with no software required for easy, immediate installation

# **System Requirements**

USB 3.2 Gen 2 computer port and USB 3.2 Gen 2 connected device required to meet USB 3.2 Gen 2 speeds

# **Package Includes**

U330-05M-C2A-G2 USB-C Active Extension Cable, USB-C to USB-A (M/F), 5 m (16.4 ft.)





POWER	
USB Power Delivery (PD) Charging Support	No
CONNECTIONS	
Side A - Connector 1	USB C (MALE)
Side B - Connector 1	USB A (FEMALE)
Connector Plating	Nickel
Contact Plating	Gold; Nickel
Connector Style	Straight
PHYSICAL	
Material of Construction	TPE + ABS
Cable Jacket Color	Black
Cable Jacket Material	TPE
Cable Outer Diameter (OD)	4.8MM
Cable Length (ft.)	16.4
Cable Length (m)	5.00
Unit Packaging Type	Polybag
Unit Weight (lbs.)	0.51
Unit Weight (kg)	0.23
ENVIRONMENTAL	
Operating Temperature Range	32° to 113°F (0° to 45°C)
Storage Temperature Range	14° to 158°F (-10° to 70°C)
Operating Humidity Range	10% TO 85% RH, Non-Condensing
Storage Humidity Range	5% TO 90% RH, Non-Condensing
Power Provided to Connected Device(s)	900mA
FEATURES & SPECIFICATIONS	
USB Specification	USB 3.2 Gen 2 (Up to 10 Gbps)
Driver Required	No
STANDARDS & COMPLIANCE	
Product Compliance	RoHS; CE (Europe); REACH; FCC (USA)
WARRANTY & SUPPORT	





Product Warranty Period (Worldwide)	3-year limited warranty
--	-------------------------

1000 Eaton Boulevard Cleveland, OH 44122 United States https://tripplite.eaton.com © 2024 Eaton. All Rights Reserved. Eaton is a registered trademark. All other trademarks are the property of their respective owners.