



USB 3.2 Gen 1 Active Extension Repeater Cable (A M/F), 10 m (32.8 ft.)

MODEL NUMBER: U330-10M-1











USB 3.2 Gen 1 active extension cable increases the distance between 2 connected USB-A devices with no latency issues or loss of signal.

Features

Extension Cable Connects Computers, Printers, Modems and Other USB Equipment

This USB-A active extension repeater cable (M/F) attaches to your current USB cable to extend it by 10 meters (32.8 feet). It connects your computer, laptop or other compatible USB device to a USB-A cable from a webcam, keyboard, printer, portable hard drive, game console or other peripheral. By adding 10 more meters to your connection, you have more flexibility in placing your devices. And by daisy-chaining two U330-10M-1 cables, you can extend the USB connection even further – up to 20 meters (65.6 feet).

Built-In Signal Booster Ensures Top Performance

Just connect the active cable's male end to your computer's USB port and the female end to a USB device cable to extend your total connection beyond USB's natural five-meter (16.4-foot) limit. The buspowered signal booster ensures USB 3.2 Gen 1 data transfer speeds up to 5 Gbps with no signal loss. The cable is backward compatible with previous USB generations, so you can use it with legacy equipment.

900mA of Power Keeps Your Devices Functioning

The U330-10M-1 works with standard USB cables and supports up to 900mA of power to a connected device. Although not required, the cable's additional USB-A male connector is provided for applications where power is needed. If your application is not working correctly without power, connect the built-in connector to a USB-A port on your monitor. The plug-and-play U330-10M-1 supports all major operating systems, including Windows, macOS and Linux.

Specifications

OVERVIEW		
UPC Code	037332268679	
Technology	USB 3.x	
Cable Type	Active	

Highlights

- Adds 10 meters to your existing connection to provide flexibility in placing devices
- Increase the extension to 20 meters by daisy-chaining 2 cables together
- Bus-powered cable provides up to 900mA of power to connected device
- Supports USB 3.2 Gen 1 data transfer rates up to 5 Gbps – 10x faster than USB 2.0
- Plug-and-play operation with all major operating systems, including Windows and macOS

System Requirements

USB 3.2 Gen 1 computer port and USB 3.2 Gen 1 connected devices required to meet USB 3.2 Gen 1 speeds

Package Includes

U330-10M-1 USB 3.2 Gen 1 Active Extension Repeater Cable (M/F), 10 m (32.8 ft.)





INPUT		
Bus Powered	Yes	
POWER		
USB Power Delivery (PD) Charging Support	No	
CONNECTIONS		
Side A - Connector 1	USB A (MALE)	
Side B - Connector 1	USB A (FEMALE)	
Side B - Connector 2	USB A (MALE)	
Connector Plating	Nickel	
Contact Plating	Gold	
Connector Style	Straight	
PHYSICAL		
Cable Jacket Color	Black	
Cable Jacket Material	PVC	
Cable Jacket Rating	VW-1	
Cable Outer Diameter (OD)	6.0mm	
Cable Length (ft.)	32.8	
Cable Length (m)	10.00	
Unit Packaging Type	Polybag	
ENVIRONMENTAL		
Operating Temperature Range	32° to 113°F (0° to 45°C)	
Storage Temperature Range	-40° to 158°F (-40° to 70°C)	
Operating Humidity Range	10% TO 85% RH, Non-Condensing	
Storage Humidity Range	5% TO 90% RH, Non-Condensing	
Power Provided to Connected Device(s)	900mA VIA ADDITIONAL USB-A CONNECTOR	
FEATURES & SPECIFICATIONS		
USB Specification	USB 3.2 Gen 1 (up to 5 Gbps)	
Driver Required	No	
STANDARDS & COMPLIANCE		
Product Compliance	RoHS; CE (Europe); REACH; FCC (USA)	





WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	3-year limited warranty

1000 Eaton Boulevard Cleveland, OH 44122 United States https://tripplite.eaton.com © 2024 Eaton. All Rights Reserved. Eaton is a registered trademark. All other trademarks are the property of their respective owners.