

USB 3.2 Gen 1 Active Extension Cable with USB-C Charging - USB-C to USB-C (M/F), 5 Gbps, Data Only, 15 m (49.2 ft.)

MODEL NUMBER: U330-15M-C2C-C



Active USB-C extension cord allows flexible placement of a USB-C device up to 49.2 ft. from the source.

Features

USB-C Extension Cable Connects Computers, Printers, Modems and Other USB-C Equipment

This USB-C to USB-C Active Extension Cable (M/F) attaches to your current USB 3.2 Gen 1 cable to extend it by 15 meters (49.2 feet). It connects your computer, tablet, notebook, MacBook Pro, Chromebook, smartphone or other compatible USB-C device to a USB-C keyboard, portable hard drive, webcam or microphone/headset. The 15-meter length allows you great flexibility in placing equipment. The U330-15M-C2C-C is recommended for classrooms, conference rooms and other areas where USB-C devices may be placed apart from each other.

Built-In Signal Booster for Peak Performance

Just connect the active cable's male USB-C plug to your laptop or notebook computer and the female USB-C connector to a USB device cable to extend your total connection well beyond USB's natural five-meter limit. The bus-powered signal booster ensures USB 3.2 Gen 1 data transfer speeds up to 5 Gbps with no signal loss. The USB-C active extension cable is backward compatible with previous USB generations, so you can use it with legacy equipment.

5V USB-C PD Charging Port Keeps Devices Functioning

The U330-15M-C2C-C works with a standard USB-C charging cable and a compatible Power Delivery (PD) charger to provide 5V to a connected device to ensure a stable connection from the host to the device. **Note:** The USB-C 5V charging port is not required for all applications. In the event that external power is required, the following USB power adapter models can be purchased separately: U280-002-W12, U280-W02-A1C1.

Highlights

- Adds 49.2 ft. to your existing USB-C connection to provide flexibility in placing devices
- Supports USB 3.2 Gen 1 data transfer rates up to 5 Gbps: 10x faster than USB 2.0
- USB-C PD charging port provides up to 5V to ensure stable connection
- Recommended for laptops, Chromebooks, MacBook Pros and other USB-C devices

System Requirements

- USB 3.2 Gen 1 computer port and USB 3.2 Gen 1 connected device required to meet USB 3.2 Gen 1 speeds up to 5 Gbps
- Optional USB-C power port requires a USB-C cable and PD charger (sold separately)

Package Includes

U330-15M-C2C-C USB-C Active Extension Cable, USB-C to USB-C (M/F), 15 m (49.2 ft.)

Specifications

OVERVIEW	
UPC Code	037332293466
Technology	USB 3.x
Country/Region	Global



Powering Business Worldwide

TRIPP LITE
SERIES

Cable Type	Active
INPUT	
Voltage Compatibility (VDC)	5V
Bus Powered	Yes
CONNECTIONS	
Side A - Connector 1	USB C (MALE)
Side B - Connector 1	(2) USB C (FEMALE)
Connector Plating	Nickel
Contact Plating	Gold
Connector Style	Straight
Daisy-chainable / Cascadable	No
USER INTERFACE, ALERTS & CONTROLS	
LED Indicators	(x1) Blue LED (Power)
PHYSICAL	
Color	Black; Gray
Material of Construction	PVC + ALUMINUM
Cable Jacket Color	Black
Connector Color	Black; Gray
Cable Jacket Material	PVC
Cable Jacket Rating	VW-1
Cable Outer Diameter (OD)	USB-C 3.2 M: 7.0MM ; USB-C 2.0 F (POWER): 2.8MM
Wire Gauge (AWG)	28/22
Cable Length (ft.)	49.2
Cable Length (m)	15.00
Cable Length (in.)	590.6
Cable Length (cm)	50
Shipping Dimensions (hwd / in.)	17.01 x 14.02 x 0.50
Shipping Weight (lbs.)	2.29
Unit Dimensions (hwd / in.)	10.000 x 7.090 x 0.500
Unit Packaging Type	Polybag
Unit Weight (lbs.)	2.29
Unit Weight (kg)	1.04
ENVIRONMENTAL	



Powering Business Worldwide

TRIPP LITE
SERIES

Operating Temperature Range	32° to 104°F (0° to 40°C)
Storage Temperature Range	-4° to 140°F (-20° to 60°C)
Relative Humidity	0% TO 90% RH, NON-CONDENSING
Power Provided to Connected Device(s)	5V 3A
COMMUNICATIONS	
USB Extension Support	Yes
FEATURES & SPECIFICATIONS	
USB Specification	USB 3.2 Gen 1 (up to 5 Gbps)
Driver Required	No
STANDARDS & COMPLIANCE	
Product Certifications	EN 55032; EN 55035
Product Compliance	CE (Europe); FCC Part 15 Class B (USA); REACH; RoHS3; UKCA; WEEE
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	3-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.