

USB 3.0 SuperSpeed to SATA III Adapter for 2.5 in. to 3.5 in. SATA Hard Drives

MODEL NUMBER: U338-000-SATA



Format new hard drives, or salvage data off old drives

Description

The U338-000-SATA USB 3.0 SuperSpeed to SATA III Adapter allows connection to a Serial ATA Hard drive (2.5" / 3.5"). Configure hard drives without having to install them first, or pull data from a crashed computer hard drive to a new computer. The unit features a 22-pin SATA Data + Power connector and USB 3.0 Micro-B connector. Works with any 2.5 in. to 3.5 in. SATA Hard Drive. The U338-000-SATA is compatible with Windows (up to 10) and macOS, and can be connected to older USB generation computers.

Features

- USB 3.0 and below compliant
- SATA III (6Gbps) and below compliant
- Supports Plug-and-Play...No Drivers or Software needed
- Supports LBA-48 bit (Logical Block Addressing)
- Supports USB Mass Storage Class Bulk-Only Transport
- 22-Pin SATA Data + Power connector
- Compatible with 2.5" / 3.5" SATA Hard drives
- Supports drives up to 4TB
- Compatible with Windows (up to 10), Mac, Linux

Specifications

OVERVIEW	
UPC Code	037332182135
Technology	SATA/eSATA
POWER	

Highlights

- SuperSpeed (5Gbps) / Hi-Speed (480 Mbps) / Full-Speed (12 Mbps) Compliant
- SATA III (6Gbps) / SATA Gen2i (3Gbps) / Gen1i (1.5Gbps) Compliant
- For 2.5 in. to 3.5 in. SATA Hard Drives
- Supports drives up to 4TB
- Compatible with Windows (up to 10), MAC, LINUX

System Requirements

- Computer with USB 3.0 port (2.0 and 1.1 compatible, but at slower transfer speeds)
- SATA 2.5" or 3.5" Hard Drive

Package Includes

- U338-000-SATA USB 3.0 SuperSpeed to SATA III Adapter
- USB 3.0 Micro-B Cable, 2.5 ft.
- External Power Supply with NEMA 1-15P Plug (Input: 100-240V, 50/60Hz, 0.8A; Output: 12V, 2A)



Powering Business Worldwide



AC Adapter	Input: 100-240V, 50/60Hz, 0.8A; Output: 12V, 2A
CONNECTIONS	
Side A - Connector 1	USB 3.0 A (MALE)
Side B - Connector 1	22 PIN SATA + POWER (FEMALE)
PHYSICAL	
Color	Black
Shipping Dimensions (hwd / in.)	3.00 x 3.20 x 5.00
Shipping Dimensions (hwd / cm)	7.62 x 8.13 x 12.70
Shipping Weight (lbs.)	0.56
Shipping Weight (kg)	0.25
ENVIRONMENTAL	
Operating Temperature Range	-4° to 140°F (-20° to 60°C)
Storage Temperature Range	-4° to 158°F (-20° to 70°C)
STANDARDS & COMPLIANCE	
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	3-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.