

USB 3.0 SuperSpeed to VGA Adapter, 512MB SDRAM - 2048x1152,1080p

MODEL NUMBER: U344-001-VGA



Description

Tripp Lite's U344-001-VGA USB 3.0 to VGA Multi Monitor External Video Adapter allows you to connect an additional monitor or projector to a computer/laptop's USB 3.0 port. Up to six adapters can be used simultaneously, allowing the user to connect up to six additional monitors to a single computer. Once the installation is done, the computer screen appears on the add-on monitor(s) without the hassle of function keys to swap to a second monitor. Supports video resolutions up to 2048 x 1152 (60Hz), 1080p (60Hz). Windows and Intel Mac compatible.

Features

- Add an additional VGA monitor through a single USB 3.0 port
- Use up to six adapters simultaneously, adding up to six additional monitors to a single computer
- View large spreadsheets across multiple screens by extending video amongst all monitors
- Play video on one monitor while working on another
- Do multiple screen presentations from a laptop computer
- Bus powered...no external power adapter needed
- Features 512MB DDR2 SDRAM of memory
- Supports video resolutions up to 2048 x 1152 (60Hz), 1080p (60Hz)
- Compatible with Windows 7 and later. Supports both 32- and 64-bit.
- Supports Surface tablets running non-RT Windows 8 and 8.1
- Compatible with Intel Mac OS X 10.8.5 and later. Supports both 32- and 64-bit.
- Uses DisplayLink DL3100 chipset

Specifications

OVERVIEW	
UPC Code	037332186355

Highlights

- Add an additional VGA monitor through a single USB 3.0 port
- Up to six adapters can be added to one computer
- Features 512MB DDR2 SDRAM of memory
- Supports video resolutions up to 2048 x 1152 (60Hz), 1080p (60Hz)
- Windows and Intel Mac compatible
- Compatible with Ubuntu 14.04.2

System Requirements

- Compatible with Windows 7 and later. Supports both 32- and 64-bit.
- Supports Surface tablets running non-RT Windows 8 and 8.1
- Compatible with Intel Mac OS X 10.8.5 and later. Supports both 32- and 64-bit.
- Reference the owner's manual for system requirements when using multiple adapters or when using the add-on monitor for DVD playback.

Package Includes

- (1) U344-001-VGA USB 3.0 to VGA Adapter
- (1) Driver CD
- (1) Owner's Manual

Technology	VGA/SVGA
VIDEO	
Max Supported Video Resolution	2048 x 1152 (1080p) @ 60Hz
INPUT	
Bus Powered	Yes
Product Length (in.)	8
POWER	
Power Consumption (Watts)	1.3
PHYSICAL	
Color	Black
Material of Construction	PVC, ABS
Cable Jacket Rating	VW-1
Shipping Dimensions (hwd / in.)	5.20 x 5.20 x 0.91
Shipping Weight (lbs.)	0.12
Unit Dimensions (hwd / in.)	0.000 x 0.000 x 0.000
Unit Packaging Type	Box
Unit Weight (lbs.)	0.06
Unit Weight (kg)	0.03
ENVIRONMENTAL	
Operating Temperature Range	32 to 104 F (0 to 40 C)
Storage Temperature Range	-4 to 140 F (-20 to 60 C)
Relative Humidity	10% to 90 % RH, Non-Condensing
BTUs	4.4 BTU/Hr
CONNECTIONS	
Side A - Connector 1	USB 3.0 A (MALE)
Side B - Connector 1	HD15 (FEMALE)
Connector Plating	Nickel
FEATURES & SPECIFICATIONS	
USB Specification	USB 3.0 (up to 5 Gbps); USB 3.1 Gen 1 (up to 5 Gbps)
Driver Required	Yes

STANDARDS & COMPLIANCE	
Product Compliance	RoHS; CE (Europe); REACH; FCC (USA)
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	3-year limited warranty