

USB 3.0 SuperSpeed 2 Bay SATA Hard Drive RAID Enclosure w Fan for 3.5" and 2.5" drives

MODEL NUMBER: U357-002



Create inexpensive external mass storage for Music, Videos, Photos

Description

Tripp Lite's U357-002, USB3.0 Dual-Bay External RAID enclosure, allows you to quickly turn any two 2.5" or 3.5" internal SATA hard drives into external hard drives. Compatible with SATA I, II, and III hard drives, and tested to support up to 4TB 3.5" HDD per bay (8TB total), and up to 1TB 2.5" HDD per bay (2TB total). Creates massive amounts of inexpensive external storage for large files, such as Videos, Music, Photos, and more. When used with computers supporting USB3.0, can achieve transfer speeds of up to 5Gbps. Backward compatible with USB 2.0 computers as well (480mbps). Features RAID 0, RAID 1, JBOD, and Normal disk modes, giving you the flexibility to access your data in whatever way works best for you. Built in cooling fan keeps drives cool during prolonged use. Unit is Plug-and-Play...no drivers or software required.

Features

- Dual Bay supports two 2.5" or 3.5" SATA I, II, or III drives
- Up to 8TB with 2 x 4TB 3.5" drives, or 2TB with 2 x 2.5" drives
- RAID 0, RAID 1, JBOD, or Normal modes available
- Supports USB 3.0 5Gbps transfer rates (backward compatible with USB 2.0 and 1.1)
- Built-in cooling fan keeps drives cool
- Plug-and-Play...no Drivers or Software required
- Compatible with Windows (up to 10), MAC, and Linux

Specifications

OVERVIEW	
UPC Code	037332181619
AC Adapter	Input: 100-240V, 50/60Hz, 1.2A; Output: 12V, 4A
Drives Supported	2

Highlights

- Dual Bay External RAID for SATA 3.5" and 2.5" drives (not included)
- 5Gbps transfer speed with USB3.0 enabled computer
- Windows (up to 10), MAC, Linux compatible

System Requirements

- (x2) 2.5" or 3.5" SATA HARD Drives
- Computer with available USB port, with USB3.0 port required to achieve maximum transfer rate

Package Includes

- U357-002 Enclosure
- USB 3.0 A/B Device Cable, 4ft
- External Power Supply with NEMA 1-15P Plug and removable power cord (Input: 100-240V, 50/60Hz, 1.2A; Output: 12V, 4A)
- Screws for mounting 2.5" hard drives
- Owners Manual



Accessories Type	Hard Drive Enclosure
Technology	SATA/eSATA
PHYSICAL	
Color	Black
Shipping Dimensions (hwd / cm)	19.00 x 27.30 x 19.51
Shipping Dimensions (hwd / in.)	7.48 x 10.75 x 7.68
Shipping Weight (kg)	2.25
Shipping Weight (lbs.)	4.96
Unit Dimensions (hwd / in.)	4.80 x 5.30 x 8.90
Unit Dimensions (hwd / cm)	12.192 x 13.462 x 22.61
Unit Weight (lbs.)	3.50
Unit Weight (kg)	1.59
CONNECTIONS	
Side A - Connector 1	USB 3.0 A (MALE)
Side B - Connector 1	(2) 22 PIN SATA + POWER (FEMALE)
WARRANTY	
Product Warranty Period (Worldwide)	3-year limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>