

2 Bay RAID Enclosure, SuperSpeed USB 5Gbps, Fan Cooled, For 3.5" and 2.5" drives

MODEL NUMBER: U357-002



Create inexpensive external mass storage for music, videos, photos

Description

This double-bay RAID enclosure with USB 3.0 support lets you quickly turn any two 2.5-inch or 3.5-inch internal SATA hard drives into external hard drives. Compatible with SATA I, II, and III hard drives and tested to support up to 4TB 3.5-inch HDD per bay (8TB total) and up to 1TB 2.5-inch HDD per bay (2TB total). This high-performance hard drive enclosure creates massive amounts of inexpensive external storage for large files, such as videos, music and photos. When used with computers supporting USB 3.0, it can achieve transfer speeds of up to 5 Gbps. Backward compatible with USB 2.0 computers as well (480 Mbps), it features RAID 0, RAID 1, JBOD and Normal disk modes, giving you the flexibility to access your data in whatever way works best for you. A built-in cooling fan keeps drives cool during prolonged use. The unit is plug-and-play with no drivers or other software required.

Features

- 2-bay HDD enclosure supports two 2.5" or 3.5" SATA I, II, or III drives
- Up to 8TB with 2 x 4TB 3.5" drives, or 2TB with 2 x 2.5" drives
- RAID 0, RAID 1, JBOD, or Normal modes available
- Supports SuperSpeed USB 5Gbps transfer rates (backward compatible with USB 2.0 and 1.1)
- Built-in cooling fan keeps drives cool
- Plug-and-Play... no Drivers or Software required
- Compatible with Windows (up to 10), MAC, and Linux

Specifications

OVERVIEW	
UPC Code	037332181619
Drives Supported	2
Accessory Type	Hard Drive Enclosure
Technology	SATA/eSATA

Highlights

- 2 Bay External RAID enclosure for SATA 3.5" and 2.5" drives
- 5Gbps transfer speed with USB 3.2 Gen 1 enabled computer
- Windows, MAC, Linux compatible

System Requirements

- (x2) 2.5" or 3.5" SATA Hard Drives
- Computer with USB 3.2 Gen 1 port required to achieve maximum transfer rate

Package Includes

- U357-002 Enclosure
- USB 3.0 A/B Device Cable, 4-ft
- External Power Supply with NEMA 1-15P Plug and removable power cord (Input: 100-240V, 50/60Hz, 1.2A; Output: 12V, 4A)
- Screws for mounting 2.5" hard drives
- Owners Manual



Powering Business Worldwide



POWER	
AC Adapter	Input: 100-240V, 50/60Hz, 1.2A; Output: 12V, 4A
CONNECTIONS	
Side A - Connector 1	USB 3.0 A (MALE)
Side B - Connector 1	(2) 22 PIN SATA + POWER (FEMALE)
PHYSICAL	
Color	Black
Shipping Dimensions (hwd / in.)	7.67 x 10.74 x 7.48
Shipping Dimensions (hwd / cm)	19.48 x 27.28 x 19.00
Shipping Weight (lbs.)	4.96
Shipping Weight (kg)	2.25
Unit Dimensions (hwd / in.)	4.500 x 8.900 x 5.300
Unit Dimensions (hwd / cm)	12.192 x 22.61 x 13.46
Unit Weight (lbs.)	3.50
Unit Weight (kg)	1.59
STANDARDS & COMPLIANCE	
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	3-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.