



USB 3.0 SuperSpeed External 2.5" SatA III Hard Drive Enclosure with Built-in Cable

MODEL NUMBER: U357-025-R







Description

Tripp Lite's U357-025-R is an inexpensive way to create an external USB storage drive for laptop / notebook / netbook users. Simply insert a SATA 2.5" hard drive (not supplied) into the enclosure and plug the built-in USB 3.0 cable into a computer or hub's USB port. The unit is Plug-n-Play so there's no software to load. At only 4.9"L x 3.5"W x 0.63"H, the U357-025-R travels easily and is great for storing large files like photos, music, movies, etc. Compatible with Windows, Mac, and Linux. Supports USB 3.0 data transfer rates up to 5Gbps, provided the USB source is USB 3.0.

Features

- USB 3.0 transfer rates up to 5Gbps, 10X faster than USB 2.0
- Create a portable, high volume storage device for Laptop / Netbook
- Built-in USB cable for quick attachment to your computer
- SATA I, II, and III compliant
- Backwards compatible with USB 2.0
- Plug-and-Play, no software required
- No power supply required
- Power / Activity LED Lights

Specifications

OVERVIEW	
UPC Code	037332161161
Drives Supported	2.5" SATA
Technology	SATA/eSATA

Highlights

- Supports data transfer rates up to 5Gbps
- Lightweight, compact design, ideal for portable storage
- Windows, Mac, and Linux compatible, Plug and Play
- Accepts most Manufacturers 2.5" SATA Hard Drives (see "Features" tab, "System Requirements")

System Requirements

- Available USB 3.0 "A" (or USB 2.0 / 1.1) Computer or Hub port
- Compatible with Windows, Mac, and Linux
- 2.5" SATA hard drive must be able to operate on the power provided by the USB port (USB 3.0 provides up to 900mA, USB 2.0 up to 500mA)
- 2.5" SATA hard drive with a maximum height of 9.5mm.

Package Includes

- U357-025-R External Enclosure (no hard drive supplied)
- USB 3.0 Cable
- User Manual





INPUT		
Input Plug Type	USB A (Male)	
CONNECTIONS		
Side A - Connector 1	USB 3.0 A (MALE)	
Side B - Connector 1	22 PIN SATA + POWER (FEMALE)	
PHYSICAL		
Color	Black	
Material of Construction	ABS	
Housing Color	Black	
Shipping Dimensions (hwd / in.)	6.30 x 4.80 x 1.20	
Shipping Dimensions (hwd / cm)	16.00 x 12.19 x 3.05	
Shipping Weight (lbs.)	0.33	
Shipping Weight (kg)	0.15	
Unit Dimensions (hwd / in.)	0.000 × 0.000 × 0.000	
Unit Dimensions (hwd / cm)	1.6 x 8.8 x 12.4	
Unit Weight (lbs.)	0.15	
Unit Weight (kg)	0.07	
WARRANTY & SUPPORT		
Product Warranty Period (Worldwide)	1-year limited warranty	

1000 Eaton Boulevard Cleveland, OH 44122 United States https://tripplite.eaton.com © 2024 Eaton. All Rights Reserved. Eaton is a registered trademark. All other trademarks are the property of their respective owners.