

USB 3.0 SuperSpeed External 2.5 in. SATA Hard Drive Enclosure with Built-In Cable and UASP Support

MODEL NUMBER: **U357-025-UASP**



Connects a 2.5 in. SATA hard disk drive or solid state drive to your laptop, netbook or notebook computer's USB port for extra storage and fast data transfer. UASP enabled for 70% more speed with UASP host controller.

Description

The U357-025-UASP USB 3.0 SuperSpeed External 2.5 in. SATA Hard Drive Enclosure is a quick, easy way to connect a SATA HDD (Hard Disk Drive) or SSD (Solid State Drive) to your laptop, netbook or notebook's USB port. Not only does it support USB 3.0 data transfer rates up to 5 Gbps, but its UASP (USB Attached SCSI Protocol) feature reduces latency and allows it to perform up to 70% faster when connected to a UASP-enabled host controller.

Perfect for storing and sharing large files like photos, music and video files, the enclosure is compatible with 2.5-inch SATA drives up to 3 TB. Just insert the drive into the SATA connector, connect the included one-foot USB 3.0 Micro-B cable to your computer, and slide the protective cover over the drive, even when it's in use, to keep it dust-free at all times.

The U357-025-UASP accepts SATA III (6 Gbps), SATA II (3 Gbps) and SATA I (1.5 Gbps) drives, as well as USB 2.0 (480 Mbps) and USB 1.1 (12 Mbps) transfer speeds. A blue LED flashes to indicate data transfer is occurring. After thirty minutes of inactivity, the enclosure goes into hibernation mode and wakes up when activity resumes. No software, drivers or external power supply is required. Compatible with Windows, Mac and Linux.

Features

Quickly Connects a SATA Drive to Your Computer's USB Port

- Ideal for storing large files like photos, music and video files and sharing them on your laptop, netbook or notebook

Highlights

- Supports USB 3.0 data transfer rates up to 5 Gbps
- Works up to 70% faster when connected to UASP host controller
- Compatible with 2.5 in. SATA HDDs and SSDs up to 3 TB
- Protective cover keeps SATA drive free of dust
- Requires no software, drivers or external power supply

System Requirements

- Device with USB port (USB 3.0 required for USB 3.0 speeds)
- UASP-enabled host controller required for UASP performance
- 2.5 in. SATA HDD or SSD with 9.5 mm maximum height

Package Includes

- U357-025-UASP USB 3.0 SuperSpeed External 2.5 in. SATA Hard Drive Enclosure
- USB 3.0 Micro-B cable, 1 ft.
- Owner's manual



- Supports USB 3.0 data transfer rates up to 5 Gbps
- Features UASP (USB Attached SCSI Protocol) for performance up to 70% faster when connected to UASP-enabled host controller
- Hibernates after 30 minutes of inactivity
- Compatible with Windows, Mac and Linux

Compatible with 2.5 in. SATA Drives Up to 3 TB

- Accepts SATA III (6 Gbps), SATA II (3 Gbps) and SATA I (1.5 Gbps) drives
- Backward compatible with USB 2.0 (480 Mbps) and USB 1.1 (12 Mbps) transfer speeds
- Works with both HDDs (Hard Disk Drives) and SSDs (Solid State Drives)

Easy to Use Right from the Box

- Plug and play—no software, drivers or external power supply needed
- SATA drive slides easily into convenient slot
- Protective cover keeps dust and dirt away from sensitive SATA drives
- Blue LED indicates successful data transfer
- 1 ft. USB 3.0 Micro-B cable included

Specifications

OVERVIEW	
UPC Code	037332190000
Drives Supported	2.5" HDD and SSD
Technology	USB 3.0 (SuperSpeed); SATA/eSATA; USB
INPUT	
Bus Powered	Yes
USER INTERFACE, ALERTS & CONTROLS	
LED Indicators	Blue (Read, Write, Power)
PHYSICAL	
Color	Black
Cable Length (ft.)	0.2
Cable Length (m)	0.06
Material of Construction	ABS
Shipping Dimensions (hwd / cm)	4.80 x 18.11 x 12.80
Shipping Dimensions (hwd / in.)	1.89 x 7.13 x 5.04



Shipping Weight (kg)	0.18
Shipping Weight (lbs.)	0.40
Unit Dimensions (hwd / cm)	1.5 x 12.1 x 7.8
Unit Dimensions (hwd / in.)	0.57 x 4.8 x 3.1
Unit Packaging Type	Box
Unit Weight (kg)	0.05
Unit Weight (lbs.)	0.11
ENVIRONMENTAL	
Operating Temperature Range	50 to 122 F (10 to 50 C)
Storage Temperature Range	32 to 149 F (0 to 65 C)
Relative Humidity	10% to 80% RH, Non-Condensing
BTUs	17.1 BTU/Hr
Power Consumption (Watts)	5
CONNECTIONS	
Ports	1
Side A - Connector 1	USB 3.0 A (MALE)
Side B - Connector 1	22 PIN SATA + POWER (FEMALE)
Connector Plating	Nickel
FEATURES & SPECIFICATIONS	
USB Specification	USB 3.0 (up to 5 Gbps); USB 3.1 Gen 1 (up to 5 Gbps)
Driver Required	No
UASP Support	Yes
STANDARDS & COMPLIANCE	
Certifications	CE, FCC, RoHS, REACH
WARRANTY	
Product Warranty Period (Worldwide)	3-year limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>