

## 4-Port USB 3.0 SuperSpeed Hub for Data and USB Charging - USB-A, BC 1.2, 2.4A

MODEL NUMBER: U360-004-2F



Adds 4 new USB 3.0 ports to your computer, laptop, MacBook or Chromebook for connecting hard drives, smartphones and other USB devices.

### Features

**USB 3.0 Hub/Charger Adds up to 4 USB Devices to Your Computer, MacBook or Chromebook** This four-port USB 3.0 hub connects directly to the USB-A port on your computer, laptop, MacBook, Ultrabook or Chromebook using the included cable. It allows you to use as many as four USB devices, such as flash drives, external hard drives, printers, barcode scanners and digital cameras, at the same time. Each USB port supports Battery Charging v1.2 (BC 1.2) standards for faster charging of mobile devices, including Apple and Android smartphones and tablets.

**Supports SuperSpeed USB 3.0 to Ensure Fast Data Transfers** The hub supports USB 3.0 SuperSpeed data transfer rates up to 5 Gbps, which is 10 times faster than USB 2.0. It is especially recommended for high-bandwidth USB 3.0 devices, such as security cameras and high-resolution webcams. The bus-powered hub distributes 900mA to its four ports. When using the included external power supply to draw additional power, the hub can provide up to 1.5A for fast charging of mobile devices. All four ports support BC 1.2 and 2.4A Quick Charge for Apple devices, up to a maximum of 3.5A total at any one time.

**Plug-and-Play Hub Comes Ready to Connect Right Away** The U360-004-2F works with all major operating systems and requires no software to download and install. It's backward compatible with previous USB versions, so you can also continue using older peripherals while getting maximum performance from current devices. Overcurrent and overvoltage safeguards protect your connected equipment against damage or data loss due to power surges.

**Sleek and Slim Housing Designed for Everyday Workspace Use or Connecting on the Go** The compact unit is designed for convenient positioning within your reach, making USB ports accessible while not taking up much workspace. It is also slim enough to pack in your pocket, purse or laptop bag for use in a hotel, conference room or airport as both a multiport hub and a USB charger.

## Specifications

### OVERVIEW

### Highlights

- Adds a printer, scanner, hard drive, webcam—up to 4 USB devices—to your computer
- Supports USB 3.0 SuperSpeed rates up to 5 Gbps to ensure fast data transfers
- BC 1.2-compliant USB-A ports provide up to 3.5A total for charging mobile devices
- Compact hub fits easily in your purse, backpack or laptop bag for connecting on the go
- Plug-and-play operation with no software required for easy, immediate installation

### Applications

- Connect up to 4 USB devices to your PC, laptop, MacBook, Ultrabook or Chromebook's USB-A port
- Add easy-to-access USB ports to desktop computers that are in a cabinet, behind furniture or otherwise hard to reach
- Charge your smartphone or tablet
- Pack it in your laptop bag for quick connection of peripherals at a remote workspace or conference

### System Requirements

- Compatible with all USB-enabled operating systems (USB 3.0 port needed to achieve USB 3.0 speeds)

### Package Includes

- U360-004-2F 4-Port USB 3.0 SuperSpeed Hub
- USB-A to USB-B 3.0 cable, 4 ft.
- External power supply with 5 ft. cord (Input: 100–240V, 50/60 Hz, 0.6A; Output: 12V 2A)

UPC Code	037332217912
Product Type	Hub
Technology	USB 3.x
Host Connector	USB A (MALE)
<b>VIDEO</b>	
Number of Monitors Supported	0
<b>DATA</b>	
Data Ports	(4) USB A (FEMALE)
Data Ports Details	(4) USB-A - USB 3.2 Gen 1 (5 Gbps)
<b>INPUT</b>	
Voltage Compatibility (VAC)	100; 110; 120; 125; 127; 200; 208; 220; 230; 240
Bus Powered	Yes
Product Length (in.)	3.622
Product Length (cm.)	9.2
Product Length (ft.)	0.301
Product Length (m.)	0.092
<b>POWER</b>	
Power Source Type	AC Adapter
External Power Supply Plug(s)	NEMA 1-15P North America
External Power Supply Input Specs (V / Hz / A)	100-240V / 50/60Hz / 0.6A
External Power Supply Output Specs (V / A)	12V / 2A
External Power Supply Cord Length (ft.)	5
External Power Supply Cord Length (m.)	1.5
AC Adapter	Input: 100-240V, 50/60Hz, 0.6A; Output: 12V, 2A
DC Barrel Plug	OD: 5.5 x 2.5 x 10mm, Positive Pin, Negative Sleeve
USB Power Delivery (PD) Charging Support	Yes
<b>USER INTERFACE, ALERTS &amp; CONTROLS</b>	
LED Indicators	Blue (Power)
<b>CHARGING</b>	

Charging Ports Details	All four ports up to a maximum of 3.5A total at any one time.
Charging Ports	(4) USB-A: 5V 1.5A (7.5W); 2.4A Quick Charge
Charging Ports / Amps	(4) 1.5A
<b>PHYSICAL</b>	
Color	Black
Material of Construction	ABS, PBT
Unit Dimensions (hwd / in.)	0.850 x 3.620 x 2.010
Unit Packaging Type	Box
Unit Weight (lbs.)	0.7716
Unit Weight (kg)	0.35
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	32 to 104 F (0 to 40 C)
Storage Temperature Range	32 to 149 F (0 to 65 C)
Relative Humidity	20% to 80% RH, Non-Condensing
Power Provided to Connected Device(s)	0.9A (Bus-Powered), 1.5A (connected to external PSU)
<b>CONNECTIONS</b>	
Number of Ports	4
Side A - Connector 1	USB B (FEMALE)
Side B - Connector 1	(4) USB A (FEMALE)
Connector Plating	Nickel
<b>FEATURES &amp; SPECIFICATIONS</b>	
USB Hub Ports	Yes
USB Specification	USB 3.0 (up to 5 Gbps); USB 3.1 Gen 1 (up to 5 Gbps)
Driver Required	No
<b>STANDARDS &amp; COMPLIANCE</b>	
External Power Supply Certifications	FCC; UL
Product Compliance	RoHS; REACH; WEEE; FCC (USA)
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	3-year limited warranty



1000 Eaton Boulevard  
Cleveland, OH 44122  
United States



© 2023 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.