

## 4-Port Portable USB 3.0 SuperSpeed Hub

MODEL NUMBER: **U360-004-MINI**



Connect up to four USB devices via a single USB 3.0 port on your desktop, laptop, or tablet

### Description

Tripp Lite U360-004-MINI is a compact, 4-Port USB 3.0 SuperSpeed hub, with built-in cable, that provides up to 5Gbps transfer rates in a compact, portable format ( Computer and devices must be both USB3.0 rated to achieve maximum 5Gbps speeds ). Hub is backward compatible to USB 2.0 and 1.1, so that older USB devices can be attached ( devices will run at their native speeds of 480Mbps and 12Mbps respectively ).

Small, portable design allows the hub to travel easily, and built-in cable eliminates the need to carry a separate cable for attachment to laptops and tablets. Needed power comes from the attached computer... no need for external power adapter. Plug-n-Play...no drivers or software required. Works with all Windows and MAC operating systems.

### Features

- Add 4 additional USB 3.0 ports to your PC, Laptop, or Tablet
- Compact design...4in long by 1.25in wide by .75in high
- Built-in 1-ft. attachment cable
- USB 3.0 SuperSpeed 5gbps
- Plug-n-Play...no drivers or software to load
- Bus powered...separate power supplied not needed
- Compatible with all Windows and MAC OS
- Backward compatible with Hi-Speed ( 480Mbps ), Full Speed ( 12Mbps ), and Low Speed ( 1.5Mbps )  
USB versions

## Specifications

### Highlights

- Portable design with built-in 1-ft. cable
- USB data transfer rates up to 5Gbps
- Plug and Play

### System Requirements

- Desktop, Laptop or Tablet with USB 3.0 USB port
- USB 3.0 ( or less ) Peripherals

### Package Includes

- Portable USB 3.0 SuperSpeed Hub - 4-Port



<b>OVERVIEW</b>	
UPC Code	037332184726
Product Type	Hub
Host Connector	USB A (MALE)
<b>VIDEO</b>	
Extended Mode	No
Mirror Mode	No
Number of Monitors Supported	0
<b>DATA</b>	
Data Ports	(4) USB A (FEMALE)
Data Ports Detail	(4) USB-A - USB 3.2 Gen 1 (5 Gbps)
<b>INPUT</b>	
Bus Powered	Yes
Product Length (in.)	16.8
Product Length (cm.)	42.67
Product Length (ft.)	1.4
Product Length (m.)	0.426
<b>PHYSICAL</b>	
Cable Jacket Rating	VW-1
Color	Black; Silver
Included Mounting Accessories	No
Material of Construction	Plastic
Shipping Dimensions (hwd / cm)	13.97 x 9.91 x 3.05
Shipping Dimensions (hwd / in.)	5.50 x 3.90 x 1.20
Shipping Weight (kg)	0.11
Shipping Weight (lbs.)	0.24
Unit Dimensions (hwd / in.)	0.8 x 4.3 x 1.3
Unit Packaging Type	Box
Unit Weight (kg)	0.06
Unit Weight (lbs.)	0.13
<b>ENVIRONMENTAL</b>	



Operating Temperature Range	-4 to 158 F (-20 to 70 C)
Storage Temperature Range	-4 to 185 F (-20 to 85 C)
Relative Humidity	20% to 80% RH, Non-Condensing
BTUs	2.6 BTU/Hr
Power Consumption (Watts)	0.77
Power Provided to Connected Device(s)	5V 0.9A (4.5W) Output per USB port
<b>CONNECTIONS</b>	
Ports	4
Side A - Connector 1	USB 3.0 A (MALE)
Side B - Connector 1	(4) USB 3.0 A (FEMALE)
Connector Plating	Nickel
<b>FEATURES &amp; SPECIFICATIONS</b>	
USB Specification	USB 3.0 (up to 5 Gbps); USB 3.1 Gen 1 (up to 5 Gbps)
Driver Required	No
Technology	USB 3.0 (SuperSpeed); USB
<b>STANDARDS &amp; COMPLIANCE</b>	
Certifications	CE, FCC, RoHS, REACH
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	3-year limited warranty

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>