

4-Port USB 3.x (5Gbps) Hub

MODEL NUMBER: U360-004-R



Description

The U360-004-R USB 3.0 SuperSpeed 4-port hub carries your data from a USB 3.0 enabled computer at a blazing 5 Gbps transfer rate. Connect to a variety of USB enabled devices such as USB external hard drives, cameras, printers and more. Backward compatible to previous USB generations. Bus powered for use with devices that require minimal power. For more power-hungry devices, an external power supply is included. Sleek, compact design is perfect for USB port expansion.

Features

- USB 3.0 SuperSpeed compatible
- 5Gbps Transfer Speed - 10X as fast as USB 2.0
- Supports USB Battery Charging (BC) specification v1.2
- On bus-power, 900mA from the USB 3.0 computer port is shared between all four ports
- The included external power supply provides 2A of power, allowing each port to provide up to 1.5A of charging power to mobile devices.
- Plug-and-Play - No Drivers Required
- 1 Upstream and 4 Downstream USB ports

Highlights

- USB 3.0 SuperSpeed Compatible
- 5Gbps Transfer Speed - 10X as fast as USB 2.0
- All 4 ports are USB Battery Charging (BC) 1.2-compliant, providing up to 1.5A for charging mobile devices
- External power supply included for use with more power hungry devices

NOTEIf your hub features white housing, see the FAQ tab on this page.

System Requirements

Windows, MAC, or Linux computer with an available USB 3.0 port

Package Includes

- USB 3.0 SuperSpeed 4-Port Hub
- External Power Supply with NEMA 1-15P Plug (Input: 100-240V, 50/60Hz, 0.5A; Output: 5V, 2A)
- USB 3.0 Cable, 3-ft.
- User manual

Specifications

OVERVIEW	
UPC Code	037332161154
Product Type	Hub
Technology	USB 3.x
Host Connector	USB A (MALE)
DATA	
Data Ports	(4) USB A (FEMALE)

Data Ports Details	(4) USB-A - USB 3.2 Gen 1 (5 Gbps)
INPUT	
AC Power Adapter Plug(s)	NEMA 1-15P North America
AC Power Adapter Input Specs (V / Hz / A)	100-240V / 50/60Hz / 0.35A
AC Power Adapter Output Specs (V / A)	5V / 2A
AC Power Adapter Cord Length (ft.)	5
AC Power Adapter Cord Length (m)	1.5
Voltage Compatibility (VAC)	100; 110; 120; 125; 127; 200; 208; 220; 230; 240
Bus Powered	No
POWER	
Power Source Type	AC Adapter
AC Adapter	Input: 100-240V, 50/60Hz, 0.35A; Output: 5V, 2A
DC Barrel Plug	OD: 3.5 x 1.35 x 10mm, Positive Pin, Negative Sleeve
Power Consumption (Watts)	0.7
Output Power Capacity (Amps)	1.50
CONNECTIONS	
Number of Ports	4
Side A - Connector 1	USB 3.0 A (MALE)
Side B - Connector 1	(4) USB 3.0 A (FEMALE)
Connector Plating	Nickel
USER INTERFACE, ALERTS & CONTROLS	
LED Indicators	Blue (Power)
CHARGING	
Charging Ports	(4) USB-A: 5V 1.5A (7.5W)
Charging Ports Details	Any of the 4 ports
Charging Amps per Port	1.5
PHYSICAL	
Color	Black
Material of Construction	ABS
Shipping Dimensions (hwd / in.)	5.35 x 2.87 x 4.72
Shipping Dimensions (hwd / cm)	13.59 x 7.29 x 11.99



Powering Business Worldwide



Shipping Weight (lbs.)	0.61
Shipping Weight (kg)	0.28
Unit Dimensions (hwd / in.)	1.000 x 4.000 x 2.500
Unit Packaging Type	Box
Unit Weight (lbs.)	0.13
Unit Weight (kg)	0.06
ENVIRONMENTAL	
Operating Temperature Range	-4° to 158°F (-20° to 70°C)
Storage Temperature Range	-4° to 185°F (-20° to 85°C)
Relative Humidity	20% to 80% RH, Non-Condensing
BTUs	2.4 BTU/Hr
Power Provided to Connected Device(s)	5V 0.9A (4.5W) Output per USB Port
FEATURES & SPECIFICATIONS	
USB Hub Ports	Yes
Number of USB Hub Ports	4
USB Specification	USB 3.0 (up to 5 Gbps); USB 3.1 Gen 1 (up to 5 Gbps); USB 3.2 Gen 1 (up to 5 Gbps)
Driver Required	No
STANDARDS & COMPLIANCE	
TAA Compliant Option	N
External Power Supply Certifications	FCC; UL; cUL; RoHS
Product Compliance	RoHS; CE (Europe); REACH; FCC (USA)
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	3-year limited warranty

1000 Eaton Boulevard
 Cleveland, OH 44122
 United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
 Eaton is a registered trademark. All other trademarks
 are the property of their respective owners.