

## 4-Port USB 3.0 SuperSpeed Hub

MODEL NUMBER: **U360-004-R**



### Description

Tripp Lites U360-004-R USB 3.0 SuperSpeed 4-port hub carries your data from a USB3.0 enabled computer at a blazing 5Gbps transfer rate. Connect to a variety of USB enabled devices such as USB external hard drives, cameras, printers and more. Backward compatible to previous USB generations. Bus powered for use with devices that require minimal power. For more power hungry devices, an external power supply is included. Sleek, compact design is perfect for USB port expansion.

### Features

- USB 3.0 SuperSpeed compatible
- 5Gbps Transfer Speed - 10X as fast as USB 2.0
- Supports USB Battery Charging (BC) specification v1.2
- On bus-power, 900mA from the USB 3.0 computer port is shared between all four ports
- The included external power supply provides 2A of power, allowing each port to provide up to 1.5A of charging power to mobile devices.
- Plug-and-Play - No Drivers Required
- 1 Upstream and 4 Downstream USB ports

## Specifications

OVERVIEW	
UPC Code	037332161154
Product Type	Hub
AC Adapter	Input: 100-240V, 50/60Hz, 0.35A; Output: 5V, 2A
Technology	USB
Host Connector	USB A (MALE)
VIDEO	

### Highlights

- USB 3.0 SuperSpeed Compatible
- 5Gbps Transfer Speed - 10X as fast as USB 2.0
- All 4 ports are USB Battery Charging (BC) 1.2-compliant, providing up to 1.5A for charging mobile devices
- External power supply included for use with more power hungry devices

\*\*\*NOTE\*\*\*If your hub features white housing, see the FAQ tab on this page.

### System Requirements

Windows, MAC, or Linux computer with an available USB 3.0 port

### Package Includes

- USB 3.0 SuperSpeed 4-Port Hub
- External Power Supply with NEMA 1-15P Plug (Input: 100-240V, 50/60Hz, 0.5A; Output: 5V, 2A)
- USB 3.0 Cable, 3-ft.
- User manual



Number of Monitors Supported	0
Extended Mode	No
Mirror Mode	No
<b>DATA</b>	
Data Ports	(4) USB A (FEMALE)
Data Ports Details	(4) USB-A - USB 3.2 Gen 1 (5 Gbps)
<b>INPUT</b>	
Voltage Compatibility (VAC)	100; 110; 120; 125; 127; 200; 208; 220; 230; 240
External Power Supply Plug(s)	NEMA 1-15P North America
Bus Powered	No
<b>POWER</b>	
External Power Supply Input Specs (V / Hz / A)	100-240V / 50/60Hz / 0.35A
External Power Supply Output Specs (V / A)	5V / 2A
External Power Supply Cord Length (ft.)	5
External Power Supply Cord Length (m.)	1.5
DC Barrel Plug	OD: 3.5 x 1.35 x 10mm, Positive Pin, Negative Sleeve
External Power Supply Certifications	FCC; UL; cUL; RoHS
<b>USER INTERFACE, ALERTS &amp; CONTROLS</b>	
LED Indicators	Blue (Power)
<b>CHARGING</b>	
Charging Ports Details	Any of the 4 ports
Charging Ports	(4) USB-A: 5V 1.5A (7.5W)
<b>PHYSICAL</b>	
Color	Black
Material of Construction	ABS
Shipping Dimensions (hwd / cm)	13.59 x 7.29 x 11.99
Shipping Dimensions (hwd / in.)	5.35 x 2.87 x 4.72
Shipping Weight (kg)	0.28
Shipping Weight (lbs.)	0.61
Unit Packaging Type	Box



Unit Weight (lbs.)	0.13
Unit Weight (kg)	0.06
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	-4 to 158 F (-20 to 70 C)
Storage Temperature Range	-4 to 185 F (-20 to 85 C)
Relative Humidity	20% to 80% RH, Non-Condensing
BTUs	2.4 BTU/Hr
Power Consumption (Watts)	0.7
Power Provided to Connected Device(s)	5V 0.9A (4.5W) Output per USB Port
<b>CONNECTIONS</b>	
Ports	4
Side A - Connector 1	USB 3.0 A (MALE)
Side B - Connector 1	(4) USB 3.0 A (FEMALE)
Connector Plating	Nickel
<b>FEATURES &amp; SPECIFICATIONS</b>	
USB Specification	USB 3.0 (up to 5 Gbps); USB 3.1 Gen 1 (up to 5 Gbps)
Driver Required	No
<b>STANDARDS &amp; COMPLIANCE</b>	
Certifications	CE, FCC, RoHS, REACH
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	3-year limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>