

7-Port USB-C Hub - USB 3.2 Gen 1 and USB 3.2 Gen 2, 5 USB-A and 2 USB-C Ports, Gray

MODEL NUMBER: U360-007-5A2C



Portable hub adds 7 USB ports to your PC, MacBook or Chromebook for connecting hard drives, webcams and other USB devices.

Features

Powered USB Hub Connects 7 USB Peripherals to Your Computer, Laptop or Tablet

The U360-007-5A2C adds as many as seven USB devices to your computer, laptop, MacBook, Surface or Chromebook, turning it into a mini workstation. The hub expands the potential of your device by connecting peripherals that can help you do your job faster, easier and better, such as USB headset/microphones, barcode scanners, webcams, keyboards/mice, power meters, portable card readers and external storage drives for uploading and downloading important files.

Supports the Latest USB Devices at Fast USB 3.2 Gen 1 and USB 3.2 Gen 2 Speeds

This compact hub features a variety of USB-A and USB-C ports to fit all your working needs. One USB 2.0 Type-A port connects a mouse or keyboard. Three USB 3.2 Gen 1 (5 Gbps) Type-A ports connect external storage or accessories. One USB 3.2 Gen 2 (10 Gbps) Type-A port and two USB-C ports make it easy to quickly move large files between storage devices. The hub is especially recommended for high-bandwidth USB devices, such as security cameras and high-resolution webcams.

Supports Fast Charging of Connected USB Devices

The USB-A ports each support 5V 1.5A (7.5W) fast charging of connected devices, while the two USB-C ports support 5V 3A (15W) for charging tablets, e-readers or other devices. The USB ports are backward compatible with previous USB generations, so you can continue using older peripherals while getting high-speed performance from new devices.

Ready to Use Right Out of the Package

The plug-and-play U360-007-5A2C connects to your Windows or Mac computer or laptop via the included USB-C host cable. It requires no drivers or other software to download or install. The included power supply comes with international plug adapters that allow you to connect to almost any AC outlet. The slim housing fits easily into a pocket, briefcase or laptop bag, so you can set up your workstation anywhere.

Highlights

- Accepts up to 7 USB peripherals, turning your computer into a mini workstation
- One USB-A and 2 USB-C ports support USB 3.2 Gen 2 speeds up to 10 Gbps
- USB-A ports support 7.5W and USB-C ports support 15W for charging mobile devices
- Slim housing fits easily into backpack or bag for convenient work-from-anywhere use
- Plug-and-play operation with no software required for immediate connection

System Requirements

Compatible with USB-enabled operating systems (USB 3.2 Gen 1/Gen 2 port needed to achieve USB 3.2 Gen 1/Gen 2 speeds)

Package Includes

- U360-007-5A2C 7-Port USB-C Hub
- USB-C host cable with optional USB-A adapter, 3 ft. (0.9 m)
- External power supply (Input: 100–240V, 50/60 Hz, 0.6A; Output: 12V 2A) with 5 ft. (1.5 m) cord
- (4) International plug adapters (North America, U.K., Europe, Australia)
- Installation instructions

Specifications

OVERVIEW	
UPC Code	037332293985



Powering Business Worldwide

TRIPP LITE
SERIES

Product Type	Hub
Technology	USB 2.0 (High Speed); USB 3.x
Host Connector	USB A (MALE); USB C (MALE)
VIDEO	
Number of Monitors Supported	0
Extended Mode	No
Mirror Mode	No
DisplayPort Alt Mode	No
DATA	
Data Ports	(5) USB A (FEMALE); (2) USB C (FEMALE)
Data Ports Details	(1) USB-A - USB 2.0; (3) USB-A - USB 3.2 Gen 1 (5 Gbps); (1) USB-A - USB 3.2 Gen 2 (10 Gbps); (2) USB-C - USB 3.2 Gen 2 (10 Gbps)
INPUT	
AC Power Adapter Plug(s)	AS/NZS 3112 Australia; BS 1363 UK; CEE 7/7 Schuko; NEMA 1-15P North America
AC Power Adapter Input Specs (V / Hz / A)	100-240V, 50/60Hz, 0.6A
AC Power Adapter Output Specs (V / A)	12V, 2A
AC Power Adapter Cord Length (ft.)	5
AC Power Adapter Cord Length (m)	1.5
Voltage Compatibility (VAC)	100; 110; 120; 125; 127; 200; 208; 220; 230; 240
Bus Powered	No
Product Length (in.)	4.65
Product Length (cm.)	15.5
Product Length (ft.)	0.508
Product Length (m)	0.155
POWER	
Power Source Type	AC Adapter
AC Adapter	Input: 100-240V, 50/60Hz, 0.6A; Output: 12V, 2A, 5 ft.
DC Barrel Plug	OD: 5.5 x 2.5 x 10mm, Positive Pin, Negative Sleeve
CONNECTIONS	
Number of Ports	7
Side A - Connector 1	(1) USB C (FEMALE)
Side B - Connector 1	(5) USB A (MALE); (2) USB C (FEMALE)
Connector Plating	Nickel



Powering Business Worldwide

TRIPP LITE
SERIES

USER INTERFACE, ALERTS & CONTROLS	
LED Indicators	White (Connection)
CHARGING	
Number of Charging Ports	7
Total Charging Watts	7.5
Charging Ports	(5) USB-A: 5V 1.5A (7.5W); (1) USB-C: 5V 1.5A (7.5W)
Charging Ports Details	USB-A: BC 1.2 Specification provides 1.5A to connected devices and 2.4A for Apple devices; USB-C: support 5V 1.5A/5V 3A charging protocol
Charging Ports / Amps	3A / 2A / 1.5A
PHYSICAL	
Color	Gray
Material of Construction	ABS
Cable Jacket Color	Black
Cable Jacket Material	PVC
Cable Outer Diameter (OD)	5.0mm
Wire Gauge (AWG)	24/30/32
Total Number of Ports	8
Shipping Dimensions (hwd / in.)	2.36 x 6.30 x 4.72
Shipping Dimensions (hwd / cm)	5.99 x 16.00 x 11.99
Shipping Weight (lbs.)	0.86
Shipping Weight (kg)	0.39
Unit Dimensions (hwd / in.)	0.875 x 5.500 x 2.875
Unit Dimensions (hwd / cm)	11.8 x 4.95 x 0.26
Unit Packaging Type	Box
Unit Weight (lbs.)	0.44
Unit Weight (kg)	0.20
ENVIRONMENTAL	
Operating Temperature Range	32° to 122°F (0° to 50°C)
Storage Temperature Range	68° to 158°F (20° to 70°C)
Relative Humidity	20% to 80% RH, Non-Condensing
BTUs	4.8 BTU/Hr
Operating Humidity Range	10% to 90% RH, Non-Condensing
Storage Humidity Range	0% to 95% RH, Non-Condensing
Power Provided to Connected Device(s)	5V 1.5A/5V 3A



Powering Business Worldwide

TRIPP LITE
SERIES

FEATURES & SPECIFICATIONS	
Over Current Protection	Yes
USB Hub Ports	Yes
Number of USB Hub Ports	7
USB Specification	USB 2.0 (up to 480 Mbps); USB 3.2 Gen 1 (up to 5 Gbps); USB 3.2 Gen 2 (Up to 10 Gbps)
Driver Required	No
STANDARDS & COMPLIANCE	
TAA Compliant Option	N
External Power Supply Certifications	C-Tick; CCC; CE; DOE; GS; TUV; UL; WEEE; cUL
Product Compliance	CE (Europe); EAC (Belarus, Kazakhstan, Russia); FCC (USA); FCC Part 15 Class B (USA); RoHS; UKCA; WEEE
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	3-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.