

7-Port USB 3.x (5Gbps) / USB 2.0 Combo Hub - USB Charging, 2 USB 3.x & 5 USB 2.0 Ports

MODEL NUMBER: U360-007C-2X3



Adds 7 USB ports to your computer, laptop, MacBook or Chromebook for connecting hard drives, tablets, webcams and other USB devices.

Features

USB 3.0/2.0 Hub Adds 7 USB Devices to Your Computer, MacBook or Chromebook

This 7-port USB 3.0 hub connects directly to the USB-A port on your computer, laptop, MacBook, Ultrabook or Chromebook. It allows you to use as many as seven USB devices, such as flash drives, external hard drives, printers, barcode scanners, webcams, keyboards/mice and power meters, all at the same time.

Supports SuperSpeed USB 3.0 to Ensure Fast Data Transfers

Two USB 3.0 ports support data transfer rates up to 5 Gbps, which is 10 times faster than USB 2.0 and recommended for high-bandwidth USB 3.0 devices, such as security cameras and high-resolution webcams. Five USB 2.0 ports transfer data at speeds up to 480 Mbps. All seven ports are backward compatible with previous USB generations, so you can continue using older peripherals while getting high-speed performance from new devices.

Charge a Device Even When Your Computer or Laptop Is Not in Use

The first USB 3.0 port, which is labeled with a charge symbol, can charge a mobile device, such as a smartphone or tablet, when the source device is in Suspend mode only. A blue LED indicates the hub is receiving sufficient power to support all connected devices.

Plug-and-Play Hub Comes Ready to Connect Right Away

The U360-007C-2X3 works with Windows and Mac computers and requires no software or drivers to download and install. The included external power supply comes with four international plug adapters that ensure you can use the hub almost anywhere. Most of the time, the hub will receive plenty of power from your computer or laptop. The included power supply should only be necessary when connecting high-current, power-hungry USB peripherals.

Sleek and Slim Housing Designed for Everyday Workspace Use or Connecting on the Go

The compact unit is designed for convenient positioning within your reach, making USB ports accessible while not taking up much workspace. It is slim enough to pack in your pocket, purse or laptop bag for use in a hotel, conference room or airport.

Highlights

- Turns your computer or laptop into a mini workstation with 7 extra USB ports
- USB 3.0 ports support SuperSpeed rates up to 5 Gbps to ensure fast data transfers
- Charging port charges mobile device when your computer/laptop is in Suspend mode
- Slim aluminum hub fits easily in your backpack or laptop bag for connecting on the go
- Plug-and-play operation with no software required for easy, immediate installation

Applications

- Connect up to 7 USB peripherals, such as an external hard drive, MP3 player, power meter and printer, to your MacBook or Chromebook
- Transfer files quickly to and from a USB thumb drive
- Attach a USB headset/microphone for recording your podcast
- Write a report using a USB keyboard with your tablet or Android smartphone
- Download photos from a digital camera

System Requirements

- Compatible with all USB-enabled operating systems (USB 3.0 port needed to achieve USB 3.0 speeds)

Package Includes

- U360-007C-2X3 7-Port USB 3.0 / USB 2.0 Combo Hub
- USB-A to USB Micro-B 3.0 cable, 3 ft.
- External power supply (Input: 100–240V, 50/60 Hz, 1.5A; Output: 5V 4A)
- (4) International plug adapters (North America, U.K., Europe, Australia)

Specifications

OVERVIEW	
UPC Code	037332242082
Product Type	Hub
Technology	USB 2.0 (High Speed)
Host Connector	USB A (MALE)
VIDEO	
Number of Monitors Supported	0
Extended Mode	No
Mirror Mode	No
DATA	
Data Ports	(7) USB A (FEMALE)
Data Ports Details	(2) USB-A - USB 3.2 Gen 1 (5 Gbps); (5) USB-A - USB 2.0
INPUT	
AC Power Adapter Plug(s)	AS/NZS 3112 Australia; BS 1363 UK; CEE 7/16 Schuko; NEMA 1-15P North America
AC Power Adapter Input Specs (V / Hz / A)	100-240V / 50/60HZ / 0.6A
AC Power Adapter Output Specs (V / A)	5V / 3A
AC Power Adapter Cord Length (ft.)	5
AC Power Adapter Cord Length (m)	1.5
Voltage Compatibility (VAC)	100; 110; 120; 125; 127; 200; 208; 220; 230; 240
Bus Powered	Yes
Product Length (in.)	6.53
Product Length (cm.)	16.6
Product Length (ft.)	0.544
Product Length (m)	0.166
POWER	
Power Source Type	AC Adapter
AC Adapter	Input: 100-240V, 50/60Hz, 0.6A; Output: 5V, 3A
DC Barrel Plug	OD: 3.5 x 1.35 x 8mm, Positive Pin, Negative Sleeve
CONNECTIONS	
Number of Ports	7
Side A - Connector 1	(2) USB 3.0 A (FEMALE)

Side A - Connector 2	(5) USB A (FEMALE)
Side B - Connector 1	USB 3.0 MICRO-B (FEMALE)
Connector Plating	Nickel
USER INTERFACE, ALERTS & CONTROLS	
LED Indicators	POWER LED (BLUE)
CHARGING	
Charging Ports	(1) USB-A: 5V 1.5A (7.5W)
Charging Ports Details	USB Charging Port supports BC 1.2 (5V 1.5A)
Charging Ports / Amps	(1) 1.5A
PHYSICAL	
Color	White
Material of Construction	ABS
Unit Dimensions (hwd / in.)	0.630 x 6.500 x 1.280
Unit Packaging Type	Box
Unit Weight (lbs.)	0.13
Unit Weight (kg)	0.06
ENVIRONMENTAL	
Operating Temperature Range	32° to 113°F (0° to 45°C)
Storage Temperature Range	23° to 158°F (-5° to 70°C)
Relative Humidity	5% to 85% RH, Non-Condensing
Power Provided to Connected Device(s)	5V 0.9A (4.5W) when bus powered
FEATURES & SPECIFICATIONS	
USB Hub Ports	Yes
Number of USB Hub Ports	7
USB Specification	USB 3.0 (up to 5 Gbps); USB 3.1 Gen 1 (up to 5 Gbps); USB 3.2 Gen 1 (up to 5 Gbps)
Driver Required	No
STANDARDS & COMPLIANCE	
TAA Compliant Option	N
External Power Supply Certifications	CCC; CE; GS; PSE; TUV; UL; cUL
Product Compliance	RoHS; CE (Europe); REACH; FCC (USA)
WARRANTY & SUPPORT	



Powering Business Worldwide



Product Warranty Period (Worldwide)	3-year limited warranty
--	-------------------------

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.