

## USB-C Cable (M/M) - USB 3.2 Gen 2 (10 Gbps), Thunderbolt 3 Compatible, 3 ft. (0.91 m)

MODEL NUMBER: **U420-003-G2**



Connects and charges USB-C and Thunderbolt 3 devices at USB 3.2 Gen 2 speeds up to 10 Gbps.

### Features

#### Connects and Charges a USB-C or Thunderbolt 3 Device

The three-foot U420-003-G2 connects two devices with USB-C or Thunderbolt 3 ports or connects one device to a USB-C wall charger. This cable supports USB 3.2 Gen 2 data transfer rates up to 10 Gbps and is backward compatible with previous USB generations. Its 3A power output is ideal for fast charging of mobile devices.

#### Premium Construction Results in Premium Signal Quality

Molded nickel-plated connectors with gold-plated contacts provide maximum conductivity and minimum data loss to guarantee a clear transmission free of interference. Foil and braid shielding delivers reliable, error-free signal quality and protection from EMI/RFI line noise that can distort or destroy data. Integral strain relief gives the cable extra flexibility, reduces stress, and helps the cable move freely without cracking or breaking loose from the connector.

#### Reversible USB-C Connectors Attach in Either Direction

Unlike traditional USB cables that connect in only one direction, the reversible USB-C male connectors plug into USB-C or Thunderbolt 3 ports in either direction for an instant connection every time.

### Highlights

- USB 3.2 Gen 2 data transfer speeds up to 10 Gbps
- Error-free signal quality and EMI/RFI protection
- Compatible with both USB-C and Thunderbolt 3 ports
- Reversible USB-C male connectors on both ends
- Power output up to 3A for fast-charging devices

### Package Includes

U420-003-G2 USB 3.2 Gen 2 Cable, USB-C (M/M), 3 ft.

## Specifications

OVERVIEW	
UPC Code	037332197368
Device Compatibility	Amazon Kindle; Chromebook; Headphones; Laptop; Phone; Tablet; Video Game System; Watch
Technology	Thunderbolt; USB 3.x
Country/Region	Global
Cable Type	Passive
VIDEO	



Powering Business Worldwide

TRIPP LITE  
SERIES

Number of Monitors Supported	1
Resolutions Supported	Capable of transmitting Ultra High Definition (UHD) video up to 4K x 2K (3840 x 2160) @ 30 Hz from hosts that support USB-C DP Alt Mode
Supported Resolutions	3840x2160 (4K)
Max Supported Video Resolution	4096 x 2160 (4K)
DisplayPort Alt Mode	Yes
<b>CONNECTIONS</b>	
Side A - Connector 1	USB C (MALE)
Side B - Connector 1	USB C (MALE)
Connector Plating	Nickel
Contact Plating	Gold
Connector Style	Straight
<b>CHARGING</b>	
Compatible Devices	Portable Speaker; Smartphone; Tablet; Video Game Console
<b>PHYSICAL</b>	
Material of Construction	PVC
Cable Jacket Color	Black
Cable Jacket Rating	VW-1
Cable Outer Diameter (OD)	5.2MM
Cable Length (ft.)	3
Cable Length (m)	0.91
Cable Length (in.)	36
Shipping Dimensions (hwd / in.)	9.00 x 6.50 x 0.50
Shipping Dimensions (hwd / cm)	22.86 x 16.51 x 1.27
Shipping Weight (lbs.)	0.10
Shipping Weight (kg)	0.05
Unit Dimensions (hwd / in.)	9.000 x 6.500 x 0.500
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	14° to 140°F (-10° to 60°C)
Storage Temperature Range	-4° to 185°F (-20° to 85°C)
Relative Humidity	10% to 85% RH, Non-Condensing
<b>FEATURES &amp; SPECIFICATIONS</b>	
USB Specification	USB 3.2 Gen 2 (Up to 10 Gbps)



Powering Business Worldwide

TRIPP LITE  
SERIES

STANDARDS & COMPLIANCE	
Product Compliance	RoHS; CE (Europe); REACH; FCC (USA)
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	3-year limited warranty

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.