

USB-C Cable (M/M) - USB 3.1, Gen 2 (10 Gbps), 5A Rating, Thunderbolt 3 Compatible, 3 ft. (0.91 m)

MODEL NUMBER: **U420-003-G2-5A**



Highlights

- Power output up to 5A for fast-charging large mobile devices
- Supports USB 3.1 Gen 2 data transfer speeds up to 10 Gbps
- Reversible USB-C plugs on both ends for fumble-free connection
- Error-free signal quality and EMI/RFI line noise protection
- Compatible with Thunderbolt™ 3 devices

System Requirements

- Devices with USB-C female connectors

Package Includes

- U420-003-G2-5A USB 3.1 Gen 2 (10 Gbps) Cable with 5A Rating, USB-C to USB-C (M/M), 3 ft.

USB-C cable provides up to 20V 5A (100W) of power—more than enough to charge large-capacity mobile devices, such as the MacBook Pro®. Also connects smartphones, computers, wall chargers and other USB-C devices.

Features

Connects 2 USB-C DevicesPower output up to 20V 5A (100W) for fast-charging large mobile devices, such as MacBook ProRecommended for connecting smartphones, tablets, computers, wall chargers and other USB-C devicesSupports USB 3.1 Gen 2 data transfer speeds up to 10 GbpsBackward compatible with previous USB generationsCompatible with Thunderbolt 3 devices

Reversible USB-C Male ConnectorsFumble-free reversible plugs connect in either direction to ensure fast, easy connection every time

Premium ConstructionMolded connectors and gold-plated contacts for maximum conductivity and minimum data lossFoil and braid shielding delivers reliable, error-free signal quality and EMI/RFI protection

Specifications

OVERVIEW	
UPC Code	037332202888
Technology	USB 3.1 (Gen 2)
PHYSICAL	
Color	Black
Cable Jacket Rating	VW-1



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Cable Outer Diameter (OD)	5.2MM
Cable Length (ft.)	3
Cable Length (m)	0.9
Cable Length (in.)	36
Material of Construction	PVC
Cable Length (cm)	91.4
Shipping Dimensions (hwd / cm)	1.27 x 15.24 x 22.86
Shipping Dimensions (hwd / in.)	0.50 x 6.00 x 9.00
Shipping Weight (kg)	0.14
Shipping Weight (lbs.)	0.30
ENVIRONMENTAL	
Operating Temperature Range	14 to 140 F (-10 to 60 C)
Storage Temperature Range	-4 to 185 F (-20 to 85 C)
Relative Humidity	10% to 85% RH, Non-Condensing
CONNECTIONS	
Side A - Connector 1	USB C (MALE)
Side B - Connector 1	USB C (MALE)
Connector Plating	Nickel
Contact Plating	Gold
FEATURES & SPECIFICATIONS	
USB Specification	USB 3.1 Gen 2 (up to 10 Gbps)
STANDARDS & COMPLIANCE	
Certifications	Tested to CE, FCC, RoHS, REACH
WARRANTY	
Product Warranty Period (Worldwide)	3-year limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>