

USB-C Cable (M/M) - USB 3.2, Gen 2 (10 Gbps), 5A (100W) Rating, Thunderbolt 3 Compatible, 3 ft. (0.91 m)

MODEL NUMBER: U420-003-G2-5A



Highlights

- Power output up to 5A for fast-charging large mobile devices
- Supports USB 3.2 Gen 2 data transfer speeds up to 10 Gbps
- Reversible USB-C plugs on both ends for fumble-free connection
- Error-free signal quality and EMI/RFI line noise protection
- Compatible with Thunderbolt™ 3 devices

System Requirements

- Devices with USB-C female connectors

Package Includes

- U420-003-G2-5A USB 3.2 Gen 2 (10 Gbps) Cable with 5A Rating, USB-C to USB-C (M/M), 3 ft.

USB-C cable provides up to 20V 5A (100W) of power—more than enough to charge large-capacity mobile devices, such as the MacBook Pro®. Also connects smartphones, computers, wall chargers and other USB-C devices.

Features

Connects 2 USB-C Devices Power output up to 20V 5A (100W) for fast-charging large mobile devices, such as MacBook Pro Recommended for connecting smartphones, tablets, computers, wall chargers and other USB-C devices Supports USB 3.2 Gen 2 data transfer speeds up to 10 Gbps Backward compatible with previous USB generations Compatible with Thunderbolt 3 devices

Reversible USB-C Male Connectors Fumble-free reversible plugs connect in either direction to ensure fast, easy connection every time

Premium Construction Molded connectors and gold-plated contacts for maximum conductivity and minimum data loss Foil and braid shielding delivers reliable, error-free signal quality and EMI/RFI protection

Specifications

OVERVIEW	
UPC Code	037332202888
Technology	Thunderbolt; USB 3.x
Cable Type	Passive
CONNECTIONS	
Side A - Connector 1	USB C (MALE)
Side B - Connector 1	USB C (MALE)
Connector Plating	Nickel



Powering Business Worldwide

TRIPP LITE
SERIES

Contact Plating	Gold
Connector Style	Straight
PHYSICAL	
Material of Construction	PVC
Cable Jacket Color	Black
Cable Jacket Rating	VW-1
Cable Outer Diameter (OD)	5.2MM
Cable Length (ft.)	3
Cable Length (m)	0.91
Cable Length (in.)	36
Cable Length (cm)	91.4
Shipping Dimensions (hwd / in.)	0.50 x 6.00 x 9.00
Shipping Dimensions (hwd / cm)	1.27 x 15.24 x 22.86
Shipping Weight (lbs.)	0.30
Shipping Weight (kg)	0.14
Unit Dimensions (hwd / in.)	0.500 x 6.000 x 9.000
ENVIRONMENTAL	
Operating Temperature Range	14° to 140°F (-10° to 60°C)
Storage Temperature Range	-4° to 185°F (-20° to 85°C)
Relative Humidity	10% to 85% RH, Non-Condensing
FEATURES & SPECIFICATIONS	
USB Specification	USB 3.2 Gen 2 (Up to 10 Gbps)
STANDARDS & COMPLIANCE	
Product Compliance	RoHS; CE (Europe); REACH; FCC (USA)
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	3-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.