

USB-C to USB-A Cable (M/M), USB 3.1 Gen 1 (5 Gbps), Thunderbolt 3 Compatible, 6 ft. (1.83 m)

MODEL NUMBER: U428-006



This USB-C to USB-A cable connects a USB Type-C (USB-C) device to the USB Type-A port on your tablet, computer or USB charger.

Features

Supports USB 3.1 Gen 1 This USB-C to USB-A cable features data transfer speeds up to 5 Gbps—10 times faster than USB 2.0 – and uses the same Type-A male connector as USB 3.0 devices.

USB Type-C (USB-C) Male Connector Unlike traditional USB cables that can be attached only one way, the fumble-free reversible USB-C plug ensures fast, easy connection every time.

Premium Design and Construction Gold-plated copper contacts, nickel-plated molded ends and a rugged PVC jacket provide for a lifetime of heavy use and superior conductivity. Foil shielding offers protection from EMI/RFI interference for reliable, error-free data communication.

Lifetime Limited Warranty The U428-006 is backed by a lifetime warranty, ensuring reliability and performance.

Highlights

- Connects a USB-C device to the USB-A port on your computer or charger
- 6-ft. (1.83 m) cable supports USB 3.1 Gen 1 data transfer speeds up to 5 Gbps
- Reversible USB-C male plug connects into a USB port in either direction
- Superior conductivity and data communication
- Backward compatible with previous USB generations
- Compatible with Thunderbolt™ 3 devices
- PD Charging Compliant

Applications

- Connect USB-C mobile devices and peripherals (such as portable hard drives) to your USB-A computer
- Charge and sync your USB-C mobile devices from a USB-A laptop or wall charger
- Ideal for those who need longer cables with USB-C to USB-A connections

System Requirements

- A device with a USB Type-C (USB-C) port
- A device with a USB Type-A port

Package Includes

- U428-006 USB 3.1 Gen 1 (5 Gbps) Cable, USB Type-C (USB-C) to USB Type-A M/M, 6-



ft. (1.83 m)

Specifications

OVERVIEW	
UPC Code	037332218391
Technology	USB 3.1 (Gen 1); USB
PHYSICAL	
Color	Black
Cable Outer Diameter (OD)	4.5MM
Cable Jacket Rating	VW-1
Cable Length (ft.)	6
Cable Length (m)	1.8
Cable Length (in.)	72
Material of Construction	PVC
Cable Length (cm)	182
Shipping Dimensions (hwd / cm)	22.86 x 17.78 x 1.27
Shipping Dimensions (hwd / in.)	9.00 x 7.00 x 0.50
Shipping Weight (kg)	0.14
Shipping Weight (lbs.)	0.30
Unit Packaging Type	Polybag
ENVIRONMENTAL	
Operating Temperature Range	14 to 140 F (-10 to 60 C)
Storage Temperature Range	-4 to 185 F (-20 to 85 C)
Relative Humidity	10% to 85% RH, Non-Condensing
CONNECTIONS	
Side A - Connector 1	USB C (MALE)
Side B - Connector 1	USB 3.0 A (MALE)
Connector Plating	Nickel
Contact Plating	Gold
FEATURES & SPECIFICATIONS	



USB Specification	USB 3.1 Gen 1 (up to 5 Gbps)
STANDARDS & COMPLIANCE	
Certifications	Tested to ROHS, REACH
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>