

## USB-C to HDMI Adapter (M/F) - 4K 60 Hz, HDCP 2.2, Black

MODEL NUMBER: **U444-06N-HD4K6B**



Connects your existing 4K HDMI TV, monitor or projector to the USB-C or Thunderbolt 3 port on your tablet, laptop, notebook, MacBook, Chromebook, smartphone or PC.

### Description

The U444-06N-HD4K6B USB 3.1 Gen 1 USB-C to HDMI 4K Adapter (M/F) helps you transmit digital audio and 4K video from your tablet, laptop, Chromebook, MacBook, smartphone or PC to an HDMI-enabled television, monitor or projector. It's an ideal tool for giving video presentations in conference rooms and classrooms, editing multiple documents on a larger screen or streaming video for digital signage in crystal-clear 4K.

With a source device that also supports USB DisplayPort Alternate Mode, you can extend video from your primary display to another, duplicate the same video on both displays or change the second display to your primary.

The plug-and-play U444-06N-HD4K6B requires no software, drivers or external power. Connect the reversible USB-C plug to your source device's USB-C or Thunderbolt 3 port. The fumble-free USB-C plug connects in either direction to ensure fast, easy connection every time. Then, connect the HDMI port to your display using an HDMI cable (sold separately).

The U444-06N-HD4K6B meets HDCP 2.2 specifications. It supports UHD video resolutions up to 4K x 2K (4096 x 2160) at 60 Hz, as specified in HDMI 2.0. It supports 24-bit Deep Color (8 bits per channel), 7.1-channel surround sound and per-lane transfer rates of 5.4 Gbps (HBR2), 2.7 Gbps (HBR) and 1.62 Gbps (RBR).

### Features

**Connects an HDMI Display to Your USB-C or Thunderbolt 3 Device** Compatible with USB-C or Thunderbolt 3 source devices that support USB DisplayPort Alternate Mode  
**Ideal for giving video presentations, editing multiple documents or streaming video for digital signage**  
**Meets HDCP 2.2 specifications**

**Common Applications** Extends video from your primary display to another  
Duplicates the same video on 2 displays  
Converts a secondary display to your primary display

**Crystal-Clear True 4K Video and Digital Audio** Supports UHD video resolutions up to 4K x 2K (4096 x 2160) @ 60 Hz, as specified in HDMI 2.0  
Supports 24-bit Deep Color (8 bits per channel)  
Supports 7.1-channel surround sound  
Supports per-lane transfer rates of 5.4 Gbps (HBR2), 2.7 Gbps (HBR) and 1.62

### Highlights

- Supports USB DisplayPort Alternate Mode for transmitting audio/video
- Supports UHD resolutions up to true 4K @ 60 Hz for crystal-clear video
- Supports 7.1-channel surround sound
- Reversible USB-C plug connects in either direction
- Plug-and-play operation with no software or drivers required

### System Requirements

- Source device with USB-C or Thunderbolt 3 port that supports USB DisplayPort Alternate Mode
- Display device with HDMI input

### Package Includes

- U444-06N-HD4K6B USB 3.1 Gen 1 USB-C to HDMI 4K Adapter (M/F)
- Owner's manual



Gbps (RBR)

**Built-In Cable with Reversible USB-C Connector**Fumble-free reversible USB-C plug connects in either direction for quick connection every time

**Ready for Instant Use**Plug-and-play operation with no software, drivers or external power requiredHalf the footprint of a credit card for easy carrying in a pocket, purse or laptop bagBackward compatible with non-4K displays

## Specifications

OVERVIEW	
UPC Code	037332203366
Technology	HDMI; USB; USB 3.0 (SuperSpeed); USB 3.1 (Gen 1)
VIDEO	
Max Supported Video Resolution	HDMI: 4096 X 2160 (4K X 2K) @ 60HZ
AUDIO	
Audio Specification	7.1 Channel Surround Sound
INPUT	
Bus Powered	Yes
Product Length (in.)	6
Product Length (cm.)	15.24
Product Length (ft.)	0.5
Product Length (m.)	0.15
BATTERY	
Battery Charging (5V/1.5A Port)	No
PHYSICAL	
Color	Black
Cable Jacket Rating	VW-1
Material of Construction	ABS
Shipping Dimensions (hwd / cm)	2.69 x 14.50 x 7.62
Shipping Dimensions (hwd / in.)	1.06 x 5.71 x 3.00
Shipping Weight (kg)	0.05
Shipping Weight (lbs.)	0.11
Unit Dimensions (hwd / in.)	0.55 x 1.8 x 1.1



Unit Packaging Type	Box
Unit Weight (kg)	0.02
Unit Weight (lbs.)	0.04
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	-4 to 158 F (-20 to 70 C)
Storage Temperature Range	-4 to 185 F (-20 to 85 C)
Relative Humidity	20% to 80% RH, Non-Condensing
BTUs	2.3 BTU/Hr
Power Consumption (Watts)	0.68
<b>CONNECTIONS</b>	
Ports	1
Side A - Connector 1	USB C (MALE)
Side B - Connector 1	HDMI (FEMALE)
Connector Plating	Nickel
Contact Plating	Gold
<b>FEATURES &amp; SPECIFICATIONS</b>	
HDCP Specification	2.2
USB Specification	USB 3.0 (up to 5 Gbps); USB 3.1 Gen 1 (up to 5 Gbps)
Driver Required	No
<b>STANDARDS &amp; COMPLIANCE</b>	
Certifications	Tested to CE, FCC, RoHS, REACH
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	3-year limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>