

USB-C to HDMI 4K Adapter with Alternate Mode - DP 1.2, Black

MODEL NUMBER: U444-06N-HDB-AM



USB-C to HDMI cable connects your HDMI display to the USB-C or Thunderbolt 3 port on your laptop, MacBook or Chromebook.

Features

USB-C to HDMI Cable Connects a 4K HDMI Display to Your USB-C or Thunderbolt 3 Device This USB 3.1 to HDMI adapter helps you transmit video from your tablet, laptop, Chromebook, MacBook, smartphone or PC to a 4K HDMI-enabled television, monitor or projector. It's ideal for giving video presentations in conference rooms and classrooms, editing multiple documents on a larger screen or streaming video for digital signage in crystal-clear 4K.

Supports USB DisplayPort Alternate Mode for Transmitting Video Signals With a source device that also supports USB DisplayPort Alt Mode, you can extend video from your primary display to another, duplicate the same video on both displays, or change the second display to your primary.

Transmits Crystal-Clear 4K HDMI Video and Digital Audio To send digital audio and Ultra High Definition video to a 4K-ready HDMI television, projector or monitor, connect the HDMI port to the display using an HDMI cable (sold separately). The HDMI port supports UHD video resolutions up to 3840 x 2160 (4K) at 24/25/30 Hz and lush 7.1 surround sound. It also supports 36-bit Deep Color (12 bits per channel) and per-lane transfer rates of 5.4 Gbps (HBR2), 2.7 Gbps (HBR) and 1.62 Gbps (RBR). This USB-C to HDMI cable is backward compatible with non-4K displays.

Built-In USB-C Cable Connects in Either Direction Connect the reversible USB-C plug to your source device's USB-C or Thunderbolt 3 port. The fumble-free USB-C plug connects in either direction to ensure fast, easy connection every time.

Ready to Use Right Out of the Package The plug-and-play USB 3.1 to HDMI adapter requires no software, drivers or external power. It's about half the size of a credit card, making it easy to carry in a pocket, briefcase or laptop bag for connecting on the go.

3-Year Warranty and Environmentally Responsible Design The U444-06N-HDB-AM comes with a 3-year warranty. It's manufactured in compliance with strict RoHS specifications, reflecting Tripp Lite's commitment to environmental responsibility.

Highlights

- Transmits video signals from sources supporting USB DisplayPort Alt Mode
- Delivers UHD picture quality at resolutions up to 4K @ 24/25/30 Hz
- Supports USB 3.1 Gen 1 speeds up to 5 Gbps to ensure fast data transfers
- Reversible USB-C plug connects in either direction for immediate no-fuss use
- Easy installation with plug-and-play operation—no software required

Applications

- Play 4K video from your laptop or PC on an HDMI display
- Give a video presentation at a meeting, training session, conference or trade show
- Multitask in two or more applications with an add-on display
- Add a second monitor to your laptop and make it your primary monitor
- Edit large documents on two different monitors

System Requirements

- Source device with USB-C or Thunderbolt 3 port that supports USB DisplayPort Alternate Mode
- Display device with HDMI input

Package Includes



- USB-C to HDMI Adapter – M/F, Thunderbolt 3, USB 3.1, 4K @ 24/25/30 Hz, Black
- Quick Start Guide

Specifications

OVERVIEW	
UPC Code	037332210661
Technology	USB 3.1 (Gen 1); HDMI; USB
VIDEO	
Max Supported Video Resolution	HDMI: 3840 X 2160 (4K) @ 24/25/30HZ
INPUT	
Bus Powered	Yes
Product Length (in.)	6
Product Length (cm.)	15.24
Product Length (ft.)	0.5
Product Length (m.)	0.15
BATTERY	
Battery Charging (5V/1.5A Port)	No
POWER	
USB Power Delivery (PD) Charging Support	No
PHYSICAL	
Cable Jacket Rating	VW-1
Color	Black
Material of Construction	PVC, ABS
Shipping Dimensions (hwd / cm)	2.03 x 9.65 x 11.94
Shipping Dimensions (hwd / in.)	0.80 x 3.80 x 4.70
Shipping Weight (kg)	0.05
Shipping Weight (lbs.)	0.10
Unit Dimensions (hwd / cm)	0.67 x 1.25 x 3.5



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Unit Dimensions (hwd / in.)	0.26 x 0.49 x 1.38
Unit Packaging Type	Box
Unit Weight (kg)	0.02
Unit Weight (lbs.)	0.05
ENVIRONMENTAL	
Operating Temperature Range	32 to 113 F (0 to 45 C)
Storage Temperature Range	14 to 158 F (-10 to 70 C)
BTUs	2.1 BTU/Hr
Power Consumption (Watts)	0.6
Operating Humidity Range	10% to 85% RH, Non-Condensing
Storage Humidity Range	5% to 90% RH, Non-Condensing
COMMUNICATIONS	
Signal Range (ft.)	16
Signal Range (m)	5
CONNECTIONS	
Ports	1
Side A - Connector 1	USB C (MALE)
Side B - Connector 1	HDMI (FEMALE)
Connector Plating	Nickel
FEATURES & SPECIFICATIONS	
Displayport Specification	1.2
HDMI Specification	1.4
HDCP Specification	1.4
USB Specification	USB 3.1 Gen 1 (up to 5 Gbps)
Driver Required	No
STANDARDS & COMPLIANCE	
Certifications	Tested to CE, FCC, RoHS, REACH
WARRANTY	
Product Warranty Period (Worldwide)	3-year limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>