

# USB-C Multiport Adapter (M/3xF) - 4K HDMI, DVI, VGA, HDCP, Black

MODEL NUMBER: U444-06N-HDV4KB



USB-C adapter connects an HDMI, DVI or VGA display to the USB-C or Thunderbolt 3 port on your laptop, MacBook or Chromebook.

## Features

**USB-C All-in-One Adapter Connects a DVI, VGA or 4K HDMI Display to Your USB-C or Thunderbolt 3 Device**No more carrying around separate adapters to match various monitors, projectors and televisions. This USB-C all-in-one adapter connects your tablet, laptop, Chromebook, MacBook, smartphone or PC to a DVI, VGA or 4K HDMI display. The simple all-in-one solution for displaying video content on a larger screen, the U444-06N-HDV4KB is ideal for giving video presentations in conference rooms and classrooms, editing multiple documents on a larger screen or streaming video for digital signage in crystal-clear 4K x 2K.

**Supports USB DisplayPort Alternate Mode for Transmitting Video Signals**With a source device that also supports USB DisplayPort Alt Mode, you can extend video from your primary display to another, duplicate the same video on both displays, or change the second display to your primary.

**Transmits Crystal-Clear 4K HDMI Video and Digital Audio**To send digital audio and Ultra High Definition video to a 4K-ready HDMI television, projector or monitor, connect the HDMI port to the display using an HDMI cable (sold separately). The HDMI port supports video resolutions up to 3840 x 2160 (4K x 2K) at 30 Hz, as well as 36-bit Deep Color (12 bits per channel), 7.1-channel surround sound audio and HDCP 1.4. The USB-C all-in-one adapter is backward compatible with non-4K HDMI displays.

**No Need to Upgrade to an Expensive New Display**The all-in-one unit also features separate DVI and HD15 ports, in addition to HDMI. This allows you to continue using an existing DVI or VGA display, instead of investing money in something new. The DVI port supports video resolutions of 1920 x 1080 (1080p) at 60 Hz. The HD15 port supports 1920 x 1200, including 1080p, at 60 Hz. Only one monitor can be connected at a time.

**Built-In USB-C Cable Connects in Either Direction**Connect the reversible USB-C plug to your source device's USB-C or Thunderbolt 3 port. The fumble-free USB-C plug connects in either direction to ensure fast, easy connection every time.

**Ready to Use Right Out of the Package**The plug-and-play USB-C all-in-one adapter is specifically designed for use with the MacBook, Google Chromebook Pixel and all other laptops, tablets and devices equipped with a female USB-C or Thunderbolt 3 port. It requires no software, drivers or external power. It's no larger than a credit card, making it easy to carry in a pocket, briefcase or laptop bag for connecting on the go.

## Highlights

- Transmits video signals from sources supporting USB DisplayPort Alt Mode
- Connects HDMI, DVI and VGA with no need to carry separate adapters for each display
- Delivers HDMI picture quality at resolutions up to 4K x 2K @ 30 Hz
- Reversible USB-C plug connects in either direction for immediate no-fuss use
- Easy installation with plug-and-play operation—no software required

## Applications

- Play video from your laptop or PC on an HDMI, DVI or VGA monitor
- Give a video presentation at a meeting, training session, conference or trade show
- Multitask in two or more applications with an add-on display
- Add a second monitor to your laptop and make it your primary monitor
- Edit large documents on two different monitors

## System Requirements

- Source device with USB-C or Thunderbolt 3 output that supports USB DisplayPort Alternate Mode
- Display device with HDMI, DVI or VGA input

## Package Includes

- U444-06N-HDV4KB USB-C Multiport Adapter, Black
- Owner's manual

**3-Year Warranty and Environmentally Responsible Design**The U444-06N-HDV4KB comes with a 3-year warranty. It's manufactured in compliance with strict RoHS specifications.

## Specifications

OVERVIEW	
UPC Code	037332210746
Product Type	Multiport Adapter
Technology	DVI; HDMI; VGA/SVGA
Host Connector	USB C (MALE)
VIDEO	
Video Input	USB C (MALE)
Video Output	DVI-I DUAL LINK (FEMALE); HD15 (FEMALE); HDMI (FEMALE)
Number of Monitors Supported	1
Video Ports	HDMI (FEMALE); DVI-I DUAL LINK (FEMALE); HD15 (FEMALE)
Video Ports Details	HDMI 1.4; HDCP 1.4
Resolutions Supported	HDMI: 4K 30Hz (3840 x 2160) DVI: 1080P 60Hz (1920 x 1080) VGA: 1920 x 1200 60Hz
Supported Resolutions	1280x720 (720p); 1920x1080 (1080p); 1920x1200; 2560x1600; 3840x2160 (4K)
Max Supported Video Resolution	HDMI: 3840 X 2160 (4K X 2K) @ 30HZ, VGA: 1920 x 1200 (1080p) @ 60Hz, DVI: 1920 x 1080 (1080p) @ 60Hz
Extended Mode	Yes
Mirror Mode	Yes
HDR Support	No
3D Video Supported	Yes
EDID Support	No
DisplayPort Alt Mode	Yes
INPUT	
Built-In Cable Length (ft.)	0.36
Built-In Cable Length (m)	0.11
Built-In Cable Length (in.)	4.33
Built-In Cable Length (cm)	11
Bus Powered	Yes
Product Length (in.)	6
Product Length (cm.)	15.24
Product Length (ft.)	0.5
Product Length (m)	0.15

<b>BATTERY</b>	
Battery Charging (5V/1.5A Port)	No
<b>POWER</b>	
Power Consumption (Watts)	1.80
USB Power Delivery (PD) Charging Support	No
<b>CONNECTIONS</b>	
Number of Ports	3
Side A - Connector 1	USB C (MALE)
Side B - Connector 1	DVI-I DUAL LINK (FEMALE)
Side B - Connector 2	HD15 (FEMALE)
Side B - Connector 3	HDMI (FEMALE)
Connector Plating	Nickel
Contact Plating	Nickel
<b>PHYSICAL</b>	
Color	Black
Material of Construction	PVC
Cable Jacket Color	Black
Cable Jacket Material	PVC
Cable Jacket Rating	VW-1
Cable Outer Diameter (OD)	3.9mm
Wire Gauge (AWG)	28+34
Shipping Dimensions (hwd / in.)	0.91 x 5.51 x 3.94
Shipping Weight (lbs.)	0.15
Unit Dimensions (hwd / in.)	0.600 x 3.300 x 1.800
Unit Packaging Type	Box
Unit Weight (lbs.)	0.12
Unit Weight (kg)	0.05
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	32° to 113°F (0° to 45°C)
Storage Temperature Range	14° to 158°F (-10° to 70°C)
BTUs	6.1 BTU/Hr
Operating Humidity Range	10% TO 85% RH, NON-CONDENSING



Powering Business Worldwide



Storage Humidity Range	5% TO 90% RH, NON-CONDENSING
<b>FEATURES &amp; SPECIFICATIONS</b>	
USB Hub Ports	No
Number of USB Hub Ports	0
USB Specification	USB 3.0 (up to 5 Gbps); USB 3.1 Gen 1 (up to 5 Gbps); USB 3.2 Gen 1 (up to 5 Gbps)
Multi-Resolution Support	Yes
UASP Support	No
Auto MDIX Support	No
Full Duplex Support	No
Suspend Mode Support	No
Remote Wakeup Support	No
HDCP Specification	1.4
Driver Required	No
<b>STANDARDS &amp; COMPLIANCE</b>	
TAA Compliant Option	N
Product Compliance	RoHS; CE (Europe); REACH; FCC (USA)
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	3-year limited warranty

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.