

USB-C to DisplayPort Flat Adapter Cable (M/F) - 4K 60 Hz, UHD, Thunderbolt 3 Compatible, Black, 5 in.

MODEL NUMBER: U444-F5N-DP4K6



Flat USB-C to DisplayPort cable connects a DP monitor to your MacBook Pro, Windows laptop or tablet's USB-C or Thunderbolt 3 port.

Features

Flat USB-C to DisplayPort Adapter Connects to Your Laptop's USB-C or Thunderbolt 3 PortThis USB Type-C to DisplayPort adapter (M/F) connects to a DisplayPort cable to add a DisplayPort monitor to the USB-C or Thunderbolt 3 port on your MacBook Pro, Windows laptop, tablet, smartphone or PC. It's ideal for multitasking, presenting video at trade shows and conferences, editing documents, playing online games and watching movies on a larger screen.

Flat FPC Design Allows Easy Handling and StorageThe flat, bendable FPC (Flexible Printed Circuit) body helps the cable connect to devices in tight spaces or around obstacles. It rolls easily for tangle-free storage in your backpack or laptop bag.

Supports USB-C DisplayPort Alternate Mode for Converting Audio/Video SignalsBy connecting the USB-C connector to a source device that supports USB DisplayPort Alt Mode, you can output 4K video and digital audio to a DisplayPort monitor, television or projector without installing special software drivers.

Transmits Crystal-Clear 4K Video with Digital Audio and 4:4:4 ColorThe U444-F5N-DP4K6 supports Ultra HD video resolutions up to 3840 x 2160 (4K x 2K) at 60 Hz, as well as 36-bit Deep Color. This adapter also supports 4:4:4 chroma subsampling for top-level PC gaming or using your HDTV as a PC monitor.

Reversible USB-C Connector Attaches in Either DirectionUnlike traditional USB cables that connect in only one direction, the reversible USB-C male connector plugs into a USB-C or Thunderbolt 3 port in either direction for an instant connection every time.

Ready to Use Right from the Package, So You Can Plug and Play ImmediatelyThe plug-and-play adapter is specifically designed for use with the MacBook Pro, Windows laptops and other devices equipped with a USB-C or Thunderbolt 3 port. It requires no software or external power. The five-inch cable fits into your pocket, briefcase or laptop bag for connecting to DisplayPort monitors anywhere.

Highlights

- Flexible flat design allows easy bending and rolling for tangle-free carrying and storage
- Converts audio/video signals from sources supporting USB-C DisplayPort Alt Mode
- Supports Ultra HD resolutions up to 4K @ 60 Hz (4:4:4) for crystal-clear video
- Reversible USB-C plug connects in either direction for immediate no-fuss use
- Plug-and-play operation with no software required for easy, immediate installation

Applications

- Watch 4K video content from a MacBook Pro or Windows laptop on an Ultra HD television, monitor or projector
- Connect a tablet, smartphone or other USB-C source to a conference table's A/V box to give a video presentation on a large screen
- Play online or PC video games that display optimal graphics
- Link an HDTV to your PC for use as a 4K monitor
- Add a secondary monitor to the laptop or Chromebook in your office or home workspace

System Requirements

- Source device with USB-C or Thunderbolt 3 port that supports USB DisplayPort Alternate



Mode

- Display device with DisplayPort input
- DisplayPort cable (M/M) that supports 4K 60 Hz resolutions

Package Includes

- U444-F5N-DP4K6 USB-C to DisplayPort Flat Adapter Cable, M/F, Black, 5 in.
- Instruction sheet

Specifications

OVERVIEW	
UPC Code	037332255396
INPUT	
Cable Length (ft.)	0.42
Cable Length (m)	0.127
Cable Length (in.)	5
Cable Length (cm)	12.7
BATTERY	
Battery Charging (5V/1.5A Port)	No
USER INTERFACE, ALERTS & CONTROLS	
LED Indicators	N/A
PHYSICAL	
Color	Black
Material of Construction	FPC
Shipping Dimensions (hwd / in.)	9.00 x 7.00 x 0.50
Shipping Weight (lbs.)	0.04
Unit Packaging Type	Polybag
ENVIRONMENTAL	



Operating Temperature Range	14 to 140°F (-10 to 60°C)
Storage Temperature Range	-4 to 158°F (-20 to 70°C)
Operating Humidity Range	10 to 85% RH
Storage Humidity Range	10 to 85% RH
CONNECTIONS	
Side A - Connector 1	USB C (MALE)
Side B - Connector 1	DISPLAYPORT (FEMALE)
FEATURES & SPECIFICATIONS	
Max Supported Video Resolution	3840 x 2160 @ 60 Hz
Displayport Specification	1.2
HDCP Specification	2.0
USB Specification	USB 3.0 (up to 5 Gbps); USB 3.1 Gen 1 (up to 5 Gbps)
Driver Required	No
Max Supported Color Depth	36-bit Deep Color
3D Video Supported	Yes
Technology	DisplayPort; USB; USB 3.1 (Gen 1)
SPECIAL FEATURES	
HDR Support	No
STANDARDS & COMPLIANCE	
Certifications	CE, FCC, RoHS, REACH
WARRANTY	
Product Warranty Period (Worldwide)	3-year limited warranty

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>