

## USB-C to HDMI Flat Adapter Cable (M/F) - 4K 60 Hz, UHD, HDR, Thunderbolt 3 Compatible, Black, 5 in.

MODEL NUMBER: U444-F5N-HDR



Flat USB-C to HDMI cable connects an HDMI monitor to your MacBook Pro, Windows laptop or tablet's USB-C or Thunderbolt 3 port.

### Features

**Flat USB-C to HDMI Adapter Connects to Your Laptop's USB-C or Thunderbolt 3 Port** This USB Type-C to HDMI adapter (M/F) connects to an HDMI cable to add an HDMI monitor to the USB-C or Thunderbolt 3 port on your MacBook Pro, Windows laptop, tablet, smartphone or PC. It's ideal for multitasking, presenting video at trade shows and conferences, editing documents, playing online games and watching movies on a larger screen.

**Flat FPC Design Allows Easy Handling and Storage** The flat, bendable FPC (Flexible Printed Circuit) body helps the cable connect to devices in tight spaces or around obstacles. It rolls easily for tangle-free storage in your backpack or laptop bag.

**Supports USB-C DisplayPort Alternate Mode for Converting Audio/Video Signals** By connecting the USB-C connector to a source device that supports USB DisplayPort Alt Mode, you can output 4K video and digital audio to an HDMI monitor, television or projector without installing special software drivers.

**Transmits Crystal-Clear 4K Video with Digital Audio and 4:4:4 Color** The U444-F5N-HDR supports Ultra HD video resolutions up to 4K at 60 Hz, as specified in HDMI 2.0. The adapter supports 36-bit Deep Color and HDR video, providing a wide range of vibrant colors with richer contrast, brighter whites and deeper blacks that pop on your 4K display. HDCP 2.2 compliance allows you to stream 4K Amazon and Netflix content with no complications. This adapter supports 4:4:4 chroma subsampling for top-level PC gaming or using your HDTV as a PC monitor.

**Reversible USB-C Connector Attaches in Either Direction** Unlike traditional USB cables that connect in only one direction, the reversible USB-C male connector plugs into a USB-C or Thunderbolt 3 port in either direction for an instant connection every time.

**Ready to Use Right from the Package, So You Can Plug and Play Immediately** The plug-and-play adapter is specifically designed for use with the MacBook Pro, Windows laptops and other devices equipped with a USB-C or Thunderbolt 3 port. It requires no software or external power. The five-inch cable fits into your pocket, briefcase or laptop bag for connecting to HDMI monitors anywhere.

### Highlights

- Flexible flat design allows easy bending and rolling for tangle-free carrying and storage
- Converts audio/video signals from sources supporting USB-C DisplayPort Alt Mode
- Delivers Ultra HD resolutions up to 4K @ 60 Hz (4:4:4) for crystal-clear video, as specified in HDMI 2.0
- Supports High Dynamic Range (HDR) for richer contrast and expanded color accuracy
- Reversible USB-C plug connects in either direction for immediate no-fuss use

### Applications

- Watch 4K video content from a MacBook Pro or Windows laptop on an Ultra HD television, monitor or projector
- Connect a tablet, smartphone or other USB-C source to a conference table's A/V box to give a video presentation on a large screen
- Play online or PC video games that display optimal graphics
- Link an HDTV to your PC for use as a 4K monitor
- Add a secondary monitor to the laptop or Chromebook in your office or home workspace

### System Requirements

- Source device with USB-C or Thunderbolt 3 port that supports



USB DisplayPort Alternate  
Mode

- Display device with HDMI input
- HDMI cable (M/M) that supports 4K 60 Hz resolutions

**Package Includes**

- U444-F5N-HDR USB-C to HDMI Flat Adapter Cable, M/F, Black, 5 in.
- Instruction sheet

## Specifications

OVERVIEW	
UPC Code	037332255402
INPUT	
Cable Length (ft.)	0.42
Cable Length (m)	0.127
Cable Length (in.)	5
Cable Length (cm)	12.7
BATTERY	
Battery Charging (5V/1.5A Port)	No
USER INTERFACE, ALERTS & CONTROLS	
LED Indicators	N/A
PHYSICAL	
Color	Black
Material of Construction	FPC
Shipping Dimensions (hwd / in.)	9.00 x 7.00 x 0.50
Shipping Weight (lbs.)	0.04
Unit Packaging Type	Polybag
ENVIRONMENTAL	



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
www.tripplite.com

Operating Temperature Range	14 to 140°F (-10 to 60°C)
Storage Temperature Range	-4 to 158°F (-20 to 70°C)
Operating Humidity Range	10% to 85% RH
Storage Humidity Range	10% to 85% RH
<b>CONNECTIONS</b>	
Side A - Connector 1	USB C (MALE)
Side B - Connector 1	HDMI (FEMALE)
<b>FEATURES &amp; SPECIFICATIONS</b>	
Max Supported Video Resolution	4K @ 60 Hz
HDMI Specification	2.0
HDCP Specification	1.4; 2.2
USB Specification	USB 3.1 Gen 1 (up to 5 Gbps)
Driver Required	No
Max Supported Color Depth	36-bit Deep Color
3D Video Supported	Yes
Technology	HDMI; HDR; Thunderbolt; USB
Chroma Sub Sampling	4:2:2; 4:4:4
<b>SPECIAL FEATURES</b>	
HDR Support	Yes
<b>STANDARDS &amp; COMPLIANCE</b>	
Certifications	CE, FCC, RoHS, REACH
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	3-year limited warranty

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>