

## USB-C to VGA Flat Adapter Cable (M/F) - 1920 x 1200 60 Hz, Thunderbolt 3 Compatible, Black, 5 in.

MODEL NUMBER: U444-F5N-VGA



Flat USB-C to VGA cable connects a VGA monitor to your MacBook Pro, Windows laptop or tablet's USB-C or Thunderbolt 3 port.

### Features

**Flat USB-C to VGA Adapter Connects to Your Laptop's USB-C or Thunderbolt 3 Port**This USB Type-C to VGA adapter (M/F) connects to a VGA cable to add a VGA monitor to the USB-C or Thunderbolt 3 port on your MacBook Pro, Windows laptop, tablet, smartphone or PC. It's ideal for multitasking, presenting video at trade shows and conferences, editing documents, playing online games and watching movies on a larger screen.

**Flat FPC Design Allows Easy Handling and Storage**The flat, bendable FPC (Flexible Printed Circuit) body helps the cable connect to devices in tight spaces or around obstacles. It rolls easily for tangle-free storage in your backpack or laptop bag.

**Supports USB-C DisplayPort Alternate Mode for Converting Video Signals**By connecting the USB-C connector to a source device that supports USB DisplayPort Alt Mode, you can output video to a VGA monitor without installing special software drivers. The U444-F5N-VGA supports video resolutions up to 1920 x 1200 (including 1080p) at 60 Hz.

**Reversible USB-C Connector Attaches in Either Direction**Unlike traditional USB cables that connect in only one direction, the reversible USB-C male connector plugs into a USB-C or Thunderbolt 3 port in either direction for an instant connection every time.

**Ready to Use Right from the Package, So You Can Plug and Play Immediately**The plug-and-play adapter is specifically designed for use with the MacBook Pro, Windows laptops and other devices equipped with a USB-C or Thunderbolt 3 port. It requires no software or external power. The five-inch cable fits into your pocket, briefcase or laptop bag for connecting to VGA monitors anywhere.

### Highlights

- Flexible flat design allows easy bending and rolling for tangle-free carrying and storage
- Converts video signals from sources supporting USB-C DisplayPort Alt Mode
- Supports VGA resolutions up to 1920 x 1200 @ 60 Hz for high-definition video
- Reversible USB-C plug connects in either direction for immediate no-fuss use
- Plug-and-play operation with no software required for easy, immediate installation

### Applications

- Watch 1080p video content from a MacBook Pro or Windows laptop on an HD monitor
- Connect a tablet, smartphone or other USB-C source to a monitor for digital signage at a trade show
- Add a secondary monitor to the laptop or Chromebook in your office or home workspace

### System Requirements

- Source device with USB-C or Thunderbolt 3 port that supports USB DisplayPort Alternate Mode
- Display device with VGA input
- VGA cable (M/M) that supports 1080p resolutions

### Package Includes

- U444-F5N-VGA USB-C to VGA



Flat Adapter Cable, M/F, Black,  
5 in.

- Instruction sheet

## Specifications

OVERVIEW	
UPC Code	037332255419
INPUT	
Cable Length (ft.)	0.42
Cable Length (m)	0.127
Cable Length (in.)	5
Cable Length (cm)	12.7
PHYSICAL	
Color	Black
Material of Construction	FPC
Shipping Dimensions (hwd / in.)	9.00 x 7.00 x 0.50
Shipping Weight (lbs.)	0.04
Unit Packaging Type	Polybag
ENVIRONMENTAL	
Operating Temperature Range	14 to 140°F (-10 to 60°C)
Storage Temperature Range	-4 to 158°F (-20 to 70°C)
Operating Humidity Range	10 to 85% RH
Storage Humidity Range	10 to 85% RH
CONNECTIONS	
Side A - Connector 1	USB C (MALE)
Side B - Connector 1	HD15 (FEMALE)
FEATURES & SPECIFICATIONS	
Max Supported Video Resolution	1920 x 1200 @ 60 Hz (1080p)
USB Specification	USB 3.0 (up to 5 Gbps); USB 3.1 Gen 1 (up to 5 Gbps)
Driver Required	No



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

Max Supported Color Depth	12-bit
3D Video Supported	No
Technology	USB; VGA/SVGA
<b>SPECIAL FEATURES</b>	
HDR Support	No
<b>STANDARDS &amp; COMPLIANCE</b>	
Certifications	CE, FCC, RoHS, REACH
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	3-year limited warranty

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>