

USB-C to VGA Flat Adapter Cable (M/F), 1080p 60 Hz, Thunderbolt 3 Compatible, Black, 5 in. (12.7 cm)

MODEL NUMBER: **U444-F5N-VGA**



Flat USB-C to VGA cable connects a VGA monitor to your MacBook Pro, Windows laptop or tablet's USB-C or Thunderbolt 3 port.

Features

Flat USB-C to VGA Adapter Connects to Your Laptop's USB-C or Thunderbolt 3 Port This USB 3.2 Gen 1 Type-C to VGA adapter (M/F) connects to a VGA cable to add a VGA monitor to the USB-C or Thunderbolt 3 port on your MacBook Pro, Windows laptop, tablet, smartphone or PC. It's ideal for multitasking, presenting video at trade shows and conferences, editing documents, playing online games and watching movies on a larger screen.

Flat FPC Design Allows Easy Handling and Storage The flat, bendable FPC (Flexible Printed Circuit) body helps the cable connect to devices in tight spaces or around obstacles. It rolls easily for tangle-free storage in your backpack or laptop bag.

Supports USB-C DisplayPort Alternate Mode for Converting Video Signals By connecting the USB-C connector to a source device that supports USB DisplayPort Alt Mode, you can output video to a VGA monitor without installing special software drivers. The U444-F5N-VGA supports video resolutions up to 1920 x 1200 (including 1080p) at 60 Hz.

Reversible USB-C Connector Attaches in Either Direction Unlike traditional USB cables that connect in only one direction, the reversible USB-C male connector plugs into a USB-C or Thunderbolt 3 port in either direction for an instant connection every time.

Ready to Use Right from the Package, So You Can Plug and Play Immediately The plug-and-play adapter is specifically designed for use with the MacBook Pro, Windows laptops and other devices equipped with a USB-C or Thunderbolt 3 port. It requires no software or external power. The five-inch cable fits into your pocket, briefcase or laptop bag for connecting to VGA monitors anywhere.

Highlights

- Flexible flat design allows easy bending and rolling for tangle-free carrying and storage
- Converts video signals from sources supporting USB-C DisplayPort Alt Mode
- Supports VGA resolutions up to 1920 x 1200 @ 60 Hz for high-definition video
- Reversible USB-C plug connects in either direction for immediate no-fuss use
- Plug-and-play operation with no software required for easy, immediate installation

Applications

- Watch 1080p video content from a MacBook Pro or Windows laptop on an HD monitor
- Connect a tablet, smartphone or other USB-C source to a monitor for digital signage at a trade show
- Add a secondary monitor to the laptop or Chromebook in your office or home workspace

System Requirements

- Source device with USB-C or Thunderbolt 3 port that supports USB DisplayPort Alternate Mode
- Display device with VGA input
- VGA cable (M/M) that supports 1080p resolutions

Package Includes

- U444-F5N-VGA USB-C to VGA Flat Adapter Cable, M/F, Black, 5 in.
- Instruction sheet

Specifications

OVERVIEW	
UPC Code	037332255419



Powering Business Worldwide

TRIPP LITE
SERIES

Product Type	Passive Cable
Technology	VGA/SVGA
Host Connector	USB C (MALE)
VIDEO	
Video Input	USB C (MALE)
Video Output	HD15 (FEMALE)
Number of Monitors Supported	1
Video Ports	HD15 (FEMALE)
Video Ports Details	DisplayPort 1.2a
Supported Resolutions	1280x720 (720p); 1920x1080 (1080p); 1920x1200
Max Supported Video Resolution	1920 x 1200 (1080p)
Max Supported Color Depth	12-bit
HDR Support	No
3D Video Supported	No
EDID Support	No
DisplayPort Alt Mode	Yes
CONNECTIONS	
Side A - Connector 1	USB C (MALE)
Side B - Connector 1	HD15 (FEMALE)
Connector Plating	Nickel
PHYSICAL	
Color	Black
Material of Construction	FPC
Cable Jacket Color	Black
Cable Jacket Material	TPE
Cable Jacket Rating	VW-1
Cable Length (ft.)	0.42
Cable Length (m)	0.13
Cable Length (in.)	5
Cable Length (cm)	12.7
Shipping Dimensions (hwd / in.)	9.00 x 7.00 x 0.50
Shipping Weight (lbs.)	0.04
Unit Dimensions (hwd / in.)	0.500 x 0.870 x 5.120
Unit Dimensions (hwd / cm)	1.26 x 2.2 x 13.0



Powering Business Worldwide

TRIPP LITE
SERIES

Unit Packaging Type	Polybag
Unit Weight (lbs.)	0.5
Unit Weight (kg)	0.23
ENVIRONMENTAL	
Operating Temperature Range	14° to 140°F (-10° to 60°C)
Storage Temperature Range	-4° to 158°F (-20° to 70°C)
Operating Humidity Range	10% to 85% RH
Storage Humidity Range	10% to 85% RH
FEATURES & SPECIFICATIONS	
USB Specification	USB 3.0 (up to 5 Gbps); USB 3.1 Gen 1 (up to 5 Gbps); USB 3.2 Gen 1 (up to 5 Gbps)
Multi-Resolution Support	Yes
IP68 Rated	No
IP20 Rated	No
Driver Required	No
STANDARDS & COMPLIANCE	
Product Compliance	RoHS; CE (Europe); REACH; FCC (USA)
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	3-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.