



# USB-C Memory Card Reader, 2-in-1 USB-A/USB-C, USB 3.1 Gen 1

MODEL NUMBER: U452-000-SD-A











Transfers memory card data to your MacBook, PC, phone or laptop via your device's USB-A, USB-C or Thunderbolt 3 port.

#### **Features**

High-Speed Data Transfer to Almost Any Desktop or Mobile Devicelf your MacBook, Chromebook, PC, tablet, smartphone or laptop has no built-in memory card reader, but does have a USB-A, USB-C or Thunderbolt 3 port, this USB 3.1 memory card reader is an essential data storage tool. It easily transfers photos, documents, HD video and other files from a wide variety of memory cards to your device. Because this unit has both USB-A and USB-C plugs, you save the expense of buying multiple memory card readers.

**USB Connectors Built Into Either End Connect to Almost Any Device**Just insert an SD or Micro SD card into the USB card reader's slot, and then plug the built-in USB-A or USB-C male connector into your MacBook, Chromebook, PC, tablet, smartphone or laptop to begin reading files. Removable caps protect the connectors from damage and debris.

Immediate Read/Write Access to Almost Any SD or Micro SD CardThe two built-in memory card slots supports all the latest formats, including SDXC (Secure Digital Extended Capacity) and SDHC (Secure Digital High Capacity). An LED next to the slots let you know data is being transferred. The slots are hotswappable, so you can exchange cards while the unit remains connected to your MacBook, Chromebook, PC, tablet, smartphone or laptop.

**Transfers Data at Rapid Speeds Up to 5 Gbps**If your MacBook, Chromebook, PC, tablet, smartphone or laptop has a USB 3.0 port, this memory card reader transfers digital photos and other files at speeds up to 5 Gbps, which is 10 times faster than USB 2.0 card readers. It's backward compatible with previous USB generations, including 2.0 and 1.1, so data can transfer regardless of your device.

Versatile Tool for Use at Home, the Office or on the GoThe compact USB 3.1 memory card reader fits easily into your camera bag or laptop sleeve, so you can access files at a moment's notice. Its plug-and-play technology requires no new software, drivers or external power supply. It's compatible with all USB-enabled operating systems, including Windows and Mac.

**3-Year Warranty and Environmentally Responsible Design**The U452-000-SD-A comes with a 3-year warranty. It's manufactured in compliance with strict RoHS specifications.

# **Highlights**

- Built-in USB-A and USB-C male connectors are compatible with most devices
- USB 3.1 Gen 1 data transfer speeds up to 5 Gbps for fast file sharing
- Supports latest SD and Micro SD formats, including SDXC and SDHC
- Easy plug-and-play operation—no new software or drivers required
- Fits easily into camera bag or laptop sleeve for use anywhere

# **Applications**

- Transferring videos, images and other data between an SD or Micro SD memory card and your MacBook, Chromebook, PC, tablet, smartphone or laptop
- Loading a PowerPoint file onto a memory card at the office for presenting on a different computer on the road
- Storing digital photographs for later upload to your work computer

# **System Requirements**

- MacBook, Chromebook, PC, tablet, smartphone or laptop with USB port (USB 3.0 port required for maximum speeds)
- Compatible with the following memory cards:
- SD Cards: Secure Digital (SD), Elite Pro SD, Extreme III SD, Gaming Edition SD, Platinum II SD, SD Pro, SDHC, SDXC, SD-Max, SD-Pleomax, SD-Pro C, Super SD, Turbo SD, Ultima I SD, Ultima II SD, Ultimate SD, Ultra High Speed SD, Ultra II SD, Ultra II SD Plus, Ultra SD, Ultra-X SD, DV-RS MMC, High Speed MMC/RS-MMC, MCCmobile, MMC Pro, MMCplus, MMCplus Turbo, RS-MMC
- Micro SD Cards: MicroSD (TransFlash), microSDHC

### **Package Includes**

 U452-000-SD-A USB-C Memory Card Reader, 2-in-1 USB-A/USB-C, USB 3.1 Gen 1





# **Specifications**

OVERVIEW		
UPC Code	037332206626	
INPUT		
Bus Powered	Yes	
Product Length (in.)	2.9	
Product Length (cm.)	7.37	
Product Length (ft.)	0.24	
Product Length (m)	0.07	
BATTERY		
Battery Charging (5V/1.5A Port)	No	
CONNECTIONS		
Number of Ports	2	
Side A - Connector 1	USB 3.0 A (MALE)	
Side A - Connector 2	USB C (MALE)	
Side B - Connector 1	SD (FEMALE)	
Side B - Connector 2	MICRO SD (FEMALE)	
Connector Plating	Nickel	
Contact Plating	Gold	
USER INTERFACE, ALERTS & CONTROLS		
LED Indicators	Blue (Power/Data)	
PHYSICAL		
Color	Black	
Material of Construction	ABS	
Cable Length (ft.)	0	
Cable Length (m)	0.00	
Unit Dimensions (hwd / in.)	0.430 x 2.900 x 0.790	
Unit Packaging Type	Вох	
Unit Weight (lbs.)	0.03	
Unit Weight (kg)	0.01	





ENVIRONMENTAL	
Operating Temperature Range	32° to 104°F (0° to 40°C)
Storage Temperature Range	-4° to 140°F (-20° to 60°C)
Relative Humidity	0% to 80% RH, Non-Condensing
FEATURES & SPECIFICATIONS	
USB Specification	USB 3.0 (up to 5 Gbps); USB 3.1 Gen 1 (up to 5 Gbps)
IP68 Rated	No
IP20 Rated	No
UASP Support	No
Auto MDIX Support	No
Full Duplex Support	No
Suspend Mode Support	No
Remote Wakeup Support	No
SD Card Specification	SD; Micro SD
Driver Required	No
STANDARDS & COMPLIANCE	
Product Compliance	RoHS; CE (Europe); REACH; FCC (USA)
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	3-year limited warranty

1000 Eaton Boulevard Cleveland, OH 44122 United States https://tripplite.eaton.com © 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark. All other trademarks are the property of their respective owners.