

USB-C Memory Card Reader, 2-in-1 USB-A/USB-C, USB 3.1 Gen 1

MODEL NUMBER: U452-000-SD-A



Transfers memory card data to your MacBook, PC, phone or laptop via your device's USB-A, USB-C or Thunderbolt 3 port.

Features

High-Speed Data Transfer to Almost Any Desktop or Mobile Device If your MacBook, Chromebook, PC, tablet, smartphone or laptop has no built-in memory card reader, but does have a USB-A, USB-C or Thunderbolt 3 port, this USB 3.1 memory card reader is an essential data storage tool. It easily transfers photos, documents, HD video and other files from a wide variety of memory cards to your device. Because this unit has both USB-A and USB-C plugs, you save the expense of buying multiple memory card readers.

USB Connectors Built Into Either End Connect to Almost Any Device Just insert an SD or Micro SD card into the USB card reader's slot, and then plug the built-in USB-A or USB-C male connector into your MacBook, Chromebook, PC, tablet, smartphone or laptop to begin reading files. Removable caps protect the connectors from damage and debris.

Immediate Read/Write Access to Almost Any SD or Micro SD Card The two built-in memory card slots supports all the latest formats, including SDXC (Secure Digital Extended Capacity) and SDHC (Secure Digital High Capacity). An LED next to the slots let you know data is being transferred. The slots are hot-swappable, so you can exchange cards while the unit remains connected to your MacBook, Chromebook, PC, tablet, smartphone or laptop.

Transfers Data at Rapid Speeds Up to 5 Gbps If your MacBook, Chromebook, PC, tablet, smartphone or laptop has a USB 3.0 port, this memory card reader transfers digital photos and other files at speeds up to 5 Gbps, which is 10 times faster than USB 2.0 card readers. It's backward compatible with previous USB generations, including 2.0 and 1.1, so data can transfer regardless of your device.

Versatile Tool for Use at Home, the Office or on the Go The compact USB 3.1 memory card reader fits easily into your camera bag or laptop sleeve, so you can access files at a moment's notice. Its plug-and-play technology requires no new software, drivers or external power supply. It's compatible with all USB-enabled operating systems, including Windows and Mac.

3-Year Warranty and Environmentally Responsible Design The U452-000-SD-A comes with a 3-year warranty. It's manufactured in compliance with strict RoHS specifications, reflecting Tripp Lite's commitment to environmental responsibility.

Highlights

- Built-in USB-A and USB-C male connectors are compatible with most devices
- USB 3.1 Gen 1 data transfer speeds up to 5 Gbps for fast file sharing
- Supports latest SD and Micro SD formats, including SDXC and SDHC
- Easy plug-and-play operation—no new software or drivers required
- Fits easily into camera bag or laptop sleeve for use anywhere

Applications

- Transferring videos, images and other data between an SD or Micro SD memory card and your MacBook, Chromebook, PC, tablet, smartphone or laptop
- Loading a PowerPoint file onto a memory card at the office for presenting on a different computer on the road
- Storing digital photographs for later upload to your work computer

System Requirements

- MacBook, Chromebook, PC, tablet, smartphone or laptop with USB port (USB 3.0 port required for maximum speeds)
- Compatible with the following memory cards:
 - SD Cards: Secure Digital (SD), Elite Pro SD, Extreme III SD,



Gaming Edition SD, Platinum II SD, SD Pro, SDHC, SDXC, SD-Max, SD-Pleomax, SD-Pro C, Super SD, Turbo SD, Ultima I SD, Ultima II SD, Ultimate SD, Ultra High Speed SD, Ultra II SD, Ultra II SD Plus, Ultra SD, Ultra-X SD, DV-RS MMC, High Speed MMC/RS-MMC, MCCmobile, MMC Pro, MMCplus, MMCplus Turbo, RS-MMC

- Micro SD Cards: MicroSD (TransFlash), microSDHC

Package Includes

- U452-000-SD-A USB-C Memory Card Reader, 2-in-1 USB-A/USB-C, USB 3.1 Gen 1

Specifications

OVERVIEW	
UPC Code	037332206626
INPUT	
Cable Length (ft.)	0
Cable Length (m)	0
Bus Powered	Yes
Product Length (in.)	2.9
Product Length (cm.)	7.37
Product Length (ft.)	0.24
Product Length (m.)	0.07
BATTERY	
Battery Charging (1.2 Port)	No



USER INTERFACE, ALERTS & CONTROLS	
LED Indicators	Blue (Power/Data)
PHYSICAL	
Unit Packaging Type	Box
Unit Dimensions (hwd / in.)	0.43 x 2.9 x 0.79
Unit Weight (lbs.)	0.03
Unit Weight (kg)	0.01
Material of Construction	ABS
Color	Black
ENVIRONMENTAL	
Operating Temperature Range	32 to 104 F (0 to 40 C)
Storage Temperature Range	-4 to 140 F (-20 to 60 C)
Relative Humidity	0% to 80% RH, Non-Condensing
CONNECTIONS	
Ports	2
Side A - Connector 1	USB 3.0 A (MALE)
Side A - Connector 2	USB C (MALE)
Side B - Connector 1	SD (FEMALE)
Side B - Connector 2	MICRO SD (FEMALE)
Connector Plating	Nickel
Contact Plating	Gold
FEATURES & SPECIFICATIONS	
USB Specification	USB 3.0 (up to 5 Gbps); USB 3.1 Gen 1 (up to 5 Gbps)
Driver Required	No
Technology	USB 3.0 (SuperSpeed); USB
SD Card Specification	SD; Micro SD
CERTIFICATIONS	
Certifications	Tested to CE, FCC, RoHS, REACH, ICES
WARRANTY	
Product Warranty Period (Worldwide)	3-year limited warranty



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

© 2019 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:
<https://www.tripplite.com/products/product-certification-agencies>