

USB 3.1 Gen 1 (5 Gbps) 2.5 in. SATA SSD/HDD to USB-A Enclosure Adapter with UASP Support

MODEL NUMBER: **U457-025-AG2**



Durable lightweight enclosure connects a 2.5 in. SATA SSD or HDD to your computer's USB-A port and performs fast file transfers at USB 3.1 Gen 1 speeds. UASP-enabled for 70% more speed with UASP host controller.

Description

The U457-025-AG2 USB 3.1 Gen 1 (5 Gbps) SATA SSD/HDD to USB-A Enclosure Adapter lets you connect a high-performance SATA solid state drive (SSD) or hard disk drive (HDD) to a computer or laptop with a USB-A port. Not only does it support USB 3.1 Gen 1 data transfer rates up to 5 Gbps, but it reads data up to 70 percent faster and writes up to 40 percent faster when connected to a UASP-enabled host controller.

Recommended for storing and sharing large files, such as photos, music and video files, the U457-025-AG2 accepts 2.5-inch SATA drives up to 2 TB. You can access data on an older SATA drive, or use a new SATA drive for additional storage space. The adapter is plug-and-play, so no software, drivers or external power supply is required, and it is backward compatible with previous USB generations. A blue LED indicates data is being read, written or transferred. Slim aluminum case stores conveniently in a backpack or laptop bag for use anywhere.

Features

Connects an Internal SATA Drive to Your Computer's USB-A Port

- Recommended for storing and sharing large photo, music and video files
- Supports USB 3.1 Gen 1 data transfer rates up to 5 Gbps
- Features UASP for performance up to 70% faster when connected to UASP-enabled host controller
- Compatible with all USB-enabled operating systems

Compatible with 2.5 in. SATA Drives Up to 2 TB

- Accepts SATA III, II and I SSDs and HDDs

Highlights

- Compatible with 2.5 in. SATA SSDs and HDDs up to 2 TB
- Supports USB 3.1 Gen 1 data transfer rates up to 5 Gbps
- Works up to 70% faster when connected to UASP host controller
- Durable slim design perfectly sized for backpack or laptop bag
- Plug-and-play—no software, drivers or external power supply

System Requirements

- Computer with USB port (USB 3.1 Gen 1 port required for maximum speed)
- 2.5 in. SATA SSD or HDD (9.5 mm max height)

Package Includes

- U457-025-AG2 USB 3.1 Gen 1 SATA SSD/HDD to USB-A Enclosure Adapter
- USB 3.1 Gen 1 Micro-B to USB-A cable, 2 ft.
- Mini screwdriver
- (2) Screws
- Storage sleeve
- Owner's manual



- Will support higher-capacity drives when available
- Backward compatible with previous USB generations
- Blue LED indicates drive data is being read, written or transferred

Designed for Immediate Use

- Plug and play—no software, drivers or external power supply needed
- Durable slim aluminum case perfectly sized for backpack or laptop bag
- Enclosed housing protects drive in applications requiring more durability
- USB 3.1 Gen 1 cable included

Specifications

OVERVIEW	
UPC Code	037332202437
Drives Supported	2.5" HDD and SSD
INPUT	
Bus Powered	Yes
USER INTERFACE, ALERTS & CONTROLS	
LED Indicators	Blue (Read, Write, Power)
PHYSICAL	
Color	Black
Material of Construction	Aluminum
Shipping Dimensions (hwd / cm)	4.80 x 18.11 x 12.80
Shipping Dimensions (hwd / in.)	1.89 x 7.13 x 5.04
Shipping Weight (kg)	0.06
Shipping Weight (lbs.)	0.14
Unit Dimensions (hwd / cm)	1.3 x 12.9 x 7.5
Unit Dimensions (hwd / in.)	0.51 x 5.1 x 3
Unit Packaging Type	Box
Unit Weight (kg)	0.06
Unit Weight (lbs.)	0.14
ENVIRONMENTAL	
Operating Temperature Range	50 to 122 F (10 to 50 C)



Storage Temperature Range	32 to 149 F (0 to 65 C)
Relative Humidity	10% to 80% RH, Non-Condensing
BTUs	17.1 BTU/Hr
Power Consumption (Watts)	5
CONNECTIONS	
Ports	1
Side A - Connector 1	USB 3.0 A (MALE)
Side B - Connector 1	22 PIN SATA + POWER (FEMALE)
Connector Plating	Nickel
Contact Plating	Nickel
FEATURES & SPECIFICATIONS	
USB Specification	USB 3.0 (up to 5 Gbps); USB 3.1 Gen 1 (up to 5 Gbps)
Driver Required	No
UASP Support	Yes
Technology	SATA/eSATA; USB; USB 3.0 (SuperSpeed); USB 3.1 (Gen 1)
CERTIFICATIONS	
Certifications	Tested to CE, FCC, RoHS, REACH
WARRANTY	
Product Warranty Period (Worldwide)	3-year limited warranty

© 2019 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>