

4-Port USB-C Hub, USB 3.x (5Gbps), 4x USB-A Ports, USB Micro-B Power Input, Silver

MODEL NUMBER: **U460-004-4A**



Adds USB-A ports to the USB-C or Thunderbolt 3 port on your tablet, laptop, notebook, MacBook, Chromebook, smartphone or PC.

Description

The U460-004-4A USB 3.1 Gen 1 USB-C Portable Hub expands the potential of your tablet, laptop, Chromebook, MacBook, smartphone or PC's USB-C or Thunderbolt 3 port. It's ideal for adding a thumb drive and other USB peripherals and charging mobile devices—all at the same time.

The plug-and-play U460-004-4A requires no software, drivers or external power. Connect the reversible USB-C plug to your source device's USB-C or Thunderbolt 3 port. The fumble-free USB-C plug connects in either direction to ensure fast, easy connection every time.

Four USB-A ports accept USB peripherals, such as a flash drive, mouse, keyboard or printer. Each port supports up to 5V/1.5A (7.5W) for fast charging of mobile devices. They also support fast USB 3.1 Gen 1 data transfer rates up to 5 Gbps and are backward compatible with previous USB generations, so you can continue using older peripherals while getting high-speed performance from new devices.

A USB Micro-B port connects to an optional external USB power adapter to provide the hub with additional power if needed.

Features

Turn Your Device's USB-C Port into a Workstation

- Ideal for adding USB peripherals and powering and charging a mobile device simultaneously
- Plug-and-play operation with no software, drivers or external power required
- Lightweight aluminum housing about the size of a credit card for easy carrying in a pocket, purse or laptop bag

Connect USB Peripherals

- 4 USB-A ports accept flash drives, mice, keyboards, printers and other USB peripherals
- Supports up to 5V/1.5A (7.5W) for fast charging of mobile devices
- Supports USB 3.1 Gen 1 data transfer rates up to 5 Gbps
- Backward compatible with USB 2.0 and USB 1.1

Note: Host must support USB OTG (On-the-Go)

Extra Port for Extra Power

- USB Micro-B port connects to optional external power adapter to provide hub with additional power if needed

Built-In Cable with Reversible USB-C Connector

Highlights

- Supports USB 3.1 Gen 1 data transfer rates up to 5 Gbps
- USB-A ports provide up to 1.5A each for charging devices
- USB Micro-B port connects to optional adapter for extra power
- Reversible USB-C plug connects in either direction
- Plug-and-play operation with no software or drivers required

System Requirements

- Source device with USB-C or Thunderbolt 3 port

Package Includes

- U460-004-4A USB 3.1 Gen 1 USB-C Portable Hub



Powering Business Worldwide



- Fumble-free reversible USB-C plug connects in either direction for quick connection every time

Specifications

| OVERVIEW | |
|---------------------------------|------------------------------------|
| UPC Code | 037332190208 |
| Product Type | Hub |
| Technology | USB 3.x |
| Host Connector | USB C (MALE) |
| VIDEO | |
| Number of Monitors Supported | 0 |
| Extended Mode | No |
| Mirror Mode | No |
| DATA | |
| Data Ports | (4) USB A (FEMALE) |
| Data Ports Details | (4) USB-A - USB 3.2 Gen 1 (5 Gbps) |
| INPUT | |
| Bus Powered | Yes |
| Product Length (in.) | 14.4 |
| Product Length (cm.) | 36.58 |
| Product Length (ft.) | 1.2 |
| Product Length (m) | 0.37 |
| BATTERY | |
| Battery Charging (5V/1.5A Port) | Yes |
| POWER | |
| Power Consumption (Watts) | 0.7 |
| CONNECTIONS | |
| Number of Ports | 5 |
| Side A - Connector 1 | USB C (MALE) |
| Side B - Connector 1 | (4) USB 3.0 A (FEMALE) |
| Side B - Connector 2 | MICRO-USB B (FEMALE) |
| Connector Plating | Nickel |



Powering Business Worldwide

TRIPP-LITE
by **EAT•N**

| CHARGING | |
|---------------------------------------|--|
| Total Charging Watts | 7.5 |
| Charging Ports | USB-A: 5V 1.5A (7.5W) |
| Charging Ports / Amps | (4) 1.5A |
| PHYSICAL | |
| Color | Silver |
| Material of Construction | Aluminum |
| Cable Jacket Rating | VW-1 |
| Shipping Dimensions (hwd / in.) | 1.20 x 4.90 x 3.90 |
| Shipping Dimensions (hwd / cm) | 3.05 x 12.45 x 9.91 |
| Shipping Weight (lbs.) | 0.22 |
| Shipping Weight (kg) | 0.10 |
| Unit Dimensions (hwd / in.) | 0.000 x 0.000 x 0.000 |
| Unit Packaging Type | Box |
| Unit Weight (lbs.) | 0.16 |
| Unit Weight (kg) | 0.07 |
| ENVIRONMENTAL | |
| Operating Temperature Range | 32° to 122°F (0° to 50°C) |
| Storage Temperature Range | 14° to 167°F (-10° to 75°C) |
| Relative Humidity | 0% to 85% RH, Non-Condensing |
| BTUs | 2.4 BTU/Hr |
| Power Provided to Connected Device(s) | Up to 5V 1.5A (7.5W) per USB Port |
| FEATURES & SPECIFICATIONS | |
| USB Hub Ports | Yes |
| Number of USB Hub Ports | 4 |
| USB Specification | USB 3.0 (up to 5 Gbps); USB 3.1 Gen 1 (up to 5 Gbps); USB 3.2 Gen 1 (up to 5 Gbps) |
| UASP Support | No |
| Auto MDIX Support | No |
| Full Duplex Support | No |
| Suspend Mode Support | No |
| Remote Wakeup Support | No |
| Driver Required | No |

| STANDARDS & COMPLIANCE | |
|-------------------------------------|-------------------------------------|
| TAA Compliant Option | N |
| Product Compliance | RoHS; CE (Europe); REACH; FCC (USA) |
| WARRANTY & SUPPORT | |
| Product Warranty Period (Worldwide) | 3-year limited warranty |

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.