



# 4-Port USB-C Hub, USB 3.x (5Gbps), 4x USB-A Ports, Black

MODEL NUMBER: U460-004-4AB











USB 3.1 Type-C hub adds 4 USB-A ports to your laptop, MacBook, Chromebook or other compatible device.

#### **Features**

**USB 3.1 Type-C Hub Connects to Your Device's USB-C or Thunderbolt 3 Port**This USB-C hub expands the potential of your tablet, laptop, Chromebook, MacBook, smartphone or PC's USB-C or Thunderbolt 3 port. It's ideal for adding a thumb drive, external hard drive, digital camera, MP3 player and other USB peripherals.

Connects Up to 4 USB-A PeripheralsFour USB-A ports accept USB peripherals, such as a flash drive, mouse, keyboard or printer, and all four provide up to 1.5A for charging smartphones and other mobile devices. All ports support fast USB 3.1 Gen 1 data transfer rates up to 5 Gbps and are backward compatible with previous USB generations, so you can continue using older peripherals while getting high-speed performance from new devices.Note: Host must support USB OTG (On-the-Go)Built-In USB-C Cable Connects in Either Direction

Connect the reversible USB-C plug to your source device's Thunderbolt 3 or USB Type-C connector. The fumble-free USB-C plug connects in either direction to ensure fast, easy connection every time.

**Ready to Use Right Out of the Package**The plug-and-play USB 3.1 Type-C hub requires no software, drivers or external power. The lightweight case fits easily into a pocket, briefcase or laptop bag for connecting on the go.

**3-Year Warranty and Environmentally Responsible Design**The U460-004-4AB comes with a 3-year warranty. It's manufactured in compliance with strict RoHS specifications, reflecting commitment to environmental responsibility.

#### **Highlights**

- Supports USB 3.1 Gen 1 for fast data transfers up to 5 Gbps
- Accepts up to 4 USB peripherals, turning your laptop into a mini workstation
- Reversible USB-C plug connects in either direction for immediate no-fuss use
- USB ports provide up to 5V/1.5A (7.5W) for charging smartphones and other devices
- Easy installation with plug-andplay operation—no software required

#### **Applications**

- Transfer files to and from a USB thumb drive or external hard drive
- Connect your smartphone or other mobile device to build up a full charge
- Attach a USB headset/microphone for recording your podcast
- Write a report using a USB keyboard with your tablet or Android smartphone

### **System Requirements**

Tablet, laptop, Chromebook, MacBook, smartphone or PC with USB-C or Thunderbolt 3 port.

#### **Package Includes**

U460-004-4AB 4-Port USB 3.1 Hub, 4x USB-A, Thunderbolt -Black

## **Specifications**

OVERVIEW		
UPC Code	037332209580	
Product Type	Hub	





Technology	USB 3.x	
Host Connector	USB C (MALE)	
VIDEO		
Number of Monitors Supported	0	
Extended Mode	No	
Mirror Mode	No	
DATA		
Data Ports	(4) USB A (FEMALE)	
Data Ports Details	(4) USB-A - USB 3.2 Gen 1 (5 Gbps)	
INPUT		
Built-In Cable Length (ft.)	0.656	
Built-In Cable Length (m)	0.2	
Built-In Cable Length (in.)	7.87	
Built-In Cable Length (cm)	20	
Bus Powered	Yes	
Product Length (in.)	11.7	
Product Length (cm.)	29.72	
Product Length (ft.)	0.98	
Product Length (m)	0.3	
BATTERY		
Battery Charging (5V/1.5A Port)	Yes	
POWER		
Power Consumption (Watts)	0.7	
CONNECTIONS		
Number of Ports	4	
Side A - Connector 1	USB C (MALE)	
Side B - Connector 1	(4) USB 3.0 A (FEMALE)	
Connector Plating	Nickel	
USER INTERFACE, ALERTS & CONTROLS		
LED Indicators	White (Connection to Power)	
CHARGING		





Total Charging Watts	7.5	
Charging Ports	USB-A: 5V 1.5A (7.5W)	
Charging Ports / Amps	(4) 1.5A	
PHYSICAL		
Color	Black	
Material of Construction	Plastic	
Cable Jacket Rating	VW-1	
Shipping Dimensions (hwd / in.)	1.06 x 3.00 x 5.70	
Shipping Weight (lbs.)	0.20	
Unit Dimensions (hwd / in.)	0.840 x 3.800 x 1.200	
Unit Dimensions (hwd / cm)	2.14 x 9.65 x 3.05	
Unit Packaging Type	Box	
Unit Weight (lbs.)	0.09	
Unit Weight (kg)	0.04	
ENVIRONMENTAL		
Operating Temperature Range	32° to 113°F (0° to 45°C)	
Storage Temperature Range	14° to 158°F (-10° to 70°C)	
Relative Humidity	20% to 80% RH, Non-Condensing	
BTUs	2.4 BTU/Hr	
Power Provided to Connected Device(s)	Up to 5V 1.5A (7.5W) per USB Port	
FEATURES & SPECIFICATIONS		
USB Hub Ports	Yes	
Number of USB Hub Ports	4	
USB Specification	USB 3.0 (up to 5 Gbps); USB 3.1 Gen 1 (up to 5 Gbps); USB 3.2 Gen 1 (up to 5 Gbps)	
UASP Support	No	
Auto MDIX Support	No	
Full Duplex Support	No	
Suspend Mode Support	No	
Remote Wakeup Support	No	
Driver Required	No	
STANDARDS & COMPLIANCE		
TAA Compliant Option	N	
Product Compliance	RoHS; CE (Europe); REACH; FCC (USA)	





WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	3-year limited warranty

1000 Eaton Boulevard Cleveland, OH 44122 United States https://tripplite.eaton.com © 2024 Eaton. All Rights Reserved. Eaton is a registered trademark. All other trademarks are the property of their respective owners.