

4-Port USB-C Hub with Power Delivery, USB-C to 4x USB-A Ports, USB 3.0, Black

MODEL NUMBER: U460-004-4AB-C



USB 3.1 Type-C hub adds USB-A and USB-C charging ports to your laptop, MacBook, Chromebook or other compatible device.

Features

USB 3.1 Type-C Hub Connects to Your Device's USB-C or Thunderbolt 3 Port This USB-C hub with PD Charging expands the potential of your tablet, laptop, Chromebook, MacBook, smartphone or PC's USB-C or Thunderbolt 3 port. It's ideal for adding a thumb drive and other USB peripherals or powering and charging a PD Charging-compliant mobile device—all at the same time.

Connects Up to 4 USB-A Peripherals Four USB-A ports accept USB peripherals, such as a flash drive, mouse, keyboard or printer, and the dedicated USB-A fast-charging port provides up to 5V 1.5A (7.5W) for charging smartphones and other mobile devices. All ports support fast USB 3.1 Gen 1 data transfer rates up to 5 Gbps and are backward compatible with previous USB generations, so you can continue using older peripherals while getting high-speed performance from new devices. **Note:** Host must support USB OTG (On-the-Go).

Charges a Connected Device The USB-C Power Delivery (PD) port provides power and charging to the PD Charging-compliant device (such as a MacBook, Chromebook or Android smartphone) the USB-C hub is connected to. Connect the device's AC wall charger to the USB-C PD port, which supports power input up to 60W. **Note:** USB-C PD port does not support Quick Charge (QC).

Built-In USB-C Cable Connects in Either Direction Connect the reversible USB-C plug to your source device's Thunderbolt 3 or USB Type-C connector. The fumble-free USB-C plug connects in either direction to ensure fast, easy connection every time.

Ready to Use Right Out of the Package The plug-and-play USB 3.1 Type-C hub requires no software, drivers or external power. The compact unit fits easily into a pocket, briefcase or laptop bag for connecting on the go.

Specifications

Highlights

- Supports USB 3.1 Gen 1 for fast data transfers up to 5 Gbps
- Accepts up to 4 USB peripherals, turning your laptop into a mini workstation
- USB-A fast-charging port provides up to 5V 1.5A (7.5W) of power
- Powers and charges PD Charging-compliant devices, such as MacBooks and Chromebooks
- Reversible USB-C plug connects in either direction for immediate no-fuss use

Applications

- Charge your notebook or laptop by connecting its wall charger to the USB-C PD Charging port
- Transfer files to and from a USB thumb drive or external hard drive
- Attach a USB headset/microphone for recording your podcast
- Write a report using a USB keyboard with your tablet or Android smartphone

System Requirements

- Tablet, laptop, Chromebook, MacBook, smartphone or PC with USB-C or Thunderbolt 3 port

Package Includes

- U460-004-4AB-C 4-Port USB 3.1 Hub, Black
- Owner's manual

OVERVIEW	
UPC Code	037332209214
Host Connector	USB C (MALE)
DATA	
Data Ports	(4) USB A (FEMALE)
Data Ports Details	(4) USB-C - USB 3.2 Gen 1 (5 Gbps)
INPUT	
Built-In Cable Length (ft.)	0.36
Built-In Cable Length (m)	0.11
Built-In Cable Length (in.)	4.33
Bus Powered	Yes
Product Length (in.)	6
Product Length (cm.)	15.24
Product Length (ft.)	0.5
Product Length (m.)	0.15
BATTERY	
Battery Charging (5V/1.5A Port)	Yes
POWER	
Power Consumption (Watts)	2.2
USB Power Delivery (PD) Charging Support	Yes
USB Power Delivery (PD) Charging Specification	2.0
CHARGING	
Total Charging Watts	60
Charging Ports	USB-A: 5V 1.5A (7.5W); USB-C: 60W (20V 3A) Power Delivery (PD 2.0)
Charging Ports / Amps	1.5A; 3A
PHYSICAL	
Color	Black
Material of Construction	Plastic
Cable Jacket Rating	VW-1
Cable Outer Diameter (OD)	3.9mm

Wire Gauge (AWG)	28/34
Shipping Dimensions (hwd / in.)	0.90 x 3.90 x 5.60
Shipping Weight (lbs.)	0.10
Unit Dimensions (hwd / in.)	0.000 x 0.000 x 0.000
Unit Packaging Type	Box
Unit Weight (lbs.)	0.1
Unit Weight (kg)	0.05
ENVIRONMENTAL	
Operating Temperature Range	32 to 113 F (0 to 45 C)
Storage Temperature Range	14 to 158 F (-10 to 70 C)
Relative Humidity	10% to 90% RH, Non-Condensing
BTUs	7.5 BTU/Hr
Power Provided to Connected Device(s)	Up to 20V 3A (60W) Input (USB-C), 5V 1.5A (7.5W) Output USB port, 5V 0.9A (4.5W) Output per USB port
CONNECTIONS	
Number of Ports	5
Side A - Connector 1	USB C (MALE)
Side B - Connector 1	(4) USB 3.0 A (FEMALE)
Side B - Connector 2	USB C (FEMALE)
Connector Plating	Nickel
FEATURES & SPECIFICATIONS	
USB Specification	USB 3.0 (up to 5 Gbps); USB 3.1 Gen 1 (up to 5 Gbps)
Driver Required	No
UASP Support	No
Auto MDIX Support	No
Full Duplex Support	No
Suspend Mode Support	No
Remote Wakeup Support	No
STANDARDS & COMPLIANCE	
Product Compliance	RoHS; CE (Europe); REACH; FCC (USA)
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	3-year limited warranty



1000 Eaton Boulevard
Cleveland, OH 44122
United States



© 2023 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.