

## 4-Port USB-C Hub with Power Delivery, USB-C to 4x USB-A Ports, USB 3.0, Black

MODEL NUMBER: U460-004-4AB-C



USB 3.1 Type-C hub adds USB-A and USB-C charging ports to your laptop, MacBook, Chromebook or other compatible device.

### Features

#### USB 3.1 Type-C Hub Connects to Your Device's USB-C or Thunderbolt 3 Port

This USB-C hub with PD Charging expands the potential of your tablet, laptop, Chromebook, MacBook, smartphone or PC's USB-C or Thunderbolt 3 port. It's ideal for adding a thumb drive and other USB peripherals or powering and charging a PD Charging-compliant mobile device—all at the same time.

#### Connects Up to 4 USB-A Peripherals

Four USB-A ports accept USB peripherals, such as a flash drive, mouse, keyboard or printer, and the dedicated USB-A fast-charging port provides up to 5V/1.5A (7.5W) for charging smartphones and other mobile devices. All ports support fast USB 3.1 Gen 1 data transfer rates up to 5 Gbps and are backward compatible with previous USB generations, so you can continue using older peripherals while getting high-speed performance from new devices.

Note: Host must support USB OTG (On-the-Go)

#### Charges a Connected Device

The USB-C Power Delivery (PD) port provides power and charging to the PD Charging-compliant device (such as a MacBook, Chromebook or Android smartphone) the USB-C hub is connected to. Connect the device's AC wall charger to the USB-C PD port, which supports power input up to 60W.

Note: USB-C PD port does not support Quick Charge (QC).

#### Built-In USB-C Cable Connects in Either Direction

Connect the reversible USB-C plug to your source device's Thunderbolt 3 or USB Type-C connector. The fumble-free USB-C plug connects in either direction to ensure fast, easy connection every time.

#### Ready to Use Right Out of the Package

The plug-and-play USB 3.1 Type-C hub requires no software, drivers or external power. The compact unit fits easily into a pocket, briefcase or laptop bag for connecting on the go.

#### 3-Year Warranty and Environmentally Responsible Design

The U460-004-4AB-C comes with a 3-year warranty. It's manufactured in compliance with strict RoHS specifications, reflecting Tripp Lite's commitment to environmental responsibility.

### Highlights

- Supports USB 3.1 Gen 1 for fast data transfers up to 5 Gbps
- Accepts up to 4 USB peripherals, turning your laptop into a mini workstation
- USB-A fast-charging port provides up to 5V/1.5A (7.5W) of fast-charging power.
- Powers and charges PD Charging-compliant devices, such as MacBooks and Chromebooks
- Reversible USB-C plug connects in either direction for immediate no-fuss use
- Easy installation with plug-and-play operation—no software required

### Applications

- Charge your notebook or laptop by connecting its wall charger to the USB-C PD Charging port
- Transfer files to and from a USB thumb drive or external hard drive
- Attach a USB headset/microphone for recording your podcast
- Write a report using a USB keyboard with your tablet or Android smartphone

### System Requirements

- Tablet, laptop, Chromebook, MacBook, smartphone or PC with USB-C or Thunderbolt 3 port



#### Package Includes

- U460-004-4AB-C 4-Port USB 3.1 Hub, 4x USB-A, Thunderbolt 3—PD Charging, Black
- Owner's manual

## Specifications

OVERVIEW	
UPC Code	037332209214
Technology	USB; USB 3.0 (SuperSpeed); USB 3.1 (Gen 1); PD Charging
Host Connector	USB C (MALE)
INPUT	
Built-In Cable Length (ft.)	0.36
Built-In Cable Length (m)	0.11
Built-In Cable Length (in.)	4.33
Bus Powered	Yes
Product Length (in.)	6
Product Length (cm.)	15.24
Product Length (ft.)	0.5
Product Length (m.)	0.15
BATTERY	
Battery Charging (5V/1.5A Port)	Yes
POWER	
USB Power Delivery (PD) Charging Support	Yes
CHARGING	
Charging Ports / Amps	1.5A; 3A
Total Charging Watts	60
PHYSICAL	
Cable Outer Diameter (OD)	3.9mm
Cable Jacket Rating	VW-1



Wire Gauge (AWG)	28/34
Color	Black
Material of Construction	Plastic
Shipping Dimensions (hwd / in.)	0.90 x 3.90 x 5.60
Shipping Weight (lbs.)	0.10
Unit Dimensions (hwd / in.)	0.43 x 3.7 x 1.6
Unit Packaging Type	Box
Unit Weight (kg)	0.05
Unit Weight (lbs.)	0.1
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	32 to 113 °F (0 to 45 °C)
Storage Temperature Range	14 to 158 °F (-10 to 70 °C)
Relative Humidity	10% to 90% RH, Non-Condensing
BTUs	7.5 BTU/Hr
Power Consumption (Watts)	2.2
Power Provided to Connected Device(s)	Up to 20V 3A (60W) Input (USB-C), 5V 1.5A (7.5W) Output USB port, 5V 0.9A (4.5W) Output per USB port
<b>CONNECTIONS</b>	
Ports	5
Side A - Connector 1	USB C (MALE)
Side B - Connector 1	(4) USB 3.0 A (FEMALE)
Side B - Connector 2	USB Type-C (FEMALE)
Connector Plating	Nickel
<b>FEATURES &amp; SPECIFICATIONS</b>	
USB Specification	USB 3.0 (up to 5 Gbps); USB 3.1 Gen 1 (up to 5 Gbps)
Driver Required	No
UASP Support	No
<b>STANDARDS &amp; COMPLIANCE</b>	
Certifications	CE, FCC, RoHS, REACH
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	3-year limited warranty



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>