

6-Port Slim USB Hub, USB 3.2 Gen 2 (10 Gbps) and USB-A 2.0 Hub Ports, USB-C Connector with USB-A Adapter, Black

MODEL NUMBER: U460-006-5A1C



Adds 6 new USB ports to the USB-C or Thunderbolt 3 port on your MacBook, Chromebook, Windows laptop, PC, tablet or smartphone.

Features

USB-C Hub Connects 6 USB Peripherals to Your MacBook or Chromebook

This slim USB-C hub connects up to six USB peripherals to your MacBook, Chromebook, Windows laptop, PC, tablet or smartphone. Expand the potential of your device by connecting multiple USB peripherals that can help you do your job faster, easier and better, such as external storage, keyboard/mouse, USB headset and microphone, power meter and printer.

Transfers Data at Lightning-Fast USB 3.2 Gen 2 Speeds

One USB-C and three USB-A ports transfer data at speeds up to 10 Gbps, which is double the rate of USB 3.2 Gen 1. The USB ports are backward compatible with previous USB generations, so you can continue using older peripherals while getting high-speed performance from new devices. The other two USB-A ports are ideal for connecting a mouse and keyboard. The USB-C port provides 1.5A charging of smartphones and other portable devices.

Ready to Use Right Out of the Package

The plug-and-play USB-C hub is specifically designed for use with the MacBook Pro, Google Chromebook Pixel and other laptops, tablets and devices equipped with a USB-C or Thunderbolt 3 port. It requires no software or external power. The lightweight aluminum case takes up little space on a desktop or workspace, and it fits easily into a pocket, briefcase or laptop bag for connecting on the go. A USB-A adapter is included for connecting to a source device without USB-C or Thunderbolt ports.

Specifications

OVERVIEW	
UPC Code	037332288714
Product Type	USB Hub
Device Compatibility	Chromebook; Computer; Laptop; Tablet

Highlights

- Compact form factor takes up little space on your desktop or workspace
- USB-C port and 3 USB-A ports support USB 3.2 Gen 2 speeds up to 10 Gbps
- 2 USB-A ports support USB 2.0 speeds for connecting a keyboard and mouse
- Built-in USB-A adapter allows hub connection to either USB-C or USB-A laptop port
- Plug-and-play operation with no software required for easy, immediate installation

System Requirements

Source device with USB-C, Thunderbolt 3 or USB-A port (USB 3.2 Gen 2 capability required for 10 Gbps speeds)

Package Includes

- U460-006-5A1C 6-Port Slim USB Hub, Black
- Installation Instructions



Powering Business Worldwide

TRIPP LITE
SERIES

Technology	Thunderbolt; USB 3.x
Country/Region	Global
Host Connector	USB C (MALE)
VIDEO	
Number of Monitors Supported	0
Extended Mode	No
Mirror Mode	No
DATA	
Data Ports	(5) USB A (FEMALE); (1) USB C (FEMALE)
Data Ports Details	(2) USB-A - USB 2.0; (3) USB-A - USB 3.2 Gen 2 (10 Gbps); (1) USB-C - USB 3.2 Gen 2 (10 Gbps)
INPUT	
Built-In Cable Length (ft.)	0.39
Built-In Cable Length (in.)	4.72
Bus Powered	Yes
BATTERY	
Battery Charging (5V/1.5A Port)	Yes
POWER	
Power Source Type	Bus
USB Power Delivery (PD) Charging Support	No
CONNECTIONS	
Number of Ports	6
Side A - Connector 1	USB A (MALE); USB C (MALE)
Side B - Connector 1	(5) USB A (FEMALE)
Side B - Connector 2	(1) USB C (FEMALE)
Connector Plating	Nickel
CHARGING	
Number of Charging Ports	6
Total Charging Watts	7.5
Charging Port Type	(5) USB A (FEMALE); (1) USB C (FEMALE)
Charging Ports	(5) USB-A: 0.9A; (1) USB-C: 5V 1.5A (7.5W)
Charging Ports / Amps	(5) 0.9A; (1) 1.5A



Powering Business Worldwide

TRIPP LITE
SERIES

Compatible Devices	Chromebook; Laptop; Smartphone; Tablet
PHYSICAL	
Color	Black
Material of Construction	TPE + ABS, PC
Cable Jacket Color	Black
Cable Jacket Material	TPE
Cable Outer Diameter (OD)	3.9MM
Wire Gauge (AWG)	34/32/28
Total Number of Ports	6
Shipping Dimensions (hwd / in.)	0.79 x 6.69 x 3.54
Shipping Weight (lbs.)	0.13
Shipping Weight (kg)	0.06
Unit Dimensions (hwd / in.)	0.400 x 5.300 x 1.340
Unit Packaging Type	Box
Unit Weight (lbs.)	0.1
Unit Weight (kg)	0.05
ENVIRONMENTAL	
Operating Temperature Range	14° TO 104° F (-10° TO 40° C)
Storage Temperature Range	14° TO 176° F (-10° TO 80° C)
Operating Humidity Range	10% TO 85% RH, NON-CONDESNING
Storage Humidity Range	25% TO 93% RH, NON-CONDESNING
Power Provided to Connected Device(s)	(x1) USB-C SUPPORTS MAX 1.5A DOWNSTREAM CHARGING; (X5) USB-A PORTS SUPPORT MAX 0.9A DOWNSTREAM CHARGING; 3A TOTAL SHARED BETWEEN HUB PORTS
FEATURES & SPECIFICATIONS	
USB Hub Ports	Yes
Number of USB Hub Ports	6
USB Specification	USB 2.0 (up to 480 Mbps); USB 3.2 Gen 2 (Up to 10 Gbps)
Data Transfer Rate	(4) 10 Gbps; (2) 480 Mbps
Ethernet Support	No
UASP Support	No
Auto MDIX Support	No
Full Duplex Support	No
Suspend Mode Support	No
Remote Wakeup Support	No
Driver Required	No



Powering Business Worldwide

TRIPP LITE
SERIES

STANDARDS & COMPLIANCE	
Product Certifications	EN 55032; EN 55035; ICES (Canada)
Product Compliance	CE (Europe); FCC (USA); REACH; RoHS; UKCA; WEEE
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	3-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.