

4-Port USB-C Hub with Self-Storing Cable and Power Delivery, 2x USB-A, 2x USB-C, 100W PD 3.0, 10Gbps, USB 3.1

MODEL NUMBER: U460-T04-2A2C-2



Adds a USB-C, a USB-C Power Delivery and 2 USB-A ports to the USB-C or Thunderbolt 3 port on your MacBook, PC, tablet or smartphone.

Features

USB-C 3.1 Hub Connects 4 USB Peripherals to Your MacBook or Chromebook

This USB-C hub allows you to connect up to four USB peripherals to your tablet, laptop, notebook, MacBook, Chromebook, smartphone or PC. Not only can you expand the potential of your device by connecting USB peripherals, such as an external hard drive, flash drive, power meter and printer, but you can also power and fast-charge the device through the USB-C Power Delivery (PD) 3.0 port.

PD Charging Port Charges the Connected Device via AC Wall Charger

The USB-C PD charging port provides power output up to 5 amps (100 watts), which is more than sufficient for charging and powering the connected device, such as a MacBook or Chromebook. Just connect the device's AC wall charger to the USB-C PD port to enjoy lightning-fast data transfer speeds up to 10 Gbps. As part of PD 3.0, this unit will support Fast Role Swap. This helps prevent any type of data loss that could possibly occur when the power unexpectedly turns off.

Connects USB Peripherals and Transfers Data at Lightning-Fast USB 3.1 Gen 2 Speeds

In addition to accepting USB peripherals, the dual USB-A 3.0 ports provide up to 0.9 amps each for charging and powering mobile devices. The USB-C data port provides up to 1.5A for charging devices. All four USB ports transfer data at speeds up to 10 Gbps, which is twice as fast as USB 3.1 Gen 1. The USB ports are backward compatible with previous USB generations, so you can continue using older peripherals while getting high-speed performance from new devices.

Self-Storing USB-C Cable Connects in Either Direction

Connect the reversible USB-C plug to your source device's USB-C or Thunderbolt 3 port. The fumble-free USB-C plug connects in either direction to ensure fast, easy connection every time. The six-inch cable wraps into the adapter when not in use, making the unit easy to carry in a briefcase or laptop bag for connecting on the go.

Ready to Use Right Out of the Package

The plug-and-play USB Type-C hub is specifically designed for use with the MacBook, Google Chromebook Pixel and other laptops, tablets and devices equipped with a USB-C or Thunderbolt 3 port. It requires no software, drivers or external power.

Highlights

- USB-C 3.1 Type-C hub is compatible with all USB-C and Thunderbolt 3 devices
- Power Delivery cable provides 5A (100W) power output for charging connected device
- Supports USB 3.1 Gen 2 speeds up to 10 Gbps to ensure lightning-fast data transfers
- Reversible USB-C plug connects in either direction for immediate no-fuss use
- Plug-and-play operation with no software required for easy, immediate installation

Applications

- Charge and power a MacBook, Chromebook, tablet or other USB-C or Thunderbolt 3 device
- Connect up to 4 USB peripherals, such as an external hard drive, flash drive, power meter and printer

System Requirements

- Device with USB-C or Thunderbolt 3 port (USB 3.1 port needed to achieve USB 3.1 speeds)

Package Includes

- U460-T04-2A2C-2 USB 3.1 C Hub, 10 Gbps, Black
- Owner's manual



Specifications

OVERVIEW	
UPC Code	037332236449
Product Type	Hub
Host Connector	USB C (MALE)
VIDEO	
Extended Mode	No
Mirror Mode	No
Number of Monitors Supported	0
DATA	
Data Ports	(2) USB A (FEMALE); (2) USB C (FEMALE)
Data Ports Detail	(2) USB-A - USB 3.2 Gen 2 (10 Gbps); (2) USB-C - USB 3.2 Gen 2 (10 Gbps)
INPUT	
Bus Powered	Yes
Product Length (in.)	6
Product Length (cm.)	15.24
Product Length (ft.)	0.5
Product Length (m.)	0.15
BATTERY	
Battery Charging (5V/1.5A Port)	No
CHARGING	
Charging Ports / Amps	(2) 0.9A; 1.5A; 5A
Charging Ports	USB-C: 100W (20V 5A) Power Delivery (PD 3.0)
USB Power Delivery (PD) Charging Support	Yes
Total Charging Watts	100
USB Power Delivery (PD) Charging Specification	3.0
PHYSICAL	
Cable Jacket Rating	VW-1
Color	Black
Material of Construction	Plastic



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Shipping Dimensions (hwd / in.)	0.00 x 0.00 x 0.00
Shipping Weight (lbs.)	0.00
Unit Dimensions (hwd / in.)	0.55 x 3 x 1.7
Unit Packaging Type	Box
Unit Weight (kg)	0.03
Unit Weight (lbs.)	0.07
ENVIRONMENTAL	
Operating Temperature Range	32 to 113 °F (0 to 45 °C)
Storage Temperature Range	23 to 158 °F (-5 to 70 °C)
Operating Humidity Range	5% ~ 85%
Storage Humidity Range	5% ~ 90%
Power Provided to Connected Device(s)	USB-A Port: 900mA; USB-C: 1.5A; USB-C PD 3.0 Charging Port: 2A
CONNECTIONS	
Ports	4
Side A - Connector 1	USB C (MALE)
Side B - Connector 1	(2) USB 3.0 A (FEMALE)
Side B - Connector 2	(2) USB C (FEMALE)
Connector Plating	Nickel
FEATURES & SPECIFICATIONS	
USB Specification	USB 3.0 (up to 5 Gbps); USB 3.1 Gen 1 (up to 5 Gbps); USB 3.1 Gen 2 (up to 10 Gbps)
Driver Required	No
UASP Support	Yes
Technology	USB; USB 2.0 (High Speed); USB 3.0 (SuperSpeed); USB 3.1 (Gen 2); PD Charging
STANDARDS & COMPLIANCE	
Certifications	RoHS, CE, FCC
WARRANTY	
Product Warranty Period (Worldwide)	3-year limited warranty

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>