

Waber-by-Tripp Lite 4-Outlet Industrial Power Strip, 6-ft. Cord, Locking Switch Cover

MODEL NUMBER: **UL603CB-6**



Highlights

- 4 outlets
- 6 ft. cord
- 7.38" length
- All metal housing
- Lighted on/off switch with locking safety cover

Package Includes

- UL603CB-6 Power Strip
- Warranty information
- Instruction manual

Description

The Waber-by-Tripp Lite UL603CB-6 Power Strip offers a convenient method of power distribution in workbench, wallmount or floor mount applications. Includes 4 NEMA 5-15R output receptacles with 1.25 inch center-to-center spacing, 6 foot AC line cord and keyhole mounting tabs for installation in a wide variety of applications. Corded, multi-outlet strip reduces cabling clutter and enables the connection of multiple electrical devices to a single AC wall socket. Unfiltered electrical pass-through makes UL603CB-6 ideal for distributing alternate waveform UPS or generator power. Features rugged all-metal housing, lighted power switch with transparent guard to prevent accidental shutoff, 15 amp resettable circuit breaker and attractive blue/gray color scheme.

PLUG/OUTLETS - Input: NEMA 5-15P/Output: 4 NEMA 5-15R

ELECTRICAL - 120VAC, 50/60Hz, 15A (Requires standard NEMA 5-15R wall receptacle)

FORMAT - Corded power distribution strip

Features

- Multi-outlet power strip offers convenient power distribution in workbench, wallmount or floor mount applications
- Includes 4 NEMA 5-15R output receptacles with 1.25 inch center-to-center outlet spacing
- Lighted power switch with transparent snap-over guard to prevent accidental shutoff
- Keyhole mounting tabs for installation in a wide variety of applications
- UL1363 (USA), cUL (Canada)
- 15 amp power handling capacity with circuit breaker

Specifications

OVERVIEW	
UPC Code	037332103734



OUTPUT	
Frequency Compatibility	50 / 60 Hz
Output Receptacles	(4) 5-15R
Output (Watts)	1800
Circuit Breaker (amps)	15
Transformer Accommodation	(2) Yes
Outlet Spacing	1.25 in.
Outlet Orientation	Single row of 4
Right-Angle Outlets	No
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	15A 120V
Input Cord Length (ft.)	6
Input Cord Length (m)	1.83
Input Cord Gauge Type	14 gauge; SJT
Voltage Compatibility (VAC)	120
Input Plug Type	NEMA 5-15P
Integrated Cord Clip	No
USER INTERFACE, ALERTS & CONTROLS	
Switches	Lighted 2 position switch controls power to all outlets
Locking Switch Cover	Transparent on/off switch cover prevents accidental turn-off
PHYSICAL	
Shipping Dimensions (hwd / in.)	2.00 x 9.60 x 6.10
Shipping Dimensions (hwd / cm)	5.08 x 24.38 x 15.49
Shipping Weight (lbs.)	1.60
Shipping Weight (kg)	0.73
Unit Dimensions (hwd / in.)	7.38 x 2.5 x 1.5
Unit Dimensions (hwd / cm)	18.75 x 6.4 x 3.8
Material of Construction	Metal
Integrated Keyhole Mounting Slots	Yes (Includes flanges)
Receptacle Color	Black
Color (AC Line Cord)	Black
Color	Gray



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Outlets Measurement (Center to Center)	30mm
Keyhole Slot Mounting Measurement (Center to Center)	Distance between keyhole tabs = 127mm; Distance between end tabs = 201.12mm
Anti-Microbial Protected	No
CERTIFICATIONS	
UL1363 (Power Tap)	UL1363
Canada	cUL
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2019 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>