

Industrial Power Strip, 6-Outlet, 15 ft. (4.6 m) Cord, 5-20P Plug

MODEL NUMBER: **UL620-15**



Highlights

- 6 outlets accept NEMA5-15P or 5-20P input plugs
- 15-ft. (4.57 m) cord
- 12.5" length
- 20-amp circuit breaker
- Lighted master switch
- All metal housing

Package Includes

- UL620-15 Power Strip
- Warranty information
- Instruction manual

Description

The UL620-15 Power Strip offers a convenient method of power distribution in workbench, wall-mount or floor-mount applications. Includes six NEMA 5-15R/20R output receptacles with 1.625-inch center-to-center spacing, 15-foot (4.6-meter) AC line cord and keyhole mounting tabs for installation in a wide variety of applications. Corded, multi-outlet strip reduces cabling clutter and enables the connection of multiple electrical devices to a single AC wall socket. Unfiltered electrical pass-through makes UL620-15 ideal for distributing alternate waveform UPS or generator power. Features rugged all-metal housing, lighted power switch with transparent guard to prevent accidental shutoff, 20A resettable circuit breaker and attractive blue/gray color scheme.

Features

- Multi-outlet power strip offers convenient power distribution in workbench, wallmount or floor mount applications
- Includes 6 NEMA 5-15R/20R output receptacles with 1.625 inch center-to-center outlet spacing
- Lighted power switch with transparent snap-over guard to prevent accidental shutoff
- Keyhole mounting tabs for installation in a wide variety of applications
- UL1363 (USA), cUL (Canada)
- 20 amp power handling capacity with circuit breaker
- 15-ft. (4.57 m) AC line cord

Specifications

OVERVIEW	
UPC Code	037332103703
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	20A 120V



Powering Business Worldwide



Input Cord Gauge Type	12 gauge; SJT
Voltage Compatibility (VAC)	120
Input Plug Type	NEMA 5-20P
Input Cord Length (ft.)	15
Right-Angle Plug	No
Input Cord Length (m)	4.57
Integrated Cord Clip	No
OUTPUT	
Frequency Compatibility	50 / 60 Hz
Output Receptacles	(6) 5-15/20R
Circuit Breaker (amps)	20
Transformer Accommodation	(2) Yes
Outlet Orientation	Single row of 6
Right-Angle Outlets	No
Outlet Spacing	1.625 in.
USER INTERFACE, ALERTS & CONTROLS	
Switches	Lighted 2 position switch controls power to all outlets
Locking Switch Cover	Transparent on/off switch cover prevents accidental turn-off
PHYSICAL	
Color	Gray
Material of Construction	Metal
Power Cord Color	Black
Housing Color	Blue; Gray
Mounting Holes or Slots	Yes
Slot or Hole Mount Measurement (Center to Center)	261.92mm
Outlets Measurement (Center to Center)	1.62 in.
Receptacle Color	Black
Shipping Dimensions (hwd / in.)	2.25 x 15.00 x 6.00
Shipping Dimensions (hwd / cm)	5.72 x 38.10 x 15.24
Shipping Weight (lbs.)	3.81
Shipping Weight (kg)	1.73
Unit Dimensions (hwd / in.)	1.500 x 13.750 x 2.500
Unit Dimensions (hwd / cm)	31.75 x 6.35 x 3.8



Powering Business Worldwide



Outlet Spacing	1.625 in.
Mounting Details	Includes flanges
FEATURES & SPECIFICATIONS	
Antimicrobial	No
Built-In Circuit Breaker	Yes
STANDARDS & COMPLIANCE	
Product Certifications	cUL Listed; UL 1363; UL Listed
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.