

Industrial Power Strip, 10-Outlet, 15 ft. (4.6 m) Cord, Large Plug Spacing

MODEL NUMBER: **UL800CB-15**



Highlights

- 10 outlets
- 15-ft. (4.57 m) cord
- 17.5" length
- Lighted master switch
- All metal housing

Package Includes

- UL800CB-15 Power Strip
- Warranty information
- Instruction manual

Description

The UL800CB-15 Power Strip offers a reliable, convenient method of power distribution for appliances, power tools, lighting and other electrical equipment. Includes 10 NEMA 5-15R output receptacles arranged with traditional wall socket spacing to accept large equipment plugs with minimal outlet blockage. Includes 15-foot (4.6-meter) AC line cord and flat sheet metal flanges for installation in a wide variety of applications. Corded, multi-outlet strip reduces cabling clutter and enables the connection of multiple electrical devices to a single AC wall socket. Unfiltered electrical pass-through makes UL800CB-15 ideal for distributing alternate waveform UPS or generator power. Features rugged all-metal housing, lighted power switch, 15A resettable circuit breaker and attractive blue/gray color scheme.

Features

- Multi-outlet power strip offers reliable, convenient, cost effective method of power distribution for appliances, power tools, lighting and other electrical equipment.
- Includes 10 NEMA 5-15R output receptacles arranged with traditional wall socket spacing to accept large equipment plugs with minimal outlet blockage
- Lighted on/off switch controls power to all outlets
- Keyhole mounting tabs for installation in a wide variety of applications
- UL Recognized Component, Tested to UL1363 (Power Tap), cUL (Canada)
- 15 amp power handling capacity with circuit breaker
- 15-ft. (4.57 m) AC line cord

Specifications

| OVERVIEW | |
|------------------------------------|--------------|
| UPC Code | 037332117724 |
| INPUT | |
| Nominal Input Voltage(s) Supported | 120V AC |



Powering Business Worldwide



| | |
|---|--|
| Recommended Electrical Service | 15A 120V |
| Input Cord Gauge Type | 14 gauge; SJT |
| Voltage Compatibility (VAC) | 120 |
| Input Plug Type | NEMA 5-15P |
| Input Cord Length (ft.) | 15 |
| Right-Angle Plug | No |
| Input Cord Length (m) | 4.57 |
| Integrated Cord Clip | No |
| OUTPUT | |
| Frequency Compatibility | 50 / 60 Hz |
| Output Receptacles | (10) 5-15R |
| Circuit Breaker (amps) | 15 |
| Transformer Accommodation | (5) Yes |
| Outlet Orientation | Two rows of 5 outlets |
| Right-Angle Outlets | No |
| USER INTERFACE, ALERTS & CONTROLS | |
| Switches | Lighted 2 position switch controls power to all outlets |
| PHYSICAL | |
| Color | Black |
| Material of Construction | Metal |
| Power Cord Color | Black |
| Housing Color | Blue; Gray |
| Included Mounting Accessories | Keyhole slots on removable mounting brackets |
| Mounting Holes or Slots | Yes |
| Slot or Hole Mount Measurement (Center to Center) | Distance between end tabs = 462.30mm |
| Outlets Measurement (Center to Center) | Distance between horizontal outlets = 2.81 in.; Distance between vertical outlets = 1.53 in. |
| Receptacle Color | Black |
| Shipping Dimensions (hwd / in.) | 2.50 x 9.00 x 20.25 |
| Shipping Dimensions (hwd / cm) | 6.35 x 22.86 x 51.44 |
| Shipping Weight (lbs.) | 5.15 |
| Shipping Weight (kg) | 2.34 |
| Unit Dimensions (hwd / in.) | 2.250 x 17.500 x 4.000 |
| Unit Dimensions (hwd / cm) | 44.5 x 10.2 x 4.4 |



Powering Business Worldwide



| | |
|--------------------------------------|--------------------------------|
| Mounting Details | Includes flanges |
| FEATURES & SPECIFICATIONS | |
| Antimicrobial | No |
| Built-In Circuit Breaker | Yes |
| STANDARDS & COMPLIANCE | |
| Product Certifications | cUL Listed; UL 1363; UL Listed |
| Product Compliance | RoHS |
| WARRANTY & SUPPORT | |
| Product Warranty Period (Worldwide) | Lifetime limited warranty |

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.