

Industrial Power Strip, 10-Outlet, 15 ft. (4.6 m) Cord, Large Plug Spacing

MODEL NUMBER: **UL800CB-15**



Highlights

- 10 outlets
- 15-ft. (4.57 m) cord
- 17.5" length
- Lighted master switch
- All metal housing

Package Includes

- UL800CB-15 Power Strip
- Warranty information
- Instruction manual

Description

The UL800CB-15 Power Strip offers a reliable, convenient method of power distribution for appliances, power tools, lighting and other electrical equipment. Includes 10 NEMA 5-15R output receptacles arranged with traditional wall socket spacing to accept large equipment plugs with minimal outlet blockage. Includes 15-foot (4.6-meter) AC line cord and flat sheet metal flanges for installation in a wide variety of applications. Corded, multi-outlet strip reduces cabling clutter and enables the connection of multiple electrical devices to a single AC wall socket. Unfiltered electrical pass-through makes UL800CB-15 ideal for distributing alternate waveform UPS or generator power. Features rugged all-metal housing, lighted power switch, 15A resettable circuit breaker and attractive blue/gray color scheme.

Features

- Multi-outlet power strip offers reliable, convenient, cost effective method of power distribution for appliances, power tools, lighting and other electrical equipment.
- Includes 10 NEMA 5-15R output receptacles arranged with traditional wall socket spacing to accept large equipment plugs with minimal outlet blockage
- Lighted on/off switch controls power to all outlets
- Keyhole mounting tabs for installation in a wide variety of applications
- UL Recognized Component, Tested to UL1363 (Power Tap), cUL (Canada)
- 15 amp power handling capacity with circuit breaker
- 15-ft. (4.57 m) AC line cord

Specifications

OVERVIEW	
UPC Code	037332117724
INPUT	
Nominal Input Voltage(s) Supported	120V AC



Powering Business Worldwide



Recommended Electrical Service	15A 120V
Input Cord Gauge Type	14 gauge; SJT
Voltage Compatibility (VAC)	120
Input Plug Type	NEMA 5-15P
Input Cord Length (ft.)	15
Right-Angle Plug	No
Input Cord Length (m)	4.57
Integrated Cord Clip	No
OUTPUT	
Frequency Compatibility	50 / 60 Hz
Output Receptacles	(10) 5-15R
Circuit Breaker (amps)	15
Transformer Accommodation	(5) Yes
Outlet Orientation	Two rows of 5 outlets
Right-Angle Outlets	No
USER INTERFACE, ALERTS & CONTROLS	
Switches	Lighted 2 position switch controls power to all outlets
PHYSICAL	
Color	Black
Material of Construction	Metal
Power Cord Color	Black
Housing Color	Blue; Gray
Included Mounting Accessories	Keyhole slots on removable mounting brackets
Mounting Holes or Slots	Yes
Slot or Hole Mount Measurement (Center to Center)	Distance between end tabs = 462.30mm
Outlets Measurement (Center to Center)	Distance between horizontal outlets = 2.81 in.; Distance between vertical outlets = 1.53 in.
Receptacle Color	Black
Shipping Dimensions (hwd / in.)	2.50 x 9.00 x 20.25
Shipping Dimensions (hwd / cm)	6.35 x 22.86 x 51.44
Shipping Weight (lbs.)	5.15
Shipping Weight (kg)	2.34
Unit Dimensions (hwd / in.)	2.250 x 17.500 x 4.000
Unit Dimensions (hwd / cm)	44.5 x 10.2 x 4.4



Powering Business Worldwide



Mounting Details	Includes flanges
FEATURES & SPECIFICATIONS	
Antimicrobial	No
Built-In Circuit Breaker	Yes
STANDARDS & COMPLIANCE	
Product Certifications	cUL Listed; UL 1363; UL Listed
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.