

Portable Wireless Magnetic Charging Power Bank, USB-C Output, 18W, 4000mAh, Lithium-Ion, Black

MODEL NUMBER: UPB-04K0-1CM



Portable power bank uses wireless technology to charge your smartphone or other compatible device.

Features

4000mAh Lithium-Ion Battery Charges Your Device without an AC Power Outlet

No more frantic searching for an outlet when your mobile device's battery power is getting low. Small and lightweight, this high-capacity power bank dishes out 4000mAh of battery capacity for charging mobile devices, including smartphones, tablets, e-readers and handheld gaming devices. Lithium-ion lasts longer than lead-acid batteries and saves you money in the end. The UPB-04K0-1CM charges devices via its magnetic wireless charging pad or its USB-C port with the included USB-C charging cable.

Magnetic Module Keeps Your Phone Charged, Secure and Ready to Use

The magnetic charging pad is compatible with all smartphones and other devices that support wireless charging. It also works with MagSafe-compatible smartphones (including iPhone 12 and later) to prevent the phone from being jostled off the pad and disconnected while charging.

Adjustable Stand Gives You More Flexibility Over Charging

You can charge your phone while it lays flat on the charging pad, or you can use the adjustable kickstand for flexible placement during charging. You can place the phone vertically to read notifications and messages while it charges or horizontally to stream video.

Protects Your Expensive Devices During Charging

Comprehensive safety features ensure worry-free charging of mobile devices. The UPB-04K0-1CM protects your devices against short circuit, over-voltage, over-current, over-charge and over-discharge. Total output current cannot exceed 9V 2A (18W). The power bank turns off automatically when the connected device reaches full charge.

Easy to Recharge for the Next Time You Leave Home

A lithium-ion battery with 4000mAh of capacity provides charging at maximum power draw for hours, making your devices ready when you need them. Status LEDs let you know how much battery capacity is left. When it's time to charge the internal battery, use the included USB charging cable to connect the power bank's USB-C port to a computer or wall charger. The UPB-04K0-1CM maintains its charge when not in use.

Compact Housing Packs in a Pocket for On-the-Go Charging

An ideal power solution when you're on the road or stuck somewhere without convenient electricity, the portable all-in-one battery charger weighs less than half a pound. It fits comfortably in your purse, pocket

Highlights

- Charges your Apple, Android or Windows smartphone without connecting a cable
- Portable power ideal for road trips, blackouts and other applications without power
- Magnetic charging pad compatible with MagSafe and other wireless-compatible devices
- Protects phone against overcharges, over-voltage, over-current and short circuits
- Adjustable stand allows scrolling, texting or watching video vertically or horizontally

System Requirements

Compatible with Apple, Android and Windows devices

Package Includes

- UPB-04K0-1CM Portable Wireless Magnetic Charging Power Bank
- USB-A to USB-C charging cable, 3 ft. (0.9 m)
- Owner's manual



Powering Business Worldwide

TRIPP LITE
SERIES

or backpack to keep your smartphone, tablet or other handheld device operating when you need it. The UPB-04K0-1CM is compatible with Apple, Android and Windows devices.

Specifications

OVERVIEW	
UPC Code	037332279323
Product Type	Portable Battery Bank with Wireless Magnetic Charging
Charging Form Factor	Pad/Stand; Portable
Device Compatibility	Phone; Tablet
Technology	USB
Country/Region	North America
INPUT	
Nominal Input Voltage(s) Supported	5V DC; 9V DC
Input Plug Type	USB-C (FEMALE)
Input Plug Type Details	USB-A to USB-C charging cable, or user supplied USB-C to USB-C cable
Power Source	USB
OUTPUT	
Output Capacity (Watts)	18
Continuous Output Capacity (Watts)	18
Overload Protection	Yes
BATTERY	
Battery Charging (5V/1.5A Port)	No
Capacity (Ah)	4000
POWER	
Battery Capacity	4000mAh
USB Power Delivery (PD) Charging Support	No
CONNECTIONS	
Number of Ports	1
Side A - Connector 1	USB C (FEMALE)
Side B - Connector 1	Magnetic Charger
USER INTERFACE, ALERTS & CONTROLS	



Powering Business Worldwide

TRIPP LITE
SERIES

LED Indicators	LED's will illuminate one by one (4 total) to indicate status of battery and to indicate device is charging. The LED's will illuminate in left to right order when charging from 0% to 100%, and will then decrease from right to left as battery is decreased during use.
CHARGING	
Number of Charging Ports	1
Total Charging Amps	3A
Total Charging Watts	18
Charging Method	Magnetic Charger; USB; Wireless
Charging Method Detail	4,000 mAh
Charging Port Type	USB C (FEMALE); WIRELESS CHARGING COIL
Charging Ports Details	Magnetic wireless pad charges compatible devices with up to 10 Watts of powerUSB-C port provides 5V/3A or 9V/2A charging outputNote: Only one charging option can be used at a time. If switching from one charging method to the other you must remove your device and wait 60 seconds before switching.
Charging Ports / Amps	2A; 3A
Magnetic Charging	Yes
Wireless Charging	Yes
Overcharge Protection	Yes
Compatible Devices	Smartphone; Tablet
PHYSICAL	
Color	Black
Material of Construction	PC+ABS
Cable Jacket Color	Black
Cable Jacket Material	PVC
Cable Jacket Rating	VW-1
Cable Outer Diameter (OD)	3.5
Cable Length (ft.)	3
Cable Length (m)	0.91
Cable Length (in.)	36
Cable Length (cm)	91.5
Total Number of Ports	1
Unit Dimensions (hwd / in.)	0.530 x 2.740 x 4.210
Unit Dimensions (hwd / cm)	1.35 x 6.97 x 10.7
Unit Dimensions (hwd / mm)	13.5 x 69.7 x 107
Unit Packaging Type	Box
Unit Weight (lbs.)	0.55
Unit Weight (kg)	0.25



Powering Business Worldwide

TRIPP LITE
SERIES

ENVIRONMENTAL	
Operating Temperature Range	32° to 104°F (0° to 40°C)
Storage Temperature Range	-13° to 113°F (-25° to 45°C)
Operating Humidity Range	20% to 90% RH
Storage Humidity Range	45% to 85% RH
FEATURES & SPECIFICATIONS	
GaN Technology	No
Overcurrent Protection	Yes
Overvoltage Protection	Yes
Over Current Protection	Yes
Quick Charge Compliant	No
USB Hub Ports	No
Qi Compliant	No
STANDARDS & COMPLIANCE	
Product Certifications	ICES (Canada); NOM (Mexico)
Product Compliance	FCC (USA); RoHS; WEEE
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	1-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.