

Portable Wireless Charging Power Bank - 10,000 mAh, Qi Certified, Apple and Samsung Compatible, Black

MODEL NUMBER: UPB-10K0-1U1CQ



Portable wireless phone charger transfers battery power to your Qi device without connecting a troublesome cable between them.

Features

Wireless Cell Phone Charger Delivers up to 10W for Apple and Samsung Phones Who wants to plug and unplug power cords when you just want to charge your cell phone? The UPB-10K0-1U1CQ makes charging more convenient by doing it wirelessly. Just place your Qi-certified device on the round charging pad. That's all there is to it. This wireless phone charger even works through most protective phone cases up to 5 millimeters. Note: please remove any magnetic or metal objects from your phone or case before charging.

Compatible with Qi-Certified Cell Phones to Ensure a Safe, Flawless Charge The UPB-10K0-1U1CQ works with all Qi smartphones from Apple, Sony, LG, Samsung and other popular brands. It protects your expensive device from overheating and overcharging that could lead to internal damage. An LED glows blue to indicate the charging process is underway. Another glows red to let you know your phone is at 100%.

Charges up to 2 Wired Mobile Devices at the Same Time or 1 Wirelessly for the Ultimate in Convenience In addition to the wireless charging pad, this portable phone bank includes two charging ports that allow you to charge up to two wired devices simultaneously. The USB-A port supports a 5V 2A output for convenient charging. The USB-C port supports an output of 5V 3A and inputs of 5V 2A or 9V 1.1A. All devices are protected against short circuits, overheating, overcurrent, overvoltage and overcharging. Note: Both USB ports will be inoperable when wireless charging is enabled.

Thin Power Bank Is Ideal for Home, Office or On the Road The portable wireless phone charger's narrow design lets it fit comfortably on your desktop or bedside table for convenient charging. It also slips easily into a purse, briefcase or laptop bag to maintain battery power on the go. An included USB cable connects the power bank to an appropriate USB-A port on a computer or wall charger to keep it at top capacity.

Highlights

- Charges your Apple iPhone or Samsung Galaxy wirelessly with no cable needed
- Includes USB-C and USB-A ports for charging 2 wired mobile devices at the same time
- LED glows blue during charging and turns red to indicate device is fully charged
- Charges your smartphone through its protective case to avoid the hassle of removing it
- Universally compatible with all Qi-certified smartphones and other devices

Applications

- Charge a Qi-certified smartphone wirelessly when plugged into a USB power source or standing alone as a 10,000mAh portable power pack
- Connect USB-A and USB-C charging cables to supply power to as many as 2 mobile devices simultaneously

System Requirements

- Compatible with all Qi-certified smartphones, including Apple, Sony, LG, Samsung and Nokia

Package Includes

- UPB-10K0-1U1CQ Portable Wireless Charging Power Bank
- USB-C to USB-A cable, USB 2.0, 3 ft.
- Owner's manual



Specifications

OVERVIEW	
UPC Code	037332248381
Product Type	Portable Charger; Wireless Charger
Charging Form Factor	Portable
Device Compatibility	Phone; Tablet; Amazon Kindle
Over Current Protection	Yes
Technology	USB; Wireless
INPUT	
Nominal Input Voltage(s) Supported	5V DC
Input Plug Type	USB-C (FEMALE)
Input Plug Type Detail	USB-A to USB-C cable provided
OUTPUT	
Output Capacity	10W
Overload Protection	Yes
POWER	
Battery Capacity	10,000mAh
USER INTERFACE, ALERTS & CONTROLS	
LED Indicators	LED's will illuminate sequentially to indicate the Power Bank's Charging Status as well as Remaining Battery Capacity. See manual for LED information.
CHARGING	
Number of Charging Ports	2
Charging Ports / Amps	(1) 2A; (1) 3A
Total Charging Amps	3A
Charging Method	USB; Wireless
Total Charging Watts	10
Charging Ports Detail	USB-C: 5V/3A USB-A: 5V/2A
Charging Port Type	WIRELESS CHARGING COIL
Charging Method Detail	10,000 mAh; Qi Compatible
PHYSICAL	



Color	Black
Material of Construction	ABS
Unit Dimensions (hwd / in.)	0.72 x 6.6 x 2.98
Unit Packaging Type	Box
Unit Weight (kg)	0.29
Unit Weight (lbs.)	0.64
ENVIRONMENTAL	
Operating Temperature Range	32 to 86°F (0 to 30°C)
Storage Temperature Range	-4 to 158°F (-20 to 70°C)
Operating Humidity Range	0% to 85% RH, Non-Condensing
Storage Humidity Range	0% to 95% RH, Non-Condensing
CONNECTIONS	
Ports	2
Side A - Connector 1	WIRELESS CHARGING COIL
Side B - Connector 1	USB A (FEMALE)
Side B - Connector 2	USB Type-C (FEMALE)
SPECIAL FEATURES	
Overcurrent Protection	Yes
Overvoltage Protection	Yes
GaN Technology	No
STANDARDS & COMPLIANCE	
Certifications	CE, FCC, RoHS, REACH
WARRANTY	
Product Warranty Period (Worldwide)	1-year limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>